D2.1.0

TRAC-LITES One Circuit Trac System

R2, R4, R6, and R8

T90-12, T90-18, T90-

24, 190-36, 190-48

T-Bar Pendant Stem Kit (12",

18", 24", 36", 48") - Use two for 2', 4', 6' of trac or

cover. WH, BL

feed.

T94WH, T94BL

60° anale.

T96WH, T96BL

Sloped Ceiling Adapter. Allows **T90** or **T91** pendant to hang

ceilings. Can be used to feed electrical wires to Trac at up to

straight down from sloped

T91-36, T91-48

three for 8' of trac. For electrical feed, order T93 wireway

T91-12, T91-18, T90-24,


Rigid Ceiling Pendant Stem Kit (12", 18", 24", 36", 48") -Use two for 2', 4', 6' of trac or

three for 8' of trac. For electri-

cal feed, order T93 wireway

Pendant Stems





4 3/4






Pendant Stem Threaded Coupling. Enables multiple pendant stems to be joined for higher ceiling applications. T56WH, T56BL Solid Rod Pendant Mounting

Kit. Attaches solid 5/16" threaded rod to Trac. Includes: plastic cap, mounting bracket and hardware. Rod not supplied.

Electrical End Feeds



R21WH, R21BL

End Feed Connector and

cover, fixture strap and

R29WH, R29BL

ground screw.

Outlet Box Cover. For outlet

box feed. Includes: outlet box

Floating Electrical Feed. Permits

mounting any point of trac under

outlet box. Includes floating connector, outlet box cove

plus extra trac dead end.

R34WH, R34BL

connector.

R36WH

Conduit Feed. For surface

wiring. Use standard 1/2"

T-Bar End Feed. Wiring com-

partment contains standard

1/2" KO's. Feeds surface

is directly above trac.

R38WH, R38BL

trac from above, when T-bar

Live End Feed Connector. Feed

trac from above with flexible

conduit, BX, etc., or end feed

in pendant systems. Accepts

standard 1/2'' connector.

Wiremold Attachment Clip. For use with R38 connector

and Wiremold Raceway

#200. (Not available in

R22WH, R22BL

Cord and Plug Connector. Comes with 15' two-wire

white cord. Includes surface wire retainers and in-line switch. Max cap. 7 amps.

T38X

Canada)













Trac Joiners



end 3/8"



R25WH, R25BL "T" Connector. Joins three required.

____4" sq. ⊣ screw.

R20WH, R20BL Accordion Adjustable Joiner. Can flex to 90° angle to

two trac sections.

R23WH, R23BL Miniature Straight Connector. Joins two trac sections end to

left, right, up or down. Joins

R24WH, R24BL Adjustable Connector. Joins two trac sections to make a

90° angle or straight run. Straight and right angle covers supplied. For outlet box feed, No. T27 cover plate required.

trac sections. For outlet box feed, No. T27 cover plate

T27WH, T27BL Outlet Box Cover. Use with Nos. R26/R25 for outlet box electrical feed. Includes: nipple, locknut and ground

4 1/8" 1/2"

Accessories



T-bar Attachment Clip. To attach to inverted tee ceiling. Use two for 2' or 4' trac and three for 6', 8'. T37D Same as above with spacer for ceilings using drop tiles.

Mono-Point



R40WH, R40BL Mono-Point Adaptor. Mounts directly to outlet box. Accepts one 120V Juno trac fixture.





T37F

1300 S. Wolf Road, P.O. Box 5065, Des Plaines, IL 60017-5065 Phone 847.827.9880 FAX 847.827.2925 220 Chrysler Dr., Brampton, Ontario, Canada, L6S 6B6 Phone 905.792.7335 FAX 905.792.0064 Visit us at www.junolighting.com Printed in U.S.A. ©2001 Juno Lighting, Inc.



JUNO° lighting

Project:

Fixture Type:

Location:

Contact/Phone:

One Circuit Trac System

TRAC SECTIONS, JOINERS & FEEDS

PRODUCT DESCRIPTION

Low-Profile, single-circuit trac sections for surface or pendant mounting. Compatible with a full range of feed, connector and mounting accessories, as listed on back of this page. Accepts all Trac-Lites and Trac-Master trac fixtures.

PRODUCT SPECIFICATIONS

Construction Extruded aluminum with Temprite® insulator • Injection molded polycarbonate dead-end with set screw.

Electrical Two 12 gauge solid copper conductors • Rated 20 amps at 120 volts • Aluminum channel used as system ground • One-piece insulator insures consistent conductor spacing for reliable electrical contact • Insulating bushings supplied at mounting hole locations to prevent shorts to ground.

Labels UL/CUL listed.

PRODUCT INSTALLATION


Debossed polarity line provides visual cue to proper trac, trac connector and fixture alignment • Supplied with toggle bolts for surface mounting • Insulator stays same length as extrusion to simplify field-cutting of trac • Connectors and feeds simply push into trac sections.


PRODUCT CODES

Catalog Number	Description	Actual Length	Finish	
R2WH	2' Trac Section	19 ⁷ / ₈ ″	White	
R2BL	2' Trac Section	19 ⁷ /8″	Black	
R4WH	4' Trac Section	43 7⁄8″	White	
R4BL	4' Trac Section	43 7⁄8″	Black	
R6WH	6' Trac Section	67 7⁄8″	White	
R6BL	6' Trac Section	67 7⁄8″	Black	
R8WH	8' Trac Section	91 7⁄8″	White	
R8BL	8' Trac Section	91 7⁄8″	Black	









TRAC-LITES

R2, R4, R6, and R8