



4" IC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS
V4ICW

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

PRODUCT DESCRIPTION

IC Air-Loc® Housing with all 4" trims complies with IECC, Washington State and other state Energy Codes • Double wall construction • Energy efficient, sealed inner housing does not require separate ALG gasket • Air-Loc housing stops infiltration and exfiltration of air, reducing heating and cooling costs • Can be completely covered with insulation.

PRODUCT SPECIFICATIONS

Lamp Lamp ratings based on trim selected – see reverse.

Socket Floating medium base porcelain socket with nickel-plated copper screw shell • Shipped with socket cap to protect against paint overspray.

Trims Trim selection shown on reverse.

Labels UL/cUL listed for through-branch wiring, damp locations and IP • Product thermally protected against improper use of lamps • Union made • UL/CUL Listed • Trim No. V4012 is wet location approved for covered ceiling applications • Trims V4034, V4017 are wet location approved for covered ceiling applications, **when used with outdoor rated lamps.**

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Product specifications subject to change without notice.

INSTALLATION



Bar Hangers Telescoping bar hangers with captive nail allow for quick placement of housing anywhere within 24" O.C. joists • Can be installed in suspended ceiling grid using T-bar clip accessory • Bars scored in two locations for fast clean breaking allowing housing installation in tight applications • Edge-mounted for extra strength and captive to mounting frame • May be installed either perpendicular or parallel to junction box • Locking set screw locks fixture in position • Alternate mounting holes included.

Junction Box Pre-wired junction box provided with (6) 1/2" and (1) 3/4" knockouts, (4) Non-metallic sheathed cable connectors and ground wire, UL/cUL Listed for through-branch wiring, maximum 6 No. 12 AWG 90° C branch circuit conductors (3 in, 3 out)
• Junction box provided with removable access plates
• Knockouts equipped with pryout slots.

Mounting Frame 22-gauge die-formed galvanized steel mounting frame • 8 3/8" L x 6" W, (excluding bar hangers)
• Rough-in section (junction box, mounting frame, housing and bar hangers) fully assembled for ease of installation.

Housing Air-Loc IC housing, .032" aluminum • Inner housing is vertically adjustable to accommodate up to a 1 1/4" ceiling thickness.

DIMENSIONS



4 1/2" CEILING CUTOUT

ACCESSORIES

Catalog No.	Description
G2405	T-Bar Clips (Set of 4)

To order, specify catalog number.

PRODUCT CODES

Catalog Number	Input Voltage	Lamp Rating (max.)
V4ICW	120V	R16/R20/PAR16/PAR20 (See reverse for max. trim rating)









4" IC NEW CONSTRUCTION HOUSING

INCANDESCENT LAMPS

V4ICW

TRIMS/LAMPS

	Cat. No.	Description	Max. Lamp Rating
	V4034W-WH◆◆	White Baffle	50W PAR20, 30W R20
	V4034B-WH◆◆	Black Baffle	
	V4017C-WH◆◆	Clear Cone	50W PAR20, 50W R20
	V4010-WH	White Gimbal Ring	50W PAR20
	V4018-WH	White Eyeball	60W PAR16, 40W R16
	V4012-WH◆	Stippled Opal Lens Shower with Reflector	35W PAR20, 30W R20

Trim Size: 5" O.D.

Trim Finish: WH - White.

Note: In Canada when insulation is present, Type IC fixtures must be used.

◆ UL/cUL Listed for use in wet location.

◆◆ UL/cUL Listed for use in wet location with outdoor rated lamp.

Air-Loc Vulite IC housings meet IECC Energy Code requirements per ASTM E283. Air-Loc® rated trims are pre-gasketed for minimum air leakage with IC housings.



1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925
 220 Chrysler Drive • Brampton, Ontario • Canada L6S 6B6 • Phone (905) 792-7335 • Fax (905) 792-0064
 Visit us at www.junolightinggroup.com

Printed in U.S.A. ©2011 Juno Lighting, LLC.