

Catalog Number	
Notes	Type

## FEATURES & SPECIFICATIONS

### INTENDED USE

For use with housings L3, LI3, and L3R.

### CONSTRUCTION

Antique bronze, oil-rubbed bronze, brushed nickel, polished brass and white finishes are one piece aluminum reflectors with integral flange. Anodized finishes are separate white polymeric flange ring as standard.

### INSTALLATION

Socket to trim interface.


Retaining clips pull and snap onto top of reflector to hold trim inside housing.

### LISTING

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.


Pull on clip Patent # (U.S.) 5707143, (Canada) 2193902.



3" Finishing Trim

# 301

**OPEN SHALLOW**  
Narrow Flange



### Specifications

Height: 4-3/4 (12.1)

Lamp Opening: 3-1/2 (8.9)

Diameter: 4-7/8 (12.4)

All dimensions are inches (centimeters) unless otherwise specified.

## ORDERING INFORMATION

Example: **301**

Choose the boldface catalog nomenclature that best suits your needs and write it on the appropriate line. Order accessories as separate catalog number.

301		
Series	Finish	Options
<b>301</b>	(blank) White	<b>TRBL</b> Black flange ring <sup>1</sup>
	<b>BL</b> Black diffuse	
	<b>BN</b> Brushed nickel	
	<b>BZA</b> Antique bronze	
	<b>ORB</b> Oil-rubbed bronze	
	<b>PB</b> Polished brass	
	<u>Anodized finish</u>	
	<b>A</b> Clear diffuse	
	<b>AZ</b> Clear specular	
	<b>BLZ</b> Black specular	
	<b>G</b> Gold diffuse	
	<b>GZ</b> Gold specular	

NOTES:

1 Available with anodized finishes only.

### Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
<i>IC</i>	Incandescent	40 PAR16	<b>L13</b>
		50 PAR20	<b>L13</b>
		35 PAR20	<b>L3, L3R</b>
		50 R20	<b>L13</b>
		30 R20	<b>L3, L3R</b>
<i>Non-IC</i>	Incandescent	75 PAR16	<b>L3</b>
		45 PAR16	<b>L3R</b>
		50 PAR20	<b>L3, L3R</b>
		50 R20	<b>L3, L3R</b>

# 301 3" Open Shallow Full Reflector Trim

---

For BR and PAR reflector lamps, see Lamp Manufactures's published raw lamp data for Photometrics.

