

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L7X, L7XR, LC6, L7XF and L7XFR.

CONSTRUCTION

Aluminum one piece reflector.

Polyester powder coat paint.

Antique brass, brush nickel, oil-rubbed bronze, and white finishes are one-piece aluminum reflectors with integral flange.

INSTALLATION

Socket to trim interface.

Trim retention is achieved by utilizing two side-mounted torsion springs on the trim and two receiving brackets in the can, ensuring a consistently tight fit with the ceiling.

LISTINGS

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

WARRANTY — 1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx



NOTE: Specifications subject to change without notice.

Catalog Number	
Notes	Type

6" Full Reflector Trim

702

OPEN
Narrow Flange



Specifications

Height: 6-1/8 (15.6)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

All dimensions are inches (centimeters) unless otherwise specified.

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: **702 TOR**

702	
Series	Finish
702	(blank) White
A PFMW¹	Clear diffuse, matte white plastic flange
AB	Antique brass
MW	Matte white
BN	Brushed nickel
ORB	Oil-rubbed bronze

TOR
Mounting method
TOR Torsion springs

Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	L7X, L7XR, LC6
		65 BR30	L7X, L7XR, LC6
	Fluorescent	13DTT	L7XF, L7XFR
		26TRT	L7XF, L7XFR

NOTE

¹ PFMW is a two-piece design with plastic flange ring.

702 6" Open Full Reflector Trim

For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.



Sheet #: 702-TOR

© 2009-2012 Acuity Brands Lighting, Inc. All rights reserved. Rev. 10/01/12

Lithonia Lighting
Recessed Downlighting
One Lithonia Way, Conyers, GA 30012
Phone: 800-315-4935 Fax: 770-860-3129
www.lithonia.com