

WALLPACK® SERIES

- **Unique underpass refractor** Redirects light from drivers line of sight and spreads light across multiple lanes of traffic.

- **More efficient precision reflector** Provides up to 55% higher street side output than competitive units.

- **Adjustable optics** 50° or 60° main beam optimizes one or two sided designs and visibility.

- **Borosilicate prismatic glass refractor** Non-yellowing, precise control with minimum glare.

- **Corrosion protection** Low copper aluminum housing, phosphate pretreatment and 2-4 mil polyester powder finish provides long life where salt and alkali leachate is a problem.

- **Protected HPS starter** Shuts off when lamp fails. Prevents starter failure and ballast thermal damage from continuous operation.

- **Multiple wiring access** Wallpacks can be wired from side or back. Wallpack® III features optional thru wiring capability



Underpass Wallpack



Wallpack III


Ordering data

How to construct a catalog number:

Example: WL3K — 250HP — 12 — BZ — _____ Fixture type _____

1 2 3 4 5


Cat. no.	Description
1 Luminaire	
— WL2K	Wallpack II; UL listed 40°C wet location
— WL3K	Wallpack III; UL listed 40°C wet location; CSA certified
2 Source and wattage	
WL2K	
— 035LP	35W LPS (N/A with "MT")
— 070HP	70W HPS
— 100HP	100W HPS
— 15AHP	150W-55V HPS
— 100MV	100W mercury
— 175MV	175W mercury
— 250MV	250W mercury (N/A with "MT")
— 70DMH	70W MH (N/A with 480V)
— 10DMH	100W MH (N/A with 480V)
— 15DMH	150W MH (N/A with 347 or 480V)
— 175MH	175W MH
— 30DIN	300W incandescent, medium base
— 26QFL	26W CF (min. starting temp. 50° F)
WL3K	
— 250HP*	250W HPS
— 400HP*	400W HPS
— 250MH*	250W MH
— 400MH*	400W MH
3 Voltage	
— 12	120V
— 20	208V
— 24	240V
— 27	277V
— 34	347V
— 48	480V
— MT	Multi-voltage 120/208/240/277V
— VT	Vari-tap 120/277/347V
4 Color	
— BZ	Bronze
— BK	Black
— WH	White
— GR	Grey
5 Options & accessories	
— F1	Single fusing for 120, 240, 277 and 347V; factory installed
— F2	Double fusing for 208, 240 and 480V; factory installed
— PS	Protected starter; HPS units only
— TW	Thru-wiring (WL3K only)
— U	Underpass optics
— Lamp	Shipment of appropriate lamp
— WL2KPR12	Photocontrol kit for 120V
— WL2KPR	Photocontrol kit for 208, 240 or 277V
— WL2KPR34	Photocontrol kit for 347V
— WL2KTP	Tamper-resistant screws
— WL2KWG	Wire guard
— WL2KPA	Polycarbonate shield; not available with "TW"- thru-wiring option
— TPD1	Driver for tamper-resistant screws



Weight:

WL2K 7-11kg (15-25 lbs)

WL3K 15-16 kg (32-36 lbs)



* Available with Vari-tap

WALLPACK® SERIES