

SU202M-C40



Miniature Circuit Breaker - SU200M - 2P - C - 40 ampere

General Information

Extended Product Type	SU202M-C40
Product ID	2CDS272337R0404
EAN	4016779931168
Catalog Description	Miniature Circuit Breaker - SU200M - 2P - C - 40 ampere
Long Description	SU202M-C40 Miniature Circuit Breaker C-Char., 10kA, 40A, 2P UL489

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85362010

Popular Downloads

Data Sheet, Technical Information	2CDC002177D0202
Instructions and Manuals	2CDC002177D0202

Dimensions

Product Net Width	35 mm
Product Net Depth / Length	69 mm
Product Net Height	111 mm
Product Net Weight	0.25 kg

Technical

Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Number of Poles	2
Tripping Characteristic	C
Rated Current (I_n)	40 A
Rated Operational Voltage	acc. to IEC 60947-2 400 V AC
Power Loss	9 W at Rated Operating Conditions per Pole 4,5 W
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 440 V
Rated Frequency (f)	50 Hz

	60 Hz DC Hz
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu})	(400 V AC) 15 kA
Rated Service Short-Circuit Breaking Capacity (I_{cs})	(400 V AC) 11.2 kA
Overvoltage Category	III
Pollution Degree	3
Housing Material	Insulation Group I, RAL 7035
Contact Position Indication	Red ON / Green OFF
Degree of Protection	IP20
Remarks	IP40 in enclosure with cover 20000 cycle
Terminal Type	Screw Terminals
Screw Terminal Type	Failsafe Bi-directional Cylinder-lift Terminal
Connecting Capacity	Busbar 10 / 10 mm ² Flexible with Ferrule 0.75 ... 25 mm ² Flexible 0.75 ... 25 mm ² Rigid 0.75 ... 35 mm ² Stranded 0.75 ... 35 mm ²
Tightening Torque	2.8 N·m
Recommended Screw Driver	Pozidriv 2
Mounting on DIN Rail	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Position	Any

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
Resistance to Shock acc. to IEC 60068-2-27	25g / 2 shocks / 13 ms
Resistance to Vibrations acc. to IEC 60068-2-6	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
Environmental Conditions	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage UL/CSA	480Y / 277 V AC 96 V DC
Connecting Capacity UL/CSA	Busbar 18-8 AWG Conductor 18-4 AWG

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2CDK400595D2702
Instructions and Manuals	2CDC002177D0202
RoHS Information	2CDK400596D0203

Container Information

Package Level 1 Units	5 piece
Package Level 1 Width	121 mm

Package Level 1 Depth / Length	191 mm
Package Level 1 Height	82 mm
Package Level 1 Gross Weight	1.3 kg
Package Level 1 EAN	4016779934909
Package Level 2 Units	36 piece
Package Level 2 Width	275 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Height	210 mm
Package Level 2 Gross Weight	16 kg
Package Level 2 EAN	4016779938709

Classifications

ETIM 5	EC000042 - Miniature circuit breaker (MCB)
ETIM 6	EC000042 - Miniature circuit breaker (MCB)
ETIM 7	EC000042 - Miniature circuit breaker (MCB)
eClass	7.0 27141901
UNSPSC	39121614

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Miniature Circuit Breakers MCBs

