
Functional Devices, Inc. 101 Commerce Drive Sharpsville, IN 46068 Toll Free: (800) 888-5538 Office: (765) 883-5538 Fax: (765) 883-7505 Email: sales@functionaldevices.com Website: www.functionaldevices.com

CLC106

Enclosed Relay 5 Amp SPST, Separated Class 2 Magnetic Door Switch Input, 120 Vac Power





Specifications

Relays & Contact Type: One (1) SPST Continuous Duty Coil 10 Expected Relay Life: million cycles minimum mechanical -30

Operating Temperature: to 140° F

Dimensions: 2.90" x 1.50" x 1.05"

with Retaining Clip for 1/2" Knockout

Wires: 16", 600 V Rated (120 Vac Connections) 6' Leads on Magnetic Door Switch

Approvals: UL Listed, UL916, C-UL

Housing Rating: UL Accepted for Use in Plenum, NEMA 1

Gold Flash: No Override Switch: No

Contact Ratings:

- 5 Amp Resistive @ 120 Vac
- 5 Amp Electronic Ballast @ 120 Vac
- 5 Amp Magnetic Ballast @ 120 Vac
- 5 Amp Tungsten @ 120 Vac

Power Usage:

21 mA @ 120 Vac Max.

Notes:

• By default, the Magnetic Switch being closed turns the light off. To reverse this (Magnetic Switch Closed turns the light *on*), add "-NC" to end of model number. See table below:

Model #	Magnetic Switch Closed	Magnetic Switch Open
CLC106	Light OFF	Light ON
CLC106-NC	Light ON	Light OFF

Retrofit Applications

- · Easily fits inside junction box
- Includes magnetic door switch.
 When the magnet and contact are separated, the closet light turns on.
- 120 Vac operation

