

## **FEATURES & SPECIFICATIONS**

INTENDED USE — The adjustable LED Gimbal downlighting module is 80% more efficient than incandescent luminaries, performing for 35,000 hours or more with exceptional energy efficiency and near zeromaintenance. Multiple trim finish options are available to pick the style that matches the décor for any  $of fice\ or\ home.\ The\ LED\ Gimbal\ is\ intended\ for\ sloped\ ceiling\ applications,\ grazing\ textured\ surfaces,\ wall$ washing, and highlighting artwork or other architectural features. Retrofits into most existing recessed downlighting installations or new construction and remodel applications.

**CONSTRUCTION** — Spun steel gimbal reflectors with 180° of rotation and at least 35° of adjustable tilt in both directions. Driver affixed to a static yoke to allow maximization of LED light engine rotation

 $\textbf{OPTICS} - \textbf{Diffused lens at end of mixing chamber to provide even light distribution for general illuminations and the last of the provided even light distribution for general illuminations and the last of the last of$ tion, equivalent to 65W incandescent flood lamp.

Wide flood beam angle at >90°. Utilizes 3000 K color temperature LEDs. CRI - 80+. The LED module maintains at least 70% light output for 35,000 hours.

**ELECTRICAL** — Primary power disconnect provided for simple connection to a dedicated LED connector in the housing. Dimming down to 15%. For compatible dimmers, refer to Compatible Dimmers Chart.

Standard input wattage is 10.8 watts, 55 lumens per watt; equivalent to 65-watt incandescent.

**INSTALLATION** — Suitable for installation in standard height rough-in sections. E26 socket adapter and splice kit ships standard. This enables easy installation or permanent conversion to an LED source for Title 24 compliance. Trim retention is achieved by utilizing two side-mounted torsion springs to ensure a consistently tight fit with the ceiling and easy installation.

LISTINGS — CSA certified to US and Canadian safety standards. ENERGY STAR® qualified; California T24 compliant. Damp location listed.

WARRANTY — 5-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms\_and\_conditions.aspx

Actual wattage may differ by  $\pm$ -5% when operating at 120V  $\pm$ -10%.

Note: Specifications subject to change without notice.

3 (7.6)

as rough-in

4-5/8 (11.7)

4-5/16 (10.9)

6-7/16 (16.3)

**Specifications** 


Aperture:


Length:


Height:

Overlap trim:

Ceiling opening:







Brush

Nickel



Oil Rubbed

Bronze



IC/Non-IC

**Retrofit Gimbal** 

**Example:** 5G1MW LED L5LED T24

ORDERING INFORMATION For shortest lead times, configure product using **bolded options**.

5G1		LED								
Series/Finish		Lamp/Lumen <sup>1</sup>		Color temperature		Voltage		Options		
MB BN	Matte white Matte black Brush nickel Oil-rubbed bronze	LED	600 lumens, 10.8 watts	(blank)	3000K	(blank)	120V	L5LED T24 L5RLED T24 L5 L5R	New construction rough-in (LED connector) Remodel rough-in (LED connector) New construction rough-in <sup>2</sup> Remodel rough-in <sup>2</sup>	

Catalog

Number

Notes

Туре

Matte

Black

## Accessories: Order as separate catalog number.

Makes non-bracket housings compatible with LED module

## Notes


- 1 Total system delivered lumens.
- 2 Must be ordered on a separate line

**DOWNLIGHTING** 5G1 LED GIMBAL

## **PHOTOMETRICS**

<b>Distribution Curve</b>	<b>Distribution Data</b>	Output Data	Coefficient of Utilization	Illuminance Data at 30" Above Floor for
				a Single Luminaire

5G1MW LED, 3000 K LEDs, input watts: 11.17, delivered lumens: 672, LM/W=60, test no. LTL23565, tested in accordance with IESNA LM 79-80.



Coefficients of Utilization									
pf				2	0%				
рс		80%			70%			50%	
pw	70%	50%	30%	50%	30%	10%	50%	30%	10%
0	119	119	119	116	116	116	111	111	111
1	109	105	101	103	99	96	98	95	93
2	100	92	86	90	84	79	87	82	77
3	92	81	74	80	73	67	77	71	66
<u>~</u> 4	84	73	64	71	63	57	69	62	56
<u>2</u> 5	78	65	56	64	56	50	62	55	49
<sup>L</sup> 6	72	59	50	58	50	44	56	49	43
7	67	54	45	53	45	39	51	44	39
8	62	49	41	48	40	35	47	40	35
9	58	45	37	45	37	32	43	36	31
10	55	42	34	41	34	29	40	33	29

0° - 30°			% Fixture
0 - 30	209	31.1	31.1
0° - 40°	332	49.4	49.4
0° - 60°	553	82.2	82.2
0° - 90°	672	100.0	100.0
90° - 180°	0	0.0	0.0
0° - 180°	672	100.0	100.0
	0° - 60° 0° - 90° 90° - 180°	0° - 60° 553 0° - 90° 672 90° - 180° 0	0° - 60° 553 82.2 0° - 90° 672 100.0 90° - 180° 0 0.0

ENERGY DATA*				
Lumens	600			
Min. starting temp	-18°C (0°F)			
EMI/RFI	FCC Title 47 CFR, Part 15, Class B			
Sound rating	Class A standards			
Input voltage	120V			
Min. power factor	0.80			
Input frequency	50/60 Hz			
Rated wattage	10.8W			
Input power	10.8W			
Input current	0.11A			

<sup>\*</sup>Values at non-dimming line voltage.

