



S39392

36W/LED/HID/5000K/100-277V/E26
36 watt LED HID Replacement; 5000K; Medium base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP64 rated
- For outdoor & indoor use
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Shatter resistant materials, acceptable for use in food prep areas



S39392

Minimum Compartment Size		
Length	Width	Depth
8.5 inch	6 inch	6 inch

Optional Accessories

- In-line surge protector [80-929](#)
- Mog to med socket reducer (rated up to 250V) [92-406](#)

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	Incandescent Equivalent	Fluorescent Equivalent
S39392	Hi-Pro	045923303920	100 - 277	36	50/60Hz	200W	55W

HID Equivalent	Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches
150W	Medium	E26	36W/LED/HID/5000K/100-277V/E26	Non-Dimmable	White	7-11/32"	3-11/32"
Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack
5148	50000	5000	Natural Light	80	300	-20C (-4F) to a maximum of +65C (+149F)	12
Package Type	CEC Status	Material	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	
Box	Lawful for sale in California	Aluminum	Yes	Yes	cULus - Damp Location Rated	5 Year Limited	



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

