


# **Specifications**

7-1/2" Width:

8" Height: (20.3 cm)

Depth: (7.62 cm)

5 lbs Weight:



# Introduction

As versatile as it is efficient, the OLWX1 is designed to replace up to 250W metal halide while saving over 87% in energy costs. It combines multiple mounting options with the latest generation of LEDs for a wall pack luminaire that converts to a whole lot more. Whether you are mounting it to a recessed junction box, conduit/through wiring, as an up light, as a down light, or as a flood light - the OLWX1 has you covered.

# **Ordering Information**

3"

## **EXAMPLE: OLWX1 LED 20W 50K**

OLWX1 LED					
Series	Performance Package	Color Temperature	Voltage	Controls	Finish
OLWX1 LED	13W 13 watts 20W 20 watts 40W 40 watts	<b>40K</b> 4000 K <sup>1</sup> <b>50K</b> 5000 K	(blank) MVOLT <sup>2</sup> 120 120V <sup>3</sup> 347 347V	(blank) None PE 120V button photocell 1,3	(blank) Dark bronze

## Accessories

OLWX1TS Slipfitter - size 1 OLWX1YK OLWX1THK Knuckle - size 1

### NOTES

- 1 Not available with 347V option.
- MVOLT driver operates on any line voltage from 120-277V (50/60Hz).
- 3 Specify 120V when ordering with photocell (PE option).

# **FEATURES & SPECIFICATIONS**

# INTENDED USE

The versatility of the OLWX1 LED combines a sleek, low-profile wall pack design and high-output LEDs to provide an energy efficient, low maintenance LED wall pack suitable for replacing up to 250W metal halide fixtures. Available flood light mounting accessories convert the OLWX1 LED into a highly

OLWX1 LED is ideal for outdoor applications such as building perimeters, loading areas, driveways and sign and building flood lighting.

Rugged cast-aluminum housing with textured dark bronze polyester powder paint for lasting durability. Integral heat sinks optimize thermal management through conductive and convective cooling. LEDs are protected behind a glass lens. Housing is sealed against moisture and environmental contaminants (IP65).

High-performance LEDs behind clear glass for maximum light output. Light engines are available in 4000K and 5000K CCTs. See Lighting Facts label and photometry reports for specific fixture performance

## FI FCTRICAL

Light engine consists of 1 high-efficiency Chip On Board (COB) LED with integrated circuit board mounted directly to the housing to maximize heat dissipation and promote long life (L73/100,000 hours at 25°C). Electronic drivers have a power factor >90% and THD <20% and a minimum 2.5kV surge rating. Flood light mounting accessories include an additional 6kV surge protection device.

### INSTALLATION

Easily mounts to recessed junction boxes with the included wall mount bracket, or for surface mounting and conduit entry - with the included junction box with five 1/2" threaded conduit entry hubs. Flood light mounting accessories (sold separately) include knuckle, integral slipfitter and yoke mounting options. Each flood mount accessory comes with a top visor and vandal guard. Luminaire may be wall or ground mounted in downward or upward orientation.

UL Listed to U.S. and Canadian safety standards for wet locations. Rated for -40° C minimum ambient. Tested in accordance with IESNA LM-79 and LM-80 standards. DesignLights Consortium® (DLC) qualified product. Not all versions of this product may be DLC qualified. Please check the DLC Qualified Products List at www.designlights.org to confirm which versions are qualified.

## WARRANTY

Five-year limited warranty. Full warranty terms located at rces/Terms and conditions.aspx.

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25°C. Specifications subject to change without notice.



# **Performance Data**

## **Lumen Output**

Lumen values are from photometric tests performed in accordance with IESNA LM-79-08. Data is considered to be representative of the configurations shown, within the tolerances allowed by Lighting Facts.

Fixture Model Number	ССТ	System Watts	Lumens	LPW	В	U	G	CRI
OLWX1 LED 13W 40K	4000 K	14 W	1,271	91	1	0	0	>70
OLWX1 LED 13W 50K	5000 K	14 W	1,289	92	1	0	0	>80
OLWX1 LED 20W 40K	4000 K	22 W	1,854	84	1	0	0	>70
OLWX1 LED 20W 50K	5000 K	22 W	1,860	84	1	0	0	>80
OLWX1 LED 40W 40K	4000 K	39 W	4,027	101	2	0	0	>70
OLWX1 LED 40W 50K	5000 K	37 W	4,079	110	2	0	0	>70

# **Electrical Load**

	Input current at given input voltage (amps)						
Fixture Model Number	Rated Power (watts)	120V	208V	240V	277V	347V	
OLWX1 LED 13W 40K	14 W	0.12	0.07	0.06	0.06	0.04	
OLWX1 LED 13W 50K	14 W	0.12	0.07	0.06	0.06	0.04	
OLWX1 LED 20W 40K	22 W	0.20	0.12	0.10	0.09	0.06	
OLWX1 LED 20W 50K	22 W	0.20	0.12	0.10	0.09	0.06	
OLWX1 LED 40W 40K	39 W	0.37	0.21	0.19	0.16	0.11	
OLWX1 LED 40W 50K	37 W	0.37	0.21	0.19	0.16	0.11	

# **Lumen Ambient Temperature (LAT) Multipliers**

Use these factors to determine relative lumen output for average ambient temperatures from  $0.40^{\circ}\text{C}$  (32-104°F).

	0°C	10℃	20°C	25℃	30℃	40°C
13W	1.06	1.03	1.01	1.00	0.99	0.96
20W	1.06	1.04	1.01	1.00	0.99	0.96
40W	1.07	1.04	1.01	1.00	0.99	0.96

## **Projected LED Lumen Maintenance**

Data references the extrapolated performance projections in a 25°C ambient, based on 10,000 hours of LED testing (tested per IESNA LM-80-08 and projected per IESNA TM-21-11).


To calculate LLF, use the lumen maintenance factor that corresponds to the desired number of operating hours below. For other lumen maintenance values, contact factory.


Operating Hours	0	25,000	50,000	100,000
OLWX1 LED 13W	1.00	0.92	0.85	0.73
OLWX1 LED 20W	1.00	0.92	0.85	0.73
OLWX1 LED 40W	1.00	0.94	0.88	0.79


# **Photometric Diagrams**

To see complete photometric reports or download .ies files for this product, visit the Lithonia Lighting OLWX1 LED homepage. Tested in accordance with IESNA LM-79 and LM-80 standards










Test No. LTL22696 tested in accordance with IESNA LM-79-08.



OLWX1 LED 40W 40K, Mounting height = 15'

Test No. LTL22695 tested in accordance with IESNA LM-79-08.

# **Accessories**



OLWX1TS Slipfitter – size 1



OLWX1YK Yoke – size 1



OLWX1THK Knuckle – size 1




Top Visor and Vandal Guard included with accessories




# **Lighting Facts Labels**


#### OLWX1 LED 13W 40K XXX XX XXX




#### OLWX1 LFD 13W 50K XXX XX XXX




#### OLWX1 LED 20W 40K XXX XX XXX



#### OLWX1 LED 20W 50K XXX XX XXX



#### OLWX1 LED 40W 40K XXX XX XXX



#### OLWX1 LED 40W 50K XXX XX XXX

