

FEATURES & SPECIFICATIONS

INTENDED USE

Provides general illumination in residential and commercial applications. Ideal for use in garages, corridors, utility areas, workshops and more.

CONSTRUCTION

Features a white high-gloss polycarbonate diffuser with passive infrared (PIR) motion sensor for easy on/ off operation. The 360° PIR sensor activates when motion is detected. Can be pre-set to automatically turn off from 1 to 10 minutes.

OPTICS

The SGLL produces 5,000 lumens. Standard input = 80 watts.

80 and 90 CRI.

Minimum starting temperature at -22°F.

ELECTRICAL

Fixture operates at 120 volts, 60 Hz.

INSTALLATION

Flush or suspension mount. Can be direct wired or plugged in with the provided 5 foot power cable. Can link multiple fixtures (FLUSH MOUNT ONLY). End-to-end connector included. 18-inch adjustable suspension mount aircraft cable is also included. Mounting hardware included, for installation to j-box.

LISTINGS

UL Certified to US and Canadian standards and listed suitable for damp locations. ENERGY STAR® certified.

WARRANTY

5-year limited warranty. Complete warranty terms located at:

www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

NOTE: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25°C. Specifications subject to change without notice.

LED Garage Light







Plug in to link multiple fixtures.

Specifications

Width: 10-7/16 (26.4) Length: 24-7/16 (62.1) Depth: 3-1/2 (8.9) Weight: 5 (2.3)

10-7/16" (26.4cm)

 \oslash

All dimensions are inches (centimeters) unless otherwise indicated.

ORDERING INFORMATION For shortest lead times, configure product using bolded options . Example: SGLL 24 40K 80Cl											
SGLL		24			PIR						
Series		Length		Color temperature / CRI	Controls						
SGLL	LED garage light	24	24"	40K 80CRI 40K 90CRI ¹	PIR	Passive infrared sensor					

24-7/16" (62 1cm)

Accessories: Order as separate catalog number.

SGLL 24IN LINKABLE CORD BL 18" Black linking cord

Catalog Number Notes

Туре

LIGHTING FACTS

Lighting facts	Lithonia Lighting
Light Output (Lumens)	5000
Watts	80
Lumens per Watt (Efficacy)	62.5
Color Accuracy Color Rendering Index (CRI)	85
Light Color Correlated Color Temperature (CCT) 4000 (Bi	right White)
Warm White Bright White 2700K 3000K 4500K	Daylight 6500K
All results are according to IESNA LM-79-2008: Approved Metho Photometric Testing of Solid-State Lighting. The U.S. Department product test data and results.	
Visit www.lightingfacts.com for the Label Ref	ierence Guide.
Registration Number: NJSM-QZXW2H (2/4/2016)	
Registration Number: NJSM-QZXW2H (2/4/2016) Model Number: SGLL 24 80CRI 40K	

PHOTOMETRICS

Full photometric data report available within 2 weeks from request. Consult factory.

SGLL 24IN 40K 80CRI PIR, 5299 delivered lumens, test no. ISF 32052, tested in accordance to IESNA-LM79.

18 <u>0°</u>	_						~		ents d									
	7																	
	90°				pf				2	20%								
	190	CP Summary			рс	80%			70%		50%		Zonal Lumen Summary					
	80°		0°	90	pw	70%	50%	30%	50%	30%	10%	50%	30%	10%	Zone	Lumens	% Lamp	% Fixture
300		0°	1923	1923	0	119	119	119	116	116	116	110	110	110	0° - 30°	1471	27.8	27.8
HH X -	A	5°	1906	1915	1	108	103	99	101	97	93	96	93	90	0° - 40°	2379	44.9	44.9
600	60°	15°	1839	1821	2	98	90	83	88	82	76	84	79	74	0° - 60°	4104	77.5	77.5
	700	25°	1695	1659	3	90	79	71	77	70	64	74	68	62	0° - 90°	5230	98.7	98.7
900		35°	1477	1425	4 ش	82	70	61	69	61	54	66	59	53	90° - 120°	65	1.2	1.2
1200	۲	45°	1227	1156	<u>ک</u>	76	63	54	62	53	47	59	52	46	90° - 130°	67	1.3	1.3
		55°	950	863	6 6	70	57	48	56	47	41	54	46	40	90° - 150°	67	1.3	1.3
1500		65°	649	580	7	65	51	43	50	42	36	49	41	36	90° - 180°	68	1.3	1.3
	\40°	75°	352	355	8	60	47	38	46	38	32	45	37	32	0° - 180°	5297	100.0	100.0
1800		85°	82	192	9	56	43	35	42	35	29	41	34	29				
0° 20°		90	9	131	10	53	40	32	39	32	27	38	31	26				
 0° 90°																		

