




LED Linear Lights

STANDARD's flexible LED linear lights are designed to add ambiance and character to any setting. Delivering even, brilliant light, the colour changing RGB, cool white and warm white colours can be used in a multitude of applications, both indoor and outdoor, ranging from under cabinets to cove and perimeter applications.



RGB



Cool White



Warm White

Linear Decorative

LED Low Voltage Tape Light Kit

- ▶ Using high quality 5050 SMD LEDs, the tape light can be cut at every 3.94" (10 cm)
- ▶ Silicon cover doesn't yellow over time
- ▶ 3M adhesive backing for solid, easy installation on many surfaces
- ▶ Quick, easy installation - plug and play no wiring needed
- ▶ Don't waste cut pieces - separate power supplies available
- ▶ Quick connectors to rejoin various lengths and work around corners

Kit includes

- ▶ Tape light
- ▶ 1 power supply
- ▶ Remote control (for RGB kit only)
- ▶ RGB controller (for RGB kit only)

Order code	Description	Watts ¹ (W)	Volts (VDC)	Colour	Average life (hrs)	Lumen output per foot	LED per foot	Length (ft) (m)	IP rating	Dimmable (Yes/No)	Case qty
------------	-------------	---------------------------	----------------	--------	-----------------------	--------------------------	-----------------	-----------------------	--------------	----------------------	-------------

Low Voltage Tape Light Kit

61953	LED/TAPE/16.4/5050/RGB KIT/12V/50M/STD	27	12	RGB	50 000	-	9	16.4	5	64	Y	20
61954	LED/TAPE/16.4/5050/WW KIT/12V/50M/STD	28	12	Warm white	50 000	145	9	16.4	5	64	N	20
61955	LED/TAPE/16.4/5050/CW KIT/12V/50M/STD	28	12	Cool white	50 000	145	9	16.4	5	64	N	20

Power Supply

Length : 3 3/4 in. (95 mm) Width : 1 1/8 in. (43 mm) Height : 3/16 in. (30 mm)

62265	LED/TAPE/WW+CW/PS/STD	-	12	White	-	-	-	6.56	2	-	-	50
62266	LED/TAPE/RGB/PS/STD	-	12	White	-	-	-	6.56	2	-	-	50

Accessories

61956	LED/TAPE/RGB/CONNECTOR/STD	-	-	-	-	-	-	0.56	0.17	-	-	10
61957	LED/TAPE/WW+CW/CONNECTOR/STD	-	-	-	-	-	-	0.56	0.17	-	-	10
62017	LED/10PCS TAPE LIGHT 12V MOUNTING CLIPS	-	-	-	-	-	-	-	-	-	-	100

NOTE: To avoid decreases in light levels, avoid connecting more 16.4' (5 m) at a time.
¹ Watts for 16.4' (5 m)

