JUNO°

TRAC-LITES

| Project: | ——— One Circuit Trac System |
|----------------|--------------------------------|
| Fixture Type: | TRAC SECTIONS, JOINERS & FEEDS |
| Location: | |
| Contact/Phone: | R2, R4, R6, and R8 |

PRODUCT DESCRIPTION

Reduced-profile, single-circuit trac sections for surface or pendant mounting. Compatible with a full range of feed, connector and mounting accessories, as listed on back of this page. Accepts all Trac-Lites and Trac-Master trac fixtures.

PRODUCT SPECIFICATIONS

Construction Extruded aluminum with thermoplastic insulator

- Injection molded polycarbonate dead-end with set screw
- Standard lengths may be cut-to-length by installer.

Electrical Two 12 gauge solid copper conductors • Rated 20 amps at 120 volts • Aluminum channel used as system ground

• One-piece insulator insures consistent conductor spacing for reliable electrical contact • Insulating bushings supplied at mounting hole locations to prevent shorts to ground.

Labels UL/CUL listed.


PRODUCT INSTALLATION


Debossed polarity line provides visual cue to proper trac, trac connector and fixture alignment • Supplied with toggle bolts for surface mounting • Insulator stays same length as extrusion to simplify field-cutting of trac • Connectors and feeds simply push into trac sections.

Product specifications subject to change without notice.

DIMENSIONS







PRODUCT CODES

| Catalog Number | Description | Actual Length | Finish |
|----------------|-----------------|---------------------|---------|
| R2WH | 2' Trac Section | 19 7/8" | White |
| R2BL | 2' Trac Section | 19 7/8" | Black |
| R2SL | 2' Trac Section | 19 7/8" | Silver |
| R2NA | 2' Trac Section | 19 7/8" | Natural |
| R2BZ | 2' Trac Section | 19 7/8" | Bronze |
| R4WH | 4' Trac Section | 43 7/8" | White |
| R4BL | 4' Trac Section | 43 7/8" | Black |
| R4SL | 4' Trac Section | 43 7/8" | Silver |
| R4NA | 4' Trac Section | 43 7/8" | Natural |
| R4BZ | 4' Trac Section | 43 7/8" | Bronze |
| R6WH | 6' Trac Section | 67 7/8" | White |
| R6BL | 6' Trac Section | 67 7/8" | Black |
| R6SL | 6' Trac Section | 67 7/8" | Silver |
| R6NA | 6' Trac Section | 67 7/8" | Natural |
| R6BZ | 6' Trac Section | 67 7/8" | Bronze |
| R8WH | 8' Trac Section | 91 7/8" | White |
| R8BL | 8' Trac Section | 91 ⁷ /8" | Black |
| R8SL | 8' Trac Section | 91 ⁷ /8" | Silver |
| R8NA | 8' Trac Section | 91 ⁷ /8" | Natural |
| R8BZ | 8' Trac Section | 91 7/8" | Bronze |




TRAC-LITES

One Circuit Trac System

TRAC SECTIONS, JOINERS & FEEDS

R2, R4, R6, and R8

Electrical End Feeds











R21WH, R21BL, R21SL, R21BZ

End Feed Connector and Outlet Box Cover. For outlet box feed. Includes: outlet box cover, fixture strap and around screw

R29WH, R29BL, R29SL, R29BZ

Floating Electrical Feed. Permits mounting any point of trac under outlet box. Includes floating connector, outlet box cover plus extra trac dead end.

R34WH, R34BL, R34SL, R34BZ

Conduit Feed. For surface wiring. Use standard 1/2"

R36WH, R36BL, R36SL, R36BZ

T-Bar End Feed. Wiring compartment contains standard 1/2" KO's. Feeds surface trac from above, when T-bar is directly above trac.

R38WH, R38BL, R38SL, R38BZ

Live End Feed Connector. Feed trac from above with flexible conduit, BX, etc., or end feed in pendant systems. Accepts standard 1/2" connector.

R22WH, R22BL, R22SL, R22BZ

Cord and Plug Connector. Comes with 15' two-wire white cord. Includes surface wire retainers and in-line switch. Max cap. 7 amps.

R122WH, R122BL, R122SL, R122BZ

Same as above but with matching color 3-wire grounded cord and plug. No switch.

Trac Joiners



R23WH, R23BL, R23SL, R23BZ

Miniature Straight Connector. Joins two trac sections end to end

R20WH, R20BL,

Accordion Adjustable Joiner.

Can flex to 90° angle to left,

right, up or down. Joins two

R2OSL, R2OBZ

‡ R24WH, R24BL, R24SL, R24BZ

Adjustable Connector. Joins two trac sections to make a 90° angle or straight run. Straight and right angle covers supplied. For outlet box feed, No. T27 cover plate required.



2 1/16"

‡ R25WH, R25BL, R25SL, R25BZ

"T" Connector. Joins three trac sections. For outlet box feed, No. T27 cover plate required.



T27WH, T27BL, T27SL, T27BZ Outlet Box Cover. Use with Nos. **R24/R25** for

outlet box electrical feed. Includes: nipple, locknut and around screw.



R49WH, R49BL, R49SL, R49BZ


Trac Continuation Kit. Permits trac to continue a run around obstructions. Includes one left and one right R34 Conduit Feed. Fits standard 1/2" conduit.



R28WH, R28BL, **R28SL, R28BZ**

Trac Dead End. For use with field-cut trac sections

Pendant Stems



T90-12, T90-18, T90-24, T90-36, T90-48

T-Bar Pendant Stem Kit (12", 18", 24", 36", 48") - Use two for 2', 4', 6' of trac or three for 8' of trac. For electrical feed, order T93 wireway cover. WH, BL, SL, BZ

T91-12, T91-18, T91-24, T91-36, T91-48

Rigid Ceiling Pendant Stem Kit (12", 18", 24", 36", 48") -Use two for 2', 4', 6' of trac or three for 8' of trac. For electrical feed, order T93 wireway cover. WH, BL, SL, BZ

T93WH, T93BL, T93SL, T93BZ

Wireway Cover for Pendant Stem Kits T90 and T91. Conceals electrical feed wires from stem to connector. One cover required for each trac feed.



T94WH, T94BL, T94SL, T94BZ

Sloped Ceiling Adapter. Allows T90 or T91 pendant to hang straight down from sloped ceilings. Can be used to feed electrical wires to Trac at up to 60° anale.



T96WH, T96BL, T96SL, T96BZ

Pendant Stem Threaded Coupling. Enables multiple pendant stems to be joined for higher ceiling applications.



T56WH, T56BL, T56SL, T56BZ

Solid Rod Pendant Mounting Kit. Attaches solid 5/16" threaded rod to Trac. Includes: plastic cap, mounting bracket and hardware. Rod not supplied.

Accessories




R37F

15/16" T-bar Attachment Clip. To attach to inverted tee ceilings using flush tiles. Use two for 2' or 4' trac and three for 6' or 8' trac. R37D

Same as above with spacer for

three for 6' or 8' trac.

ceilings using drop tiles. R37-9-16 9/16" T-bar Attachment Clip. To attach Trac-Lites trac to inverted tee ceilinas usina flush or drop



T31WH, T31BL, T31SL

Pendant Adapter. Adapts swag or chain-hung fixture to trac. Supports up to 25 lbs. Not UL Listed.



T32WH, T32BL, T32SL Plant or Utility Hook. Supports up to

25 lbs. Not UL Listed.

T33WH, T33BL, T33SL Outlet Adapter. Provides electrical receptacle. Not UL Listed.

Product specifications subject to change without notice.

‡ R24 and R25 may not be used as feed connectors in Canada due to special grounding requirements.

