

Miniature - Miniatures



Fig.70




Fig.68



Fig.62



Fig.63



Fig.64

Line Ligne	Lamp Shape Forme lampe	Volts Tension	Amps (A) Watts Puiss. (W)	Lamp Base Culot Lampe	Internal Code Interne	Filament	Couleur Couleur	Avg. Life (Hrs) Vie moy. (Hres)	Lumens	MSCP	L.C.L. Inches - (mm) H.C.L. Pouces - (mm)	M.O.L. Inches - (mm) L.H.T.M. Pouces - (mm)	Diam. inches (mm) Pouces (mm)	Fig. # N° Fig.
---------------	---------------------------------	------------------	---------------------------------	--------------------------------	-----------------------------	----------	--------------------	--	--------	------	--	--	-------------------------------------	-------------------------

T-3 1/4 Bulb Lampe T-3 1/4

498	T-3 1/4	14	0.24A	W2.1x9.5d Wedge / Poussoir	158	C-2V		500	2		9/16 (14.3)	1 1/16 (27)	13/32 (10.3)	70
499	T-3 1/4	14	0.24A	W2.1x9.5d Wedge / Poussoir	158A	C-2V	Amber Ambré	500	2		9/16 (14.3)	1 1/16 (27)	13/32 (10.3)	70
500	T-3 1/4	14	0.27A	W2.1x9.5d Wedge / Poussoir	194	C-2F		2500	2		9/16 (14.3)	1 1/16 (27)	13/32 (10.3)	70
501	T-3 1/4	14	0.27A	W2.1x9.5d Wedge / Poussoir	194A	C-2F	Amber Ambré	2500			1/2 (12.7)	1 1/16 (27)	13/32 (10.3)	70
502	T-3 1/4	14	0.33A	W2.1x9.5d Wedge / Poussoir	193	C-2F			2		9/16 (14.3)	1 1/16 (27)	13/32 (10.3)	70
503	T-3 1/4	14	0.35A	W2.1x9.5d Wedge / Poussoir	168	C-2F		1500	3		9/16 (14.3)	1 1/16 (27)	13/32 (10.3)	70
504	T-3 1/4	24	2W	W2.1x9.5d Wedge / Poussoir	2840	C-2F		5000	0,48		9/16 (14.3)	1 1/16 (27)	13/32 (10.3)	70
505	T-3 1/4	24	3W	W2.1x9.5d Wedge / Poussoir	2841	C-2F		3000	1,6		9/16 (14.3)	1 1/16 (27)	13/32 (10.3)	70
506	T-3 1/4	12.8	2.1A	Axial Plast.	890	C-6		300	43		1 (25.4)	2 17/25 (60.5)	13/32 (10.3)	68
507	T-3 1/4	2	0.06A	BA9s	1809	C-6		1000	0,02		3/4 (19)	1 3/16 (30)	13/32 (10.3)	62
508	T-3 1/4	2	0.06A	BA9s	49	S-2		1000	0,04			1 3/16 (30)	13/32 (10.3)	62
509	T-3 1/4	2.5	0.3A	BA9s	1436	C-2R		1000	0,3		5/8 (15.9)	1 3/16 (30)	13/32 (10.3)	62
510	T-3 1/4	2.5	0.5A	BA9s	43	C-2R		3000	0,5		25/32 (19.8)	1 3/16 (30)	13/32 (10.3)	62
511	T-3 1/4	2.9	0.17A	BA9s	291	C-2R		200	0,27		3/4 (19)	1 3/16 (30)	13/32 (10.3)	62
512	T-3 1/4	3.2	0.16A	BA9s	1490	C-2R		3000	0,2		25/32 (19.8)	1 3/16 (30)	13/32 (10.3)	62
513	T-3 1/4	3.2	0.35A	BA9s	45	C-2R		3000	0,5		25/32 (19.8)	1 3/16 (30)	13/32 (10.3)	62
514	T-3 1/4	4	0.06A	BA9s	1804	S-2		1000	0,07			1 3/16 (30)	13/32 (10.3)	62
515	T-3 1/4	4	0.06A	BA9s	1867	C-6		2000	0,06		3/4 (19)	1 3/16 (30)	13/32 (10.3)	62
516	T-3 1/4	5	0.07A	BA9s	1906	C-6		1000	0,19		5/8 (15.9)	1 3/16 (30)	13/32 (10.3)	62
517	T-3 1/4	5	0.09A	BA9s	1850	C-2R		1500	0,25		5/8 (15.9)	1 3/16 (30)	13/32 (10.3)	62
518	T-3 1/4	6	0.7	BA9s	316	C-2R		500		3.4	5/8 (15.9)	1 3/16 (30)	13/32 (10.3)	62
519	T-3 1/4	6	2W	BA9s	3895	C-2R		3000			0.551 (14)	0.984 (25)	13/32 (10.3)	62
520	T-3 1/4	6.3	0.042A	BA9s	1302	C-6		5000	0,08		3/4 (19)	1 3/16 (30)	13/32 (10.3)	62
521	T-3 1/4	6.3	0.15A	BA9s	755	C-2R		20000	0,33		25/32 (19.8)	1 3/16 (30)	13/32 (10.3)	62
522	T-3 1/4	6.3	0.15A	BA9s	267	C-2R Bi-Metal		5000	0,33		5/8 (15.9)	1 3/16 (30)	13/32 (10.3)	63
523	T-3 1/4	6.3	0.15A	BA9s	1830	C-2R	Black End Bout noir	3000	0,38		25/32 (19.8)	1 3/16 (30)	13/32 (10.3)	64
524	T-3 1/4	6.3	0.15A	BA9s	1847	C-2R		5000	0,38		25/32 (19.8)	1 3/16 (30)	13/32 (10.3)	62