

Catalog Number	
Notes	Type

FEATURES & SPECIFICATIONS

INTENDED USE

For use with frame-in LP6 and housings LI6 and LI6F.

CONSTRUCTION

Aluminum white polyester powder coat painted.

One piece reflector.

White integral flange as standard.

Adjustable socket plate allows lamp to align perpendicular to the floor.

Accommodates ceiling pitch ranging from 2/12 to 12/12.

INSTALLATION

Socket to trim interface.

Rough-ins with clips retain trims.

LISTING

U.L. Listed to U.S. and Canadian safety standards.


Damp location listed.

Patent # 5,452,193.

6" Full Reflector Trim


6S01

SLOPED OPEN
Narrow Flange



Specifications

Height: 7-1/4 (18.4)
Lamp opening: 6-1/4 (15.9)
Diameter: 8-1/4 (20.9)
Trim height when used with
Non-IC incandescent rough-in




All dimensions are inches (centimeters).

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: **6S01**



Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
<i>IC</i>	Incandescent	100 PAR38	LI6
		75 PAR30	LI6
		65 BR40	LI6
		65 BR30	LI6
		Fluorescent	32 TRT
<i>Non-IC</i>	Incandescent	150 PAR38	LP6
		75 PAR30	LP6
		120 BR40	LP6
		65 BR30	LP6
		100 A19	LP6

6S01 6" Sloped Open Full Reflector Trim

For photometric data consult factory.

Consult chart on page LAMP for appropriate R or PAR lamp data.