

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L7X, L7XR, LC6, L7XF and L7XFR.

CONSTRUCTION

Aluminum one piece reflector.

Polyester powder coat paint.

All finishes, excluding PF option, have integral flange.

INSTALLATION

Socket to trim interface.

Trim retention is achieved by utilizing two side-mounted torsion springs on the trim and two receiving brackets in the can, ensuring a consistently tight fit with the ceiling.

LISTINGS


U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

NOTE: Specifications subject to change without notice.




6" Full Reflector Trim



7B2

BAFFLE Narrow Flange



Specifications

Height: 6 (15.2)

Lamp opening: 5-7/8 (14.9) Diameter: 7-5/8 (19.4)


Jiameter: 7-5/8 (19.4)

All dimensions are inches (centimeters) unless otherwise specified.

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold).**

Example: 7B2W TOR



TOR	
Mounting method	Options
TOR Torsion springs	PF Integral white plastic flange (separate flange) ¹

Housing Compatibility Housing and trim ordered separately. Application Source Maximum Housing wattage IC Incandescent L7X, L7XR, LC6 75 PAR30 65 BR30 L7X, L7XR, LC6 Fluorescent 13DTT L7XF, L7XFR 26TRT L7XF, L7XFR

NOTES:

1 PF is only available with 7B2W.

Downlighting and Track Sheet #: 7B2-TOR

7B2 6" Baffle Full Reflector Trim For BR and PAR reflector lamps, see lamp manufacturer's published raw lamp data for photometrics.