

Catalog Number	
Notes	Type

FEATURES & SPECIFICATIONS

INTENDED USE

For use with rough-in LP6 and housings LC6, LI6, L7X, L7XR, LI6F, L7XF and L7XFR.

CONSTRUCTION

Aluminum one-piece reflector.

White polyester powder coat paint.

Deep conical baffles available in black, white and brushed nickel.

Integral flange.

INSTALLATION

Socket to trim interface.

Retaining clips riveted to top of reflector hold trim inside housing.

Rough-ins with clips retain trims.

LISTING


UL Listed to U.S. and Canadian safety standards.

Damp location listed.

6" Full Reflector Trim

6B2

DEEP BAFFLE
Narrow Flange




Specifications

Height: 6-1/2" (16.5)

Lamp opening: 5-1/2" (14)

Diameter: 7-5/8" (19.4)

Trim height when used with
Non-IC incandescent rough-in



All dimensions are inches (centimeters).

ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

Example: 6B2

6B2	
Series	Finish
6B2	(blank) Black baffle W White baffle

Housing Compatibility

Housing and trim ordered separately.

Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR38	LC6, LI6, L7X, L7XR
		75 PAR30	LC6, LI6, L7X, L7XR
		65 BR30/BR40	LC6, LI6, L7X, L7XR
	Fluorescent	40 A19	LI6
		13DTT	L7XF
		26TRT/18DTT 32TRT	L7XF, LI6F LI6F
Non-IC	Incandescent	65 BR30	LP6
		100 A19	LP6
	Fluorescent	18DTT	L7XF, L7XFR
		18TRT	L7XF, L7XFR

6B2 6" Deep Baffle Full Reflector Trim

