



# Disconnect Terminals

## SAKR




## SAKR-D


With StB test points



## SAKC 4



## SAKC 10



Lever

Plug

Pull Pin

Pull Pin

### Terminal Block Selection Data

Available Options	Version	SAKR		SAKR-D		SAKC 4		SAKC 10	
With 2 StB test points KrS PA		0412260000	0183360000	0546460000*					
With 2 StB test points KrS Blue PA		0412280000	0183380000						
With 2 StB test points KrS without diode PA				0413160000*					
Beige PA		0412160000	0172160000	0412960000*		0299960000*			
Blue PA		0412180000	0172180000						
Without diode PA				0413060000**		0185760000**			
With diode PA				0263360000***		0299560000***			
Orange PA		1461960000							
KrG		0412120000				0340720000	0357520000	0324020000	
KrS								0324030000	
With 1 StB test point KrG								1404520000	
With 2 StB test points KrG		0412220000				0340620000	0357620000	0324120000	1404620000
With 2 StB test points KrS								0324130000	

### Dimensions

Width / Length / Height mm (in.)	for TS 32	for TS 35	SAKR	SAKR-D	SAKC 4	SAKC 10
	↶	↷	6.5/42/40.5 (.26/1.81/1.60)	6.5/42/57 (.26/1.81/2.24)	6.5/40/67 (.26/1.57/2.64)	12/65/70.5 (.47/2.56/2.76)
Insulation stripping length			mm (in.)	8 (.31)	12 (.47)	12 (.47)

### Technical Data

Rated voltage / rated current / wire size	UL	SAKR	SAKR-D	SAKC 4	SAKC 10
		300 V / 10 A / #22...12 AWG	300 V / 10 A / #22...12 AWG	300 V / 25 A / #22...12 AWG	600 V / 25 A / #22...8 AWG
	CSA	300 V / 10 A / #26...12 AWG	300 V / 10 A / #22...12 AWG	300 V / 25 A / #22...10 AWG	600 V / 25 A / #20...10 AWG
	VDE	380 VAC / 10 A / 4 mm <sup>2</sup>	380 VAC / 10 A / 4 mm <sup>2</sup>	380 VAC / 25 A / 4 mm <sup>2</sup>	500 VAC / 27 A / 10 mm <sup>2</sup>
Torque	Nm (lb. in.)	0.6 / 0.5 StB (8.0 / 4.5 StB)		0.6 / 0.5 StB (7.0 / 4.5 StB)	
Clamping screw	M	3		4	

### Selected Accessory Data<sup>‡</sup>

End Plate (thickness mm)	Type	Part No.	Type	Part No.	Type	Part No.	Type	Part No.
Beige PA	AP (1.5)	0211360000	AP (1.5)	0211360000				
Blue PA	AP (1.5)	0211380000						
KrG	AP (1.5)	0211320000			AP (1.5)	0117920000	AP (3.0)	0146720000
KrS							AP (3.0)	0146730000
Partition (thickness mm)								
PA					TW (1.5)	0130160000	TW (1.5)	0242960000
KrG							TW (3.0)	0242920000
KrS							TW (3.0)	0242930000
HP	TW (1.0)	↶ 0297100000	TW (1.0)	↶ 0297100000	TW (1.0)	↶ 0297100000		

### Jumpers



Final number indicates number of poles. See the Accessories Section for more information. When using QB, maximum conductor connection is 2.5 mm<sup>2</sup>.

QB

Connection sleeve  
Fixing screw  
Lock washer  
Insulation sleeve

QB	Part No.	QB	Part No.	QB	Part No.	QL	Part No.
QB 2	0482700000	QB 2	0482700000	QB 2	0482700000	QL 2	0135500000
QB 3	0482800000	QB 3	0482800000	QB 3	0482800000	QL 3	0135600000
QB 4	0482900000	QB 4	0482900000	QB 4	0482900000	QL 4	0135700000
QB 25 bare*	0134000000	QB 25 bare*	0134000000	QB 25 bare*	0134000000	QL 10	0338500000
						VH 14	0299700000
						BS M 4 x 20	0362800000
						SS M 4	0136400000

### Plugs



BST 4

BST 4

Lock-out device

Test plug

Dummy plug

Socket

Diode plug without diode

Diode plug with diode 1N4007

Disconnecter plug (spare)

WTR/SAKR	Part No.	PS 2.3	Part No.	PS 2.3	Part No.	PS 4	Part No.
WTR/SAKR	9525900000	PS 2.3	0180400000	PS 2.3	0180400000	PS 4	0299600000
						StB 13.5	0135200000
		DLS 2	0321060000				
		DLS 2	0630160000				
				TST	1380600000	TST	0462700000

### Extraction Tool

0623060000

### Marking Tags

Print

Note: Part numbers are shown for a single card of pre-printed tags numbered 1-50.

Consecutive horizontal

Consecutive vertical

DEK 5/6.5	Part No.	DEK 5/6.5	Part No.	DEK 5/6.5	Part No.	DEK 5/6	Part No.
DEK 5/6.5	0468160001	DEK 5/6.5	0468160001	DEK 5/6.5	0468160001	DEK 5/6	0468660001
DEK 5/6.5	0468260001	DEK 5/6.5	0468260001	DEK 5/6.5	0468260001	DEK 5/6	0468760001

<sup>‡</sup>See Accessories section for additional information.

\*Without DLS

\*\*With empty DLS

\*\*\*With DLS 1N4007 (Diode)