

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L7X, L7XR, LC6, L7XF and L7XFR.

CONSTRUCTION

Aluminum one piece reflector.

Polyester powder coat paint.

Anodized finishes have white integral flange ring as standard.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTING

U.L. Listed to U.S. and Canadian safety standards.



Damp location listed.

Catalog Number	
Notes	Type

6" Full Reflector Trim

702

OPEN
Narrow Flange



Specifications

Height: 6-1/8 (15.6)

Lamp opening: 5-7/8 (14.9)

Diameter: 7-5/8 (19.4)

All dimensions are inches (centimeters).

ORDERING INFORMATION

Lead times will vary depending on options selected. Consult with your sales representative.

Example: **702A**

702A	
Series	Finish ¹
702	A Clear diffuse AZ Clear specular

NOTES:

1 See 702-TOR specification sheet for white finish.

Housing Compatibility

Housing and trim ordered separately.			
Application	Source	Maximum wattage	Housing
IC	Incandescent	75 PAR30	L7X, L7XR, LC6
		65 BR30	L7X, L7XR, LC6
	Fluorescent	13DTT	L7XF, L7XFR
		26TRT	L7XF, L7XFR

