

Switch



Cover plate provided by contractor



Chelsea *Digital* Switch[™]

Description: The Chelsea DigitalSwitch is a 100% digital switch which connects directly to the GR 2400 bus via Cat. 5 patch cable with RJ45 connectors. Chelsea DigitalSwitches can be ordered with 1, 2, 3, 4 or 6 buttons per gang and can be mounted in any standard 2.25" deep switch box with a decorator style switch plate. All Chelsea DigitalSwitches are 100% backwards compatible with all LC&D systems.

Features:

- · May be programmed to control any relay, **SmartBreaker**™ or dimmer in any panel
- · Custom button engraving at no cost (2 lines 8 character/line)
- · All push buttons are annunciated with a pilot light
- · Available as a Waterproof option

Advanced **Programming** Features:

- A programmable green "Locator Light" at the top of each unit is always on, can be programmed to blink to show Horn Driver Mode or help locate a switch
- Programmable Status LED logic
- · Adjustable debounce time to avoid accidental trigger

- · Factory preprogrammed. May be reprogrammed in the field using the DTC (Digital Time Clock)
- Link up to 127 digital addresses via Cat. 5 patch cable with RJ45 connectors
- · Can be enabled/disabled by optional KeyEnable[™] switch
- · Audible beep alert for warning or switch locating
- Alternate button programming to allow more flexibility of use, for example the same button can perform a different task at different times of the day
- · Capable of being digitally enabled/disabled over the bus on a per button or per switch basis

Specifications:

Mounting:

Addresses available:

1.3" w x 4" h x 1.3" d Dimensions: Programming: Via DTC

10-90% non-condensing (100% rain Switch plate: Decorator style Humidity:

proof - Waterproof option only)

32-104° F (0-40° C) Ambient temperature: (Waterproof bell box - Waterproof option only Power supply: Powered from GR 2400 bus

1-119 Two RJ45 connectors Bus connector:

Address per switch: Bus termination: Manual end-of-line termination with

jumper

Function: ON, OFF, Mixed, Group Control,

Toggle, Scene Control

2.25" deep-switch box

Ordering Information

Chelsea *DigitalSwitches*™ are available in 1, 2, 3, 4 or 6 buttons. Center plates are available in white, ivory and brushed stainless steel. Indicator light is red and locator light is green.











Waterproof Chelsea DigitalSwitch™



Note: Sealed Switch is provided with a 10ft standard Cat. 5 connection cable and may be cut to a more convenient length.

ORDERING INFORMATION

Number of Buttons	Single/Multicolor	Multicolor Button Colors			Plate Colors
CH1 = 1 button Chelsea CH2 = 2 button Chelsea CH3 = 3 button Chelsea CH4 = 4 button Chelsea CH6 = 6 button Chelsea When ordering Waterproof Chelsea, add WP to the ordering nomenclature. Example: CH1 WP, CH2 WP, CH3 WP, CH4 WP, CH6 WP	BWH = All buttons white BIV = All buttons ivory BAL = All buttons almond BGY = All buttons gray BBK = All buttons black BRD = All buttons red BGR = All buttons green BBU = All buttons blue BYL = All buttons yellow BOR = All buttons orange MC = Multicolored buttons (please select quantities from the multicolor button section)	Button Quantity 1B = 1 button 2B = 2 buttons 3B = 3 buttons 4B = 4 buttons 6B = 6 buttons	Color WH = White IV = Ivory GY = Gray BK = Black RD = Red GR = Green BU = Blue YL = Yellow OR = Orange	Multicolor Examples: CH6 MC 2BWH 4BBK PST 6 button Chelsea with 2 white and 4 black buttons and a stainless steel faceplate CH4 MC 2BBU 1BGR 1BYL PWH 4 button Chelsea with 2 blue, 1 green, and 1 yellow button and a white faceplate Button Quantity represents the number of buttons on a switch that will be in the selected color—number may not exceed total number of buttons on switch - total of all button color quantities must equal total number of buttons on switch (refer to examples).	PWH = White plate PIV = Ivory plate PST = Stainless steel plat PBK = Black plate PAL = Almond plate