

FEATURES & SPECIFICATIONS

INTENDED USE — RT5 is designed for applications that require the extremely energy efficient delivery of comfortable volumetric light from a lay-in fixture that is appealing and shallow in depth. Ideal for offices, schools, hospitals, retail and numerous other commercial applications. **Certain airborne contaminants can diminish integrity of acrylic. Click here for Acrylic Environmental Compatibility table for suitable uses.**

CONSTRUCTION — Impact modified acrylic prismatic refractor with polymer light-diffusing film.

Rugged, one-piece, cold-rolled steel reflector with embossed facets. Polyester powder paint after fabrication. Rigid structure with ballast box and endplates with integral T-bar clips.

Fixtures may be mounted end-to-end.

OPTICS — Delivers volumetric lighting by filling the entire volume of space with light, delivering the ideal amount to walls, cubicles, work surfaces and people.

Luminous characteristics are carefully managed at high angles, providing just enough intensity to deliver the volumetric effect.

Regressed, two-piece refractive system obscures and softens the lamp and smoothly washes the reflector with light.

Linear faceted reflector softens and distributes light into the space and minimizes the luminance ratio between the fixture and the ceiling.

Mechanical cut-off across the reflector and fresnel refraction along the refractor provide high angle shielding and a quiet ceiling

Sloped endplates provide a balanced fixture to ceiling ratio while enhancing the perception of fixture depth. **ELECTRICAL** — Highly efficient program-start electronic ballasts, Class P, thermally protected, resetting, HPF, non-PCB, UL Listed, CSA Certified, sound rated A. Your choice of Premium or Premium XPT5 lamp with enhanced phosphors and 85 CRI. Ballast/lamp efficacy up to 100+ LPW. Lamp is TCLP compliant.

0.90 or 0.95 ballast factor standard for typical applications. 1.15 ballast factor or F54T5H0 lamping available for higher ceiling height applications.

Step-level dimming option allows system to be switched to 50% power for compliance with common energy codes while maintaining fixture appearance.

S5 option available for use with SIMPLY5™ Lighting Intelligence system with multi-level dimming. See SYNERGY Lighting Controls specification sheets for more information. Ballast Disconnect provided standard where required to comply with U.S. and Canadian electrical codes.

INSTALLATION — Side mounted ballast tray accessed by removing adjacent ceiling tile. Ballast tray may be removed from fixture during service.


 $Lamps\ accessed\ by\ squeezing\ refractor\ to\ release\ from\ retention\ tabs.$

LISTING — UL Listed (standard). Optional: Canada CSA or cUL. Mexico NOM.

WARRANTY — 1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx.







All dimensions are inches (centimeters) unless otherwise specified.

Protected by one or more of US Patents Nos. 7,229,192; D541,467; D541,468; D544,633; D544,634; D544,992; D544,933 and additional patent pending.

Note: Specifications subject to change without notice.

ORDERINGINFORMATION

For shortest lead times, configure products using **bolded options**.

Example: 2RT5 28T5 MVOLT GEB95 LPM835P


2RT5								
Series	Lamp type	Voltage	Ballast		Lamp ⁷		Options	
2RT5 Recessed T5	28T5 28WT5 (46") 54T5H0 54WT5 (46")¹	MVOLT ² 347 ³	GEB95 GEB95S GEB115 GEB115S GEB10PS S5 GEB80 GEB80S GEB80S GEB90 GEB90S	.95 ballast factor ⁴ .95 ballast factor, step dimming ⁴ 1.15 ballast factor ⁴ 1.15 ballast factor, step dimming ⁴ 1.0 ballast factor, programmed start ⁵ .95 ballast factor SIMPLY5™ system ⁶ .80 ballast factor ⁵ .80 ballast factor, step dimming ⁵ .90 ballast factor ⁴ .90 ballast factor, step dimming ⁴	LPM835P LPM830P LPM841P L835XP L830XP L841XP LP835 LP830 LP841	Premier 3500° K lamp ⁴ Premier 3000° K lamp ⁴ Premier 4100° K lamp ⁴ Premier XP 3500° K lamp ⁴ Premier XP 3000° K lamp ⁴ Premier XP 4100° K lamp ⁴ 3500° K lamp ⁵ 3000° K lamp ⁵ 4100° K lamp ⁵	GLR PWS1836 PWS1846 EL14 EL65 HW	18-gauge, 3-wire (n/a with step dimming) ⁹

Notes

- For T5HO applications, use GEB10PS, GEB80 or GEB80S ballast. Not available with 28T5.
- 2 MVOLT (120-277 volts), 50-60HZ.
- 3 For 347V, use GEB95, GEB95S or GEB10PS.
- 4 28T5 only.
- 5 54T5H0 only.
- 6 SIMPLY5 includes 13' S5 SSC RELOC® wiring system, specify
- voltage unless HW (hardwire) or PWS is ordered.
- 7 Required. All fixtures shipped with lamps installed.
- 8 Must specify voltage, 120 or 277.
- 9 For use with standard ballast.
- 10 For use with step dimming ballast.
- 11 See $\underline{\text{PS1400QD}}$ spec sheet for EL lumen output information.

FLUORESCENT 2RT5-2X4

2RT5 28T5 GEB95 LPM835P, (2) FP28/835/PM/ECO lamps, 2730 lumens per lamp, s/m 1.2 (along) 1.3 (across), test no. LTL13260



*The LER (Luminaire Efficacy Rating) is the lumens per watt rating for this fixture. It is used to compare the energy efficiency of various products. This photometric report is based upon IES testing procedures, as stated in LM-41-1998. The reported lumen rating is based upon lamp manufacturer's published lumen output for the cold spot temperature measured during lamp calibration.

Ballast	Input Wattage 120/277
GEB90 GEB90S	55/54
GEB90S @50% power mode	27
GEB95 GEB95S	60/58
GEB95S @50% power mode	28/28
GEB115 GEB115S	73/71
GEB115S @50% power mode	35/35
GEB80 GEB80S	96/93
GEB80S @50% power mode	52/51
S5	60/58

T5/T8 Energy Comparison

System	Lamp Type	Ballast Factor	Input Watts	Watts Saved Compared to T8
3-lamp T8	F32T8	0.88	88	-
2RT5 2-lamp T5	F28T5XP	0.90	54	34
2RT5 2-lamp T5	F28T5	0.95	58	30
2RT5 2-lamp T5	F28T5	1.15	71	17