



Shown actual size: Maestro Wireless dimmer and 1-gang Claro wallplate in White (WH), with a Pico wireless control in White/Gray (WG).

Shown actual size: Pico wireless control in White/Gray (WG), W: 1.25 in (31.75 mm) x H: 2.625 in (66.68 mm) x D: .33 in (8 mm).

### **Product family features**

- Uses Lutron's Clear Connect™ Radio Frequency (RF) Technology which provides reliable RF communication
- Typical range of Pico™ wireless control is 100 ft line-of-sight, 30 ft through walls and floors
- · True multi-location dimming from every location
- · Tap on to favorite level; tap off; tap twice for full on
- · Touch rocker to adjust light level
- · Delayed off provides light as you exit the room
- Line frequency compensation maintains stable light levels, despite power line frequency and voltage variations
- Combine devices to create a system of up to ten wireless devices, dimmers, switches, sensors and/or wireless controllers
- · Mechanical air-gap to disconnect load power
- · 100% factory tested
- · Battery included with wireless controllers
- (7.6 mm) Coordinating Claro®, Satin Colors® and Stainless Steel profile wallplates only available separately
  - · Custom engraving available for wallplates, see pg. 155

#### **Control types**

Single-pole (one location)

Multi-location dimming (up to ten locations)

☐ Omage Wireless multi-location dimming (up to ten locations)

### **Direct load type compatibility**

Magnetic low-voltage lighting

□ Fluorescent lighting

LED lighting

## Load type requiring load interface

₩ Electronic low-voltage lighting

Lighting load interfaces may be applicable for some additional load type, voltage and capacity combinations.
For additional information, see pg. 174.

#### **Available finishes**

Use **BOLD** color code in model number (Example: MRF2-600M-**PD**) Gloss finishes\*



#### Satin finishes\*



<sup>\*</sup>Coordinating wallplates only available separately. For wallplate information, see pg. 160.

Stainless Steel wallplate includes black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls.

## Dimmers, switches and companion dimmers/switches

#### **Wireless dimmers**



- · Tap on to favorite level; tap off
- · Tap twice for full on
- Press, hold and release for delayed fade-to-off
- Touch rocker to adjust light level
- Provides true dimming from each location (with companion dimmers)

#### **Companion dimmers**



- For use with multi-location dimmers only, use up to nine companion dimmers with only one Maestro Wireless multi-location dimmer
- Provides true dimming from every location

#### Wireless switches



- Tap switch on/off
- For multi-location switching, use Maestro Wireless® switch with Maestro companion switches

#### **Companion switches**



 For use with multi-location switches only, use up to nine Maestro Wireless companion switches with one Maestro Wireless multi-location switch

#### Sensors and lamp dimmers

# Radio Powr Savr™ wireless occupancy/vacancy sensors



- Automatically turns lights on and/ or off based on space occupancy
- Uses Lutron's reliable Clear Connect™ Radio Frequency (RF) Technology
- Eliminates power pack and wiring expense
- Wall controls remain fully operable during automatic shut-off by sensor
- Battery included (10 year battery life)
- See pg. 144 for further details

### Radio Powr Savr<sub>TM</sub> wireless daylight sensors



- Automatically adjusts electric lighting levels based on amount of daylight entering a space
- Uses Lutron's reliable Clear Connect™ Radio Frequency (RF) Technology
- Battery included (10 year battery life)
- See pg. 146 for further details

#### Plug-in wireless table top lamp dimmers



- For use with table and floor lamps only
- Easy to install, requires no wiring or tools
- Cord is 6ft (1.8m) long

#### Plug-in wireless lamp and appliance modules



- Dimming module designed to control table and floor lamps
- Appliance module recommended for computers, printers, lamps and fans
- Cord is 2ft (0.61 m) long

#### Wireless controls and accessories

## Pico<sub>TM</sub> wireless controls (3-button with raise/lower)



- · Recalls favorite light levels for up to nine dimmers, plus on/off and adjust for fine tuning of light levels
- · "On," "Adjust," "Preset" and "Off" functions from a range of up to 100ft
- · Can be a wall-mount, tabletop, car visor or handheld control
- · Surface mount and car visor clip included
- Battery included (5 year battery life)

## **Pico wireless controls** (2-button with raise/lower)



- "On," "Raise/lower" and "Off" functions from a range of up to 100ft
- · Can be a wall-mount, tabletop, car visor or handheld control
- · Surface mount and car visor clip included
- Battery included (5 year battery life)

### Pico wireless controls (3-button)



- · "On," "Preset" and "Off" functions from a range of up to 100ft
- · Can be a wall-mount, tabletop, car visor or handheld control
- · Surface mount and car visor clip included
- Battery included (5 year battery life)

## Pico wireless controls (2-button)



- · Simplified all on and off buttons that are easy to understand
- · Can be a wall-mount, tabletop, car visor or handheld control
- · Surface mount and car visor clip included
- · Battery included (5 year battery life)

#### Available finishes

Use **BOLD** color code in model number (Example: MRF2-3BRL-**BL**)

For use with 3-button with raise/lower, 3-button, 2-button with raise/lower and 2-button models.

#### Gloss finishes



Gray

White/



WH White



Liaht Almond



AL Almond



I۷ Ivory



GR Grav



BR Brown



BL

Black

#### Wireless control accessories

#### **Wallplates**



- Use Claro® wallplates for a wall-mounted application, see pg. 160 for colors
- · Single, dual and multi-gang configurations available
- Surface mount at any location (no wallbox required)

#### **Pedestals**



- The pedestal is available in a single or dual configuration for using the Pico as a tabletop control
- Available in White (WH) or Black (BL)

### Single pedestal configuration







#### **Dual pedestal configuration**









#### **Connections overview**






## **Control types** (for 2 or more locations) Dim from multiple-locations (up to 10)




#### **Pico mounting options**



#### Dim from multiple-locations (up to 10)



#### Switch from multiple-locations (up to 10)



For more information on ballasts, visit www.lutron.com/ballasts. For more information on LED drivers, visit www.lutron.com/LED.

\*For illustration purposes only. Consult model number pages for specific voltage and capacity information.

#### **Dimmer model numbers**

## 

#### Digital fade dimmers<sup>†</sup>

Multi-location/single-pole

MRF2-600M-CC1

120V 600W

## 

## Magnetic low-voltage dimmers

#### Digital fade dimmer<sup>†</sup>

Multi-location/single-pole

MRF2-6MLV-CC1

120V 600W/VA

#### Digital fade dimmers—specification grade

Multi-location/single-pole\*† MRF2-6ND-120-CC1 120V 600W/VA

Multi-location/single-pole<sup>†</sup> MRF2-10D-120-CC1 120 V 1000 W/VA

The stated W (Watt) rating is the maximum incandescent lamp load. Ratings for MLV loads represent the maximum of the total lamp wattage plus MLV transformer loss (typically 20%).

#### □ 3-wire fluorescent dimmers\*

#### Digital fade dimmer

MRF2-F6AN-DV-CC1 Multi-location/single-pole 120/277V 6A

For use with Hi-lume®, Hi-lume® Compact SE, Hi-lume® 3D, Eco-10®, EcoSystem® ballasts.

Also compatible with Hi-lume® LED driver.

#### Plug-in lamp dimmer and plug-in module model numbers

## Plug-in wireless table top lamp dimmer

#### Plug-in lamp dimmer

120V 300W MRF2-3LD-**EE**4

Rated for: incandescent/halogen.

## Plug-in wireless module

#### Plug-in lamp dimmer module

MRF2-3PD-1-**EE**4 1 receptacle 120V 300W

3 receptacles MRF2-3PD-3-**EE**4 120V 300W

10 Watt minimum load.

Rated for: incandescent/halogen and magnetic low-voltage.

Can be converted to a switch for lighting loads.

#### Plug-in appliance module

1 receptacle MRF2-15APS-1-**EE** 120V 15A 1/2HP

## Hi-lume LED drivers: 3-wire fluorescent dimmers\*

#### Digital fade dimmer

Multi-location/single-pole MRF2-F6AN-DV-CC1 120/277V 6A

For use with Hi-lume LED driver only.

For more information on Hi-lume LED drivers, visit www.lutron.com/HilumeLED.

Low-end trim available via advanced programming.

CC1: Gloss and Satin color codes, see pg. 69 (Wallplates not included, order separately, see pg. 160)

**EE**<sup>4</sup>: Available in White (WH) and Black (BL)

All models must be derated if ganged unless otherwise noted, see pg. 170.

\*Requires neutral wire connection.

†Minimum load is 50W/VA.

#### Switch model numbers

#### **▲** Switches

#### Digital switch\*

Multi-location/single-pole MRF2-6ANS-<u>CC</u><sup>1</sup> 120 V 6 A light or 3 A fan

Rated for: incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts, general purpose fans and most non-dim LED drivers.

#### Switches-specification grade

Multi-location/single-pole\* MRF2-8ANS-120-<u>CC</u><sup>1</sup>
120V 8A light or 5.8A fan

Multi-location/single-pole\*\* MRF2-8S-DV-<u>CC</u><sup>1</sup>
120V 8A light or 3A fan or 1/4 HP motor
277V 8A light or 3A fan

Rated for: incandescent/halogen, magnetic low-voltage, electronic low-voltage, non-dim fluorescent ballasts, non-dim LED drivers, general purpose fans and most non-dim LED drivers.

#### **Companion controls model numbers**

#### **Companion controls**

#### Companion dimmers

Companion dimmer	MA-R- <b>CC</b> 3
120V	MSC-AD- <b>CC</b> ⁴
Companion dimmer	MA-R-277- <u><b>CC</b></u> 3
277 V	MSC-AD-277- <u>CC</u> ⁴

No derating required if ganged.

#### Companion switches

Companion switch	MA-AS- <u>CC</u> 3
120V	MSC-AS- <u>CC</u> 4
Companion switch	MA-AS-277- <u><b>CC</b></u> 3
277 V	MSC-AS-277- <u>CC</u> 4

No derating required if ganged.

CC1: Gloss and Satin color codes, see pg. 69

 ${\underline{\bf CC}}^3$ : Gloss color codes, see pg. 69

**CC**<sup>4</sup>: Satin color codes, see pg. 69 (Wallplates not included with above, order separately, see pg. 160)

**EE**<sup>4</sup>: Available in White (WH) and Black (BL)

All models must be derated if ganged unless otherwise noted, see pg. 170.

\*Requires neutral wire connection.

\*\*Minimum load is 40W/VA.

#### Sensor model numbers

#### **Sensors**

Radio Powr Savr™ ceiling mount wireless sensors

Occupancy/vacancy sensor LRF2-OCRB-P-<u>**EE**</u><sup>3</sup>
Vacancy sensor LRF2-VCRB-<u>**EE**</u><sup>3</sup>

Radio Powr Savr<sub>TM</sub> wall-mount wireless sensors

Occupancy/vacancy sensor LRF2-OWLB-P-WH

180° wall-mount

Vacancy sensor LRF2-VWLB-P-WH

180° wall-mount

Occupancy/vacancy sensor LRF2-OKLB-P-WH

90° corner-mount

Vacancy sensor LRF2-VKLB-P-WH

90° corner-mount

Occupancy/vacancy sensor LRF2-OHLB-P-WH

Hallway

Vacancy sensor LRF2-VHLB-P-WH

Hallway

Communicates with up to nine dimmers and switches.

Add up to three sensors for maximum coverage.

For compatibility with other systems, visit

www.lutron.com/occsensors.

Radio Powr Savrm wireless daylight sensor

Daylight sensor LRF2-DCRB-WH

## Wireless controls and accessories model numbers

#### Wireless controls

Pico™ wireless controls

3-button with raise/lower MRF2-3BRL-L-**FF¹**2-button with raise/lower MRF2-2BRL-L-**FF¹**3-button with "Preset" button MRF2-3B-L-**FF¹**3-button with MRF2-3B-L-**FF¹**-E01
"Welcome" button
2-button MRF2-2B-L-**FF¹** 

**Accessories** 

**Pedestals** 

Single pedestal L-PED1-<u>EE</u><sup>4</sup>
Double pedestal L-PED2-<u>EE</u><sup>4</sup>

Pico faceplate adapter kit

Faceplate kit PICO-FP-ADAPT


**<u>EE</u>**<sup>3</sup>: Available in White (WH), Light Almond (LA) and Black (BL)

**EE**<sup>4</sup>: Available in White (WH) and Black (BL)

FF1: Pico color codes, see pg.71

## **Wallplates**

4.75 in (121 mm)



Shown actual size: 2-gang Claro® wallplate in White (WH). For more information about Designer wallplates, see pg. 160.

#### **Coordinated electrical devices**



Tamper resistant GFCI receptacle




6-port frame



For more information about coordinated Designer electrical devices, see pg. 163.

## Wallplates and accessories | Designer | Claro / Satin Colors





Shown actual size: Maestro dimmers and 2-gang Claro wallplate in White (WH).

#### **Product family features**

- · Can be used in conjunction with the following dimmer(s) and switch(es): Maestro®, Maestro IR®, Maestro Wireless®, Pico™ wireless control, Spacer System®, Diva®, Lyneo® Lx, Skylark®, Skylark Contour™
- All Lutron® wallplates are screwless, seamless and have no visible hardware; the front plate securely snaps into the alignment adapter plate
- Full line of wiring devices in designer style opening
- · Blank inserts available for Gloss colors (DV-BI-) and Satin colors (SC-BI-)
- · Customize your designer wallplate with engraving, contact customer service to get started at 1.888.LUTRON1

### Ganging and derating

- · Designer wallplates use standard ganging
- · Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging), see pg. 170
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pg. 172

#### **Available finishes**

Use **BOLD** color code in model number (Example: SC-1- $\underline{\textbf{PL}}$ )

Gloss finishes



#### Satin finishes



<sup>\*</sup>Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Wallplates for Maestro®, Maestro IR®, Maestro Wireless®, Pico™ wireless control, Spacer System®, Diva®, Lyneo® Lx, Skylark® and Skylark Contour™




1-gang\*

CW-1-**CC**<sup>2</sup>

SC-1-<u>**CC**</u>⁴

W: 2.94 in (75 mm); H: 4.69 in (119 mm)


D: .30 in (7.6 mm)



4-gang\* CW-4-<u>CC</u><sup>2</sup> SC-4-**CC**<sup>4</sup>

W: 8.37 in (213 mm); H: 4.69 in (119 mm);


D: .30 in (7.6 mm)



2-gang\* CW-2-**CC**<sup>2</sup> SC-2-**CC**<sup>4</sup>

W: 4.75 in (121 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)




5-gang\*

CW-5-**CC**<sup>2</sup> SC-5-**CC**<sup>4</sup>

W: 10.18 in (259 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)

Multiple devices with line and low-voltage can be mounted behind a common wallplate using a standard barrier backbox, see Application Note #213 (Combining Low-Voltage and Line Voltage Wiring Devices in a Multi-Gang Box) at www.lutron.com/applicationnotes.



3-gang\* CW-3-<u>CC</u><sup>2</sup> SC-3-**CC**<sup>4</sup>

W: 6.56 in (167 mm); H: 4.69 in (119 mm);


D: .30 in (7.6 mm)

<u>CC</u><sup>2</sup>: Gloss and Stainless Steel color codes, see pg. 161

**CC⁴**: Satin color codes, see pg. 161

Multi-gang dimmer installations may require derating, see pg. 170.

\*Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.



6-gang\* CW-6-<u>CC</u><sup>2</sup> SC-6-**CC**<sup>4</sup>

W: 12.00 in (305 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)

#### Cable jacks



F-style, 75-Ohm coaxial cable

Single cable jack*	CA-CJH- <b>CC</b> 3
	SC-CJ- <b>CC⁴</b>

## Telephone jacks



6-conductor telephone jack, RJ11

SC-PJ-CC⁴

Single telephone jack\* CA-PJH-<u>CC</u><sup>3</sup>

**<u>CC</u>**<sup>2</sup>: Gloss and Stainless Steel color codes, see pg. 161

**<u>CC</u>**<sup>3</sup>: Gloss color codes, see pg. 161

**CC⁴**: Satin color codes, see pg. 161

#### **Receptacles**



#### Tamper resistant receptacles

15A, 125V*	CARS-15-TR- <b>CC</b> <sup>3</sup>
	SCRS-15-TR- <u><b>CC</b></u> ⁴
20A, 125V*	SCRS-20-TR- <u><b>CC</b></u> ⁴

#### Receptacles

15A, 125V*	CAR-15H- <u><b>CC</b></u> 3
	SCR-15- <u><b>CC</b></u> ⁴
20A, 125V*	SCR-20- <u><b>CC</b></u> ⁴

#### **GFCI** Receptacles



- Press test button to confirm LED indicator status
- Press reset button to reset GFCI after circuit interruption

#### Tamper resistant GFCI receptacles

•	•	
15A, 125V*	GFCI	CAR-15-GFTR- <b>CC</b> <sup>3</sup>
		SCR-15-GFTR- <b>CC</b> ⁴
20A, 125V*	GFCI	SCR-20-GFTR- <u>CC</u> ⁴

#### Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plugs for dimming use

#### Duplex for dimming use

15A	120/125V*	CAR-15-DFDU- <u>CC</u> 2
15A	120/125V*	SCR-15-DFDU- <u>CC</u> 4
20 A	120/125V*	CAR-20-DFDU- <u>CC</u> 2
20 A	120/125V*	SCR-20-DFDU- <u>CC</u> 4

#### Receptacles for dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plugs for dimming use
- Bottom half is a general use receptacle and will fit standard duplex plugs

#### Split duplex (half for dimming use)

15A	120/125V*	CAR-15-HFDU- <u>CC</u> 2
15A	120/125V*	SCR-15-HFDU- <u>CC</u> ⁴
20A	120/125V*	CAR-20-HFDU- <u>CC</u> <sup>2</sup>
20 A	120/125V*	SCR-20-HFDU- <u>CC</u> ⁴

#### Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plugs for dimming use
- 15A model shown
- Tamper resistant shutter mechanism

#### Dual dimming tamper resistant

15A	120/125V*	CAR-15-DDTR- <u><b>CC</b></u> <sup>2</sup>
15A	120/125 V*	SCR-15-DDTR- <u>CC</u> ⁴
20A	120/125V*	CAR-20-DDTR- <u>CC</u> 2
20 A	120/125V*	SCR-20-DDTR-CC

#### Receptacles for dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plugs for dimming use
- Bottom half is a general use receptacle and will fit standard duplex plugs
- 15A model shown
- Tamper resistant shutter mechanism

#### Half dimming tamper resistant

15A	120/125V*	CAR-15-HDTR- <u><b>CC</b></u> <sup>2</sup>
15A	120/125V*	SCR-15-HDTR- <u>CC</u> ⁴
20A	120/125V*	CAR-20-HDTR- <u>CC</u> 2
20A	120/125V*	SCR-20-HDTR- <u>CC</u> ⁴

**<u>CC</u>**<sup>2</sup>: Gloss color code and Stainless Steel,

see pg. 161

CC4: Satin color codes, see pg. 161

# Replacement plug for dimming (use with receptacles on left)



- This plug required for use with Lutron® receptacles for dimming use—plug will work in standard receptacle
- Easily replaces the existing plugs on lamps

120/125V	RP-FDU-10-WH
White	
120/125V	RP-FDU-10-BR
Brown	

UL/CSA/NOM regulatory approvals.

#### **Important notes**

- If the hot and dimmed hot feeds to the split duplex HFDU are supplied from different circuits or split-wired with separate switch-legs, a means to simultaneously disconnect these circuits must be provided at the panel board where they originate (NEC 210.7(C) 2002 Edition). A 2-pole circuit breaker or two single-pole circuit breakers with an approved handle tie can be used to accomplish this simultaneous disconnect. Feed-through dimming panels, which are those without breakers, are recommended when using the HFDU.
- Receptacles and plugs for dimming use are UL listed for use with all Lutron® wallbox dimmers included in this catalog.
- If there is only one electrical feed to the receptacle, then the duplex DFDU must be used.
- For detailed information, see Application Notes #91 (Guide to Dimming Table Lamps) and #109 (Guide to Dimming Portable Lamps via Receptacles) at www.lutron.com/applicationnotes.

**CC**<sup>2</sup>: Gloss color code and Stainless Steel, see pg. 161

CC4: Satin color codes, see pg. 161

#### Field customizable 6-port frame



- Shipped with six blanks in matching colors
- Connectors and wallplate sold separately
- Connectors snap in (no tools required)
- Connectors available in White (WH), unless noted

6-port frame*	CA-6PF- <u><b>CC</b></u> <sup>3</sup>
	SC-6PF- <b><u>CC</u>⁴</b>

#### **Connectors for 6-port frame**

#### Telephone/network jacks



8-conductor,	CON-1P-C3- <b>EE⁴</b>
RJ45 category 3	
8-conductor,	CON-1P-C5E- <b>EE⁴</b>
RJ45 category 5e	
8-conductor,	CON-1P-C6- <b>EE</b> ⁴
RJ45 category 6	

#### Fiber jacks



MT-RJ feed through	CON-1F-MTRJ-WH
SC simplex	CON-1F-SC-WH
LC non-flush mount	CON-1F-LC-WH
ST style	CON-1F-ST-WH

#### Cable jack



F-style,	CON-1C- <b>EE</b> ⁴
75-Ohm coaxial cable	

#### BNC jack



BNC connector, 50-Ohm	CON-1B-WH

Connectors only for use with 6-port frame.

#### **Switches**



- · Paddle turns on/off
- · Use with any 15A load
- General purpose switching of all sources and motor loads
- · No derating if ganged

### General purpose switches (120/277 V)

15A*	CA-1PSH- <u><b>CC</b></u> <sup>3</sup>
	SC-1PS- <u><b>CC</b></u> ⁴
15A*	CA-3PSH- <b>CC</b> <sup>3</sup>
	SC-3PS- <b>CC</b> ⁴
15A*	CA-4PSH- <b>CC</b> <sup>3</sup>
	SC-4PS- <u><b>CC</b></u> ⁴
	15A*

# General purpose switch with locator light (120 V only)

Single-pole	15A*	CA-1PSNL- <b>EE</b> <sup>2</sup>
		SC-1PSNL- <u>EE</u> 10
3-way	15A*	CA-3PSNL- <u><b>EE</b></u> ²
		SC-3PSNL- <u>EE</u> 10
4-way	15A*	CA-4PSNL- <b>EE</b> 2
		SC-4PSNL- <u>EE</u> 10

**CC**<sup>3</sup>: Gloss color codes, see pg. 161

**CC⁴**: Satin color codes, see pg. 161

**EE**<sup>2</sup>: Only available in Almond (AL), Ivory (IV), Light Almond (LA) and White (WH)

**<u>EE</u>**<sup>4</sup>: Only available in White (WH) and Black (BL)

**EE**<sup>10</sup>: Available in Biscuit (BI), Eggshell (ES), Goldstone (GS), Limestone (LS), Sea Glass (SG) and Snow (SW)

#### How to understand ganging and derating

#### Standard ganging

Ganging is the side-by-side mounting of two or more dimmers or accessory devices under a multi-gang wallplate.

Standard multi-gang installation:

- Uses standard multi-gang electrical backboxes
- Uses standard multi-gang wallplates
- Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging)
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pgs. 172–173

# Custom ganging for Architectural style controls

For Architectural style dimmers and switches, it is possible to retain the maximum capacity of dimmers in multi-gang applications via custom architectural multi-gang:

- May require customized, wider-thanstandard wallplates
- May require wider-than-standard electrical backboxes
- · Allows full capacity ("No Fins Broken") ganging
- Required for Nova® dimmers and for larger width (high capacity) architectural controls
- Visit www.lutron.com/customganging for additional information

#### Standard ganging for dimmers, switches and accessories

#### **New Architectural Architectural Designer Traditional** pg. 148 pg. 160 pg. 152 pg. 166 F Vierti<sub>®</sub> Vareo<sub>®</sub> Maestro Abella® Nova T☆® Maestro IR® Ceana® Maestro Wireless® Ariadnia Spacer System® Glyder<sub>®</sub> Diva<sub>®</sub> Rotary Lyneo<sub>®</sub> Lx Skylark<sub>®</sub> Skylark Contour<sub>TM</sub> Derating Table 1 Derating Table 2 Derating Table 1 **Derating Table 1** pg. 172 pg. 173 pg. 172 pg. 172 www.lutron.com | 1.800.523.9466 | **LUTRON**

### Standard ganging and fins broken derating examples:



One Nova T☆® dimmer



No fins broken Full capacity



Standard 1-gang backbox



Standard 1-gang architectural wallplate



Two Nova T☆ dimmers "Fins Broken" ganging




One fin broken\* Partial derating




Standard 2-gang backbox



Standard 2-gang architectural wallplate




Three Nova T☆ dimmers "Fins Broken" ganging



Inside: Two fins broken\*
Full derating

Outside: One fin broken\*



Standard 3-gang backbox



Standard 3-gang architectural wallplate

## **Custom Architectural ganging example:**



Two Nova T☆ dimmers "No Fins Broken" ganging




Partial derating

No fins broken Full capacity



Backbox with chase nipple



Custom architectural wallplate

For further information on ganging and derating, visit www.lutron.com/multigang.

\*The fins are scored and designed to be removed easily.

## Appendix | Ganging and derating

## **Derating Table 1**

New Architectural | Vierti®

**Designer** | Maestro®, Maestro IR®, Maestro Wireless®, Spacer System®, Diva®, Lyneo® Lx, Skylark Contour™, Skylark® **Traditional** | Abella®, Ceana®, Ariadni®, Glyder®, Rotary

	No fins broken	1 fin broken	2 fins broken
Incandescent	NO IIIIS DI OREII	I IIII DIOREII	Z IIIIS DIOREII
Dimmers	600W	500 W	400 W
	1000W	800W	650W
Dual dimmers	300W	250W	200W
	300W	250W	200W
Magnetic low-voltage	000 **	200 **	200 **
Dimmers	600 VA /450 W	500 VA / 400 W	400 VA/300 W
	1000 VA /800 W	800 VA / 650 W	650 VA / 500 W
Electronic low-voltage		1	
Dimmers	300W	250W	200W
	500 W	450W	400 W
	600W	500 W	400 W
Fluorescent			
Hi-lume <sub>®</sub> /Hi-lume <sub>®</sub> Compact SE/Eco-10 <sub>®</sub> /	EcoSystem <sub>®</sub>		
Vierti	60 ballasts/6A	50 ballasts/5A	35 ballasts/3.5A
Maestro/Spacer System	20 ballasts/6A	20 ballasts/5A	20 ballasts/3.5A
Diva, Skylark, Lyneo Lx and Ariadni	no derating	no derating	no derating
Tu-Wire®: Spacer System, Diva, Skylark	5A	4A	3.3A
Fan controls			
Quiet 7-speed	1.0A/300W	1.0A/300W	1.0A/300W
Quiet 3-speed	1.5A	1.5A	1.5A
Fully variable	5A	4A	3A
Fan/light controls			
Quiet 7-speed	1.0A/300W	1.0A/300W	1.0A/300W
Quiet 3-speed	1.5A/300W	1.5A/300W	1.5A/300W
	1.5A/360W	1.5A/360W	1.5A/360W
Fully variable	2.5A/300W	2.1A/250W	1.7A/200W
Electronic switches			
Vierti	6A/3A	5A/3A	3.5A/3A
Maestro (light/fan)	8A/3A	6.5A/3A	5A/3A
Abella (light/fan)	6A/3A	5A/3A	3.5A/3A

## Appendix | Ganging and derating

## **Derating Table 2**

Architectural | Vareo®, Nova T☆®

	₩ <u>₩</u> No fins broken	1 fin broken	및 2 fins broken
Incandescent			
Dimmers	600 W	500W	300W
	1000W	900W	700W
	1500W	1250W	1000W
	1950W	_	_
Magnetic low-voltage	·		
Dimmers	600 VA / 450 W	500 VA /400 W	300 VA/250 W
	1000 VA/800 W	900 VA / 750 W	700 VA/500 W
	1500 VA/1200 W	1250 VA / 1000 W	1000 VA/800 W
Electronic low-voltage		^	
Dimmers	300 W	300W	250W
	600 W	500 W	400W
Fluorescent		^	
Hi-lume <sub>®</sub> /Hi-lume <sub>®</sub> Compact SE	/Eco-10®/EcoSystem®		
Vareo	20 ballasts/8A	20 ballasts/6A	20 ballasts/4.5A
Nova T☆	6A	no derating	no derating
	8A	no derating	no derating
	16A	no derating	no derating
0-10 VDC control <sup>1</sup>	30 mA ballasts	no derating	no derating
Tu-Wire®	5A	4A	3.3A
Fan controls			
Quiet 3-speed	1.5A	no derating	no derating
Fully variable	6A	4.2 A	2.5 A
Fully variable	12A	10A	8.3A
Electronic tapswitches <sup>2</sup>			
VETS-1000-	1000 W	800W	650 W
VETS-1000-SL-	1000W	900 W	700 W
VETN-1000-	1000 VA	700 VA	550 VA

For further information on ganging Nova®, visit www.lutron.com/customganging.

<sup>&</sup>lt;sup>1</sup>PowerPack required for line voltage switching.

<sup>&</sup>lt;sup>2</sup>VETS-R-Auxiliary electronic tapswitches do not require derating.

# Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



n'	** +	•				
Dimmers	capacity <sup>†</sup>	<u> </u>				
☐ Incandescent/halogen 120V	600 W			0		
	1000W			Ø		
	1500W		WBX			
	2000W		WBX			
▼ Magnetic low-voltage 120V	600 VA (450 W)					
	1000 VA (800 W)					
	1500 VA (1200 W)		WBX			
	2000 VA (1600 W)		WBX	WBX		
▼ Magnetic low-voltage 277∨	600 VA (450 W)		WBX		WBX	
	1000 VA (800 W)		WBX		WBX	
₩ Electronic low-voltage 120 V	300W		WBX			
	450W		WBX	WBX		
	600W		WBX		WBX	
₩ Electronic low-voltage 277 V	16A		WBX	WBX	WBX	
_ Neon/cold cathode			WBX	WBX		
್/®3-wire ballasts and Hi-lume⊚ LE	ED driver 120V 6A					
Hi-lume, Hi-lume Compact SE,	8A					
Eco-10 <sub>®</sub> and EcoSystem <sub>®</sub> ballasts	16A		3F			
ಾ⁄®3-wire ballasts and Hi-lume LE	<b>D driver</b> 277V 6A		3F			
Hi-lume, Hi-lume Compact SE,	8A		3F			
Eco-10 and EcoSystem ballasts	16A		3F	3F	3F	
<b>⊅ Tu-Wire</b>	5A		PA			
<b>☞/◎0-10VDC</b> (ballasts or LED Drivers	) 120/277V 16A	TVI	TVI			

**WBX**: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

**3F**: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

\*Consult Lutron Technical Support for information on interfaces with Vierti.

<sup>†</sup>UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

# Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



Dimmers	capacity <sup>†</sup>	Ø	0	0	Ø	
☐ Incandescent/halogen 120V	600 W	<b>3</b>				<b>3</b>
	1000W					
	1500W	WBX		WBX	WBX	WBX
	2000W	WBX		WBX	WBX	WBX
<b>▼ Magnetic low-voltage</b> 120V	600 VA (450 W)					
	1000 VA (800 W)					
	1500 VA (1200 W)	WBX		WBX	WBX	WBX
	2000 VA (1600 W)	WBX		WBX	WBX	WBX
▼ Magnetic low-voltage 277 V	600 VA (450 W)	WBX		WBX	WBX	WBX
	1000 VA (800 W)	WBX		WBX	WBX	WBX
₩ Electronic low-voltage 120 V	300 W			WBX		
	450W			WBX		WBX
	600W			WBX		WBX
₩ Electronic low-voltage 277 V	16A	WBX		WBX	WBX	WBX
_ Neon/cold cathode				WBX		WBX
್ರಾ•3-wire ballasts and Hi-lume₀ L	ED driver 120V 6A					
Hi-lume, Hi-lume Compact SE,	88	3F		3F	3F	
Eco-10 <sub>®</sub> and EcoSystem <sub>®</sub> ballasts	s 16A	3F		3F	3F	3F
್ರಾ⊛3-wire ballasts and Hi-lume LE	<b>D</b> driver 277 V 6A					
Hi-lume, Hi-lume Compact SE,	8A	3F		3F	3F	3F
Eco-10 and EcoSystem ballasts	16A	3F		3F	3F	3F
Z⊕ Tu-Wire <sub>®</sub> ballasts 120 V	5A	PA		PA		
<b>™©0-10VDC</b> (ballasts or LED Drivers	s) 120/277V 16A	TVI		TVI	TVI	TVI

**WBX**: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

**3F**: Fluorescent Power Module

(PHPM-3F-DV-WH)

**TVI**: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

# Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



			pg.100		
Dimmers	capacity <sup>†</sup>				•
	600 W		9	<b>3</b>	
	1000 W				
	1500W	WBX		WBX	
	2000 W	WBX		WBX	
<b>▼ Magnetic low-voltage</b> 120V	600 VA (450 W)				
	1000 VA (800 W)			WBX	
	1500 VA (1200 W)	WBX		WBX	
	2000 VA (1600 W)	WBX		WBX	
▼ Magnetic low-voltage 277 V	600 VA (450 W)	WBX		WBX	
	1000 VA (800 W)	WBX		WBX	
₩ Electronic low-voltage 120V	300W				
	450W			WBX	
	600 W			WBX	
₩ Electronic low-voltage 277 V	16A	WBX		WBX	
		WBX		WBX	
	ED driver 120V 6A				
Hi-lume, Hi-lume Compact SE,	8A				
Eco-10 <sub>®</sub> and EcoSystem <sub>®</sub> ballasts	s 16A	3F		3F	
্ৰ-্ভ3-wire ballasts and Hi-lume LE	D driver 277V 6A				
Hi-lume, Hi-lume Compact SE,	8A	3F		3F	
Eco-10 and EcoSystem ballasts	16A	3F		3F	
<b>∠ Tu-Wire</b> ballasts 120V	5A	PA			
<b>☞®0-10VDC</b> (ballasts or LED Drivers	s) 120/277V 16A	TVI		TVI	

**WBX**: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

**3F**: Fluorescent Power Module

(PHPM-3F-DV-WH)

**TVI**: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

# Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



Dimmers	capacity <sup>†</sup>		
☐ Incandescent/halogen 120 V	600 W	<b>9</b>	9
	1000 W		
	1500W	WBX	
	2000 W	WBX	
<b>▼ Magnetic low-voltage</b> 120V	600 VA (450 W)		
	1000 VA (800 W)		
	1500 VA (1200 W)	WBX	
	2000 VA (1600 W)	WBX	
▼ Magnetic low-voltage 277 V	600 VA (450 W)	WBX	
	1000 VA (800 W)	WBX	
ਓ Electronic low-voltage 120 V	300W	WBX	
	450W	WBX	
	600W	WBX	
₩ Electronic low-voltage 277 V	16A	WBX	
_ Neon/cold cathode		WBX	
್®3-wire ballasts and Hi-lume⊚ LE	D driver 120V 6A		
Hi-lume, Hi-lume Compact SE,	8A		
Eco-10® and EcoSystem® ballasts	16A	3F	
ಿತ-wire ballasts and Hi-lume LE	<b>D driver</b> 277V 6A		
Hi-lume, Hi-lume Compact SE,	8A	3F	
Eco-10 and EcoSystem ballasts	16A	3F	
<b>ZE</b> Tu-Wire⊚ ballasts 120 V	5A	PA	
<b>☞⊚0-10VDC</b> (ballasts or LED Drivers	) 120/277V 16A	TVI	

**WBX**: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

**3F**: Fluorescent Power Module

(PHPM-3F-DV-WH)

**TVI**: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

### Dimmer models/load interface compatibility

	Incandescent, magnetic and electronic low-voltage (120/277 V)		3-wire Fluorescent ballasts or Hi-lume⊚ LED drivers (120/277 V)		0-10 VDC Ballasts or LED drivers (120/277 V)	
	WBX		3F		TVI	
	Wallbox Phase Adaptive Power Module*		Fluorescent Power Module*		0-10 V Interface	
	PHPM-WBX-	-DV-WH	PHPM-3F-DV-WH		GRX-TVI	
Dimmer Family	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location
Abella®	_	_	_	_	_	_
Ariadni®	_	AYF-103P-	_	AYF-103P-	_	AYF-103P-
Ceana®	_	_	_	_	_	_
Diva <sub>®</sub> Gloss	_	DVF-103P-	_	DVF-103P-	-	DVF-103P-
Diva Satin Colors®	_	DVSCF- 103P-	_	DVSCF- 103P-	_	DVSCF- 103P-
Glyder®	_	_	_	_	_	_
Lyneo <sub>®</sub> Lx	_	LXF-103PL-	_	LXF-103PL-	_	LXF-103PL-
Maestro® Gloss	_	MAF-6AM-	_	MAF-6AM-	_	MAF-6AM-
Maestro® Satin Colors®	_	MSCF-6AM-	_	MSCF-6AM-	_	MSCF-6AM-
Maestro Wireless®	_	MRF2- F6AN-DV-	_	MRF2- F6AN-DV-	_	MRF2- F6AN-DV-
Nova®	NF-10-	NF-103P-	NF-10-	NF-103P-	NF-10-	NF-103P-
Nova T☆®	NTF-10-	NTF-103P-	NTF-10-	NTF-103P-	NTF-10-	NTF-103P-
Skylark <sub>®</sub>	SF-10P-	SF-103P-	SF-10P-	SF-103P-	SF-10P-	SF-103P-
Spacer System <sub>®</sub>	_	SPSF-6AM-	-	SPSF-6AM-	SPSF-S6A-	SPSF-6AM-
Vareo®	-	VF-10-	_	VF-10-	_	VF-10-
Vierti®	contact Lutron		contact Lutron		_	VTF-6AM-

#### Use only dimmer model numbers listed.

<sup>\*</sup>Dual 120/277 V model given,120 V only versions are also available. Please see Technical notes, pg. 179.

#### Dimmer models/load interface compatibility

	Tu-Wire <sub>®</sub> I Ballasts (	Fluorescent 120V)	Switched Lighting (120/277 V)		
	PA		sw		
	Phase Ada Power Mo	dule*	Switching Power Module* PHPM-SW-DV-WH		
Dimmer Family	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location	
Abella®	_	_	_	AB-S6AM-	
Ariadni®	_	AYF-103P-	_	_	
Ceana®	_	_	_	_	
Diva <sub>®</sub> Gloss	_	DVF-103P-	_	_	
Diva Satin Colors®	_	DVSCF-103P-	_	_	
Glyder®	_	_	_	_	
Lyneo <sub>®</sub> Lx	_	LXF-103PL-	LX-1PSL-	LX-3PSL-	
Maestro <sub>®</sub> Gloss	_	MAF-6AM-	_	MA-S8AM-	
Maestro® Satin Colors®	_	MSCF-6AM-	_	MSC-S8AM-	
Maestro Wireless®	_	MRF2- F6AN-DV-	_	MRF2-6ANS-	
Nova <sub>®</sub>	NF-10-	NF-103P-	_	_	
Nova T☆®	NTF-10-	NTF-103P-	_	_	
Skylark <sub>®</sub>	SF-10P-	SF-103P-	_	_	
Spacer System <sub>®</sub>	SPSF- S6A-	SPSF-6AM-	SPSF- S6A-	SPSF-S6AM-	
Vareo <sub>®</sub>	_	VF-10-	_	VETN-1000-	
Vierti®	contact Lutron		contact Lutron		

#### **Technical notes**


- Lighting load interfaces must be matched to load type and voltage
- All load interfaces for dimmed load are controlled by a 120 V 3-wire fluorescent dimmer
- Power feed to dimmer may differ from lighting load/interface voltage
- Interfaces typically require additional power feeds
- For wiring information, consult wiring diagrams, see pgs. 193-195
- For assistance and additional solutions, consult Lutron Technical Support at 1.800.523.9466 (24 hours/7 days)

#### Interface mounting

- PHPM interfaces mount to 2-gang electrical backbox (W: 6.30 in x H: 5.10 in)
- GRX-TVI enclosure is surface mount only (W: 6.10 in x H: 12.50 in x D: 3.30 in)

#### Use only dimmer model numbers listed.


\*Dual 120/277 V model given, 120 V only versions are also available. Please see Technical notes, pg. 179.



For illustration purposes only. Consult model number pages for specific voltage and capacity information.

For ballast information, visit www.lutron.com/ballasts.

†Interface provides additional capacity and/or may be different voltage than dimmer.




For illustration purposes only. Consult model number pages for specific voltage and capacity information.

For more information on LED drivers, visit www.lutron.com/LED.

<sup>\*\*</sup>Consult www.lutron.com/LED for compatible 0-10V LED drivers.


<sup>†</sup>Interface provides additional capacity and/or may be different voltage than dimmer.



For illustration purposes only. Consult model number pages for specific voltage and capacity information.

For more information on LED drivers, visit www.lutron.com/LED.

†Interface provides additional capacity and/or may be different voltage than dimmer.



For illustration purposes only. Consult model number pages for specific voltage and capacity information.

For more information on LED drivers, visit www.lutron.com/LED.

<sup>\*</sup>Refer to pg. 74 for specific load type.

<sup>†</sup>Interface provides additional capacity and/or may be different voltage than dimmer.