

FEATURES & SPECIFICATIONS

INTENDED USE — The VT[™] Volumetric Troffer combines the aesthetics and high performance with intelligent LED engines for applications - offices, schools, retail locations and hospitals. High-efficacy light engine delivers long life and excellent color, ensuring a superior guality lighting installation that is highly efficient and sustainable. Featured nLight controls system provides design flexibility and ease of installation and optimum energy savings.

CONSTRUCTION — Rugged, one-piece cold-rolled steel coated polyester, painted after fabrication with embossed facets. Impact-modified, single clear acrylic diffuser provides excellent shielding and wide distribution. End plates include integral T-bar clips. Fixture may be mounted and wired in continuous rows. Total fixture height is only 4-3/8". OPTICS — Volumetric illumination is achieved by creating an optimal mix of light to walls, partitions, vertical and horizontal work surfaces — rendering the interior space, objects and occupants in a more balanced,

complementary luminous environment. Linear faceted reflector cavity softens and distributes light into the space while minimizing luminous contrast between the fixture and ceiling. Sloped end plates provide a smooth, luminous transition between fixture and ceiling while enhancing the perception of fixture depth. Advanced optical film provides superior LED concealment and even illumination across the diffuser.

ELECTRICAL — Long-life LEDs, coupled with high-efficiency drivers, provide superior quantity and quality of illumination for extended service life. VTLED is rated to deliver L80 performance for 50,000 hours.

Standard nLight[™] embedded controls make each luminaire addressable - allowing it to digitally communicate with other nLight enabled controls such as dimmers, switches, occupancy sensors and photocontrols. Simply connect all the nLight enabled control devices and the VTLED luminaires using standard Cat-5 cabling. Unique plug-and-play convenience as devices and luminaires automatically discover each other and self-commission. Lumen Management: Unique lumen management system (option N80) provides onboard intelligence that actively manages the LED light source so that constant lumen output is maintained over the system life,

preventing the energy waste created by the traditional practice of over-lighting.

Bi-level dimming option allows system to be switched to 50% power for compliance with common energy codes while maintaining fixture appearance.

LED AccuDrive [™] driver delivers full-range dimming from 0-10V control signal.

Driver disconnect provided where required to comply with US and Canadian codes.

INSTALLATION — Unique grid interfacing arrangement provides mounting into standard 1" and 9/16" tee bar or screw slot grids. 9/16" allows fixture trim to hang level with architectural ceiling tiles. Drywall ceiling adaptors available. Suitable for damp location.

LISTINGS — CSA Certified to meet U.S. and Canadian standards. Patents pending.

DLC certified test to LM80 standings.

WARRANTY — 5-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Specifications subject to change without notice.

ORDERING INFORMATION Lead times will vary depending on options selected. Consult with your sales representative.



2012 RECOGNIZED PRODUCT

2011 ARCHITECTURAL SSL PRODUCT INNOVATION AWARD

Example: 2VTL4 48L ADP D47 LP835 N80

									,						-		
2VTL4						ADP											
Series		Air func	tion	Lume	ens	Diffuse	er	Voltage		Watt	age	Color temper	ature	Controls		Option	IS
	olumetric roffer 2X4 ED	(blank) H	Static Heat removal	24L 40L 48L 72L	2400 lumens ¹ 4000 lumens ¹ 4800 lumens ¹ 7200 lumens ¹	ADP	Acrylic linear prismatic	(blank) 347	MVOLT 347 ²	D40 D47		LP835 LP840 LP850	82CRI, 3500K 82CRI, 4000K 82CRI, 5000K ⁸	NX BLD N80 N80EMG N100 N100EMG	Dimming, no nlight Bi-level dimming nlight with 80% lumen management. nlight with 80% lumen management. For use with generator supply EM power. nlight without lumen management. For use with generator supply EM power.	EL14L	1400 Iumen batter pack

. 1 2

3

Catalog

Number

Notes


nLight™ Control Accessories: Order as separate catalog number. Visit www.sensorswitch.com/nLight for complete listing of nLight controls.						
WallPod stations	Model number	Occupancy sensors	Model number			
0n/0ff	nPODM [color]	Standard range 360°, ceiling (PIR / dual tech)	nCM 9 / nCM PDT 9			
On/Off & Raise/Lower	nPODM DX [color]	Extended range 360°, ceiling (PIR / dual tech)	nCM 10 / nCM PDT 10			
Graphic Touchscreen	nPOD GFX	Wide view (PIR / dual tech)	nWV 16 / nWV PDT 16			
Photocell controls	Model number	Cat-5 cable bundles (plenum rated)	Model number			
Continuous dimming	nCM ADC	10', CAT5 10FT	CAT5 10FT J1			
On/Off & Dimming	nCM PC ADC	15', CAT5 15FT	CAT5 15FT J1			

	Accessories:	Order as separate catalog r	numt	er.				
2VT4 F916 Trim to adjust fixture mounting flush with 9/16" T-ba fixture								
	DGA24	Drywall ceiling adaptor , unit installation						
Not	tes		4	For use with 24L.				
1	Approximate Iu		5	For use with 40L.				
2	,	for availability. Not available	6	For use with 48L.				
	with EL14 battery pack or BLD controls.			For use with 70				


- For use with 721 7
- Approximate input power (watts) +/-5%.
 - Not available with 4000 lumen system. 8

PHOTOMETRICS


2VTL4 40L ADP LP835, 4026 delivered lumens, test no. LTL21200, tested in accordance to IESNA LM-79



2VTL4 48L ADP LP835, 4740 delivered lumens, test no. LTL20367, tested in accordance to IESNA LM-79



Mounting data





Dimensions

All dimensions are inches (centimeters) unless otherwise specified.


System

VTLED N100 (4800L)

VTLED N80 (4800L)


2-lamp T8 2-lamp T5

Specifications Length: 48 (122.0) Width: 24 (61.0) Depth: 4-3/8 (11.1)



Constant Lumen Management

Enabled by the embedded nLight control, the VTLED actively tracks its run-time and manages its light source such that constant lumen output is maintained over the system life. Referred to as lumen management, this feature eliminates the energy waste created by the traditional practice of over-lighting.





An **Cuity**Brands Company

With nlight 80% lumen management input watts start at 38 and gradually increasing to 47 at 50,000 hrs when using 48L system.

LED Energy Comparison to T5/T8

Lamp

type

LED

LED

F32T8

F28T5

Ballast

factor

1.0

1.0

0.88

1.0

Input

watts

47

38

55

58

2VTLED-2X4

Watts saved

by using LED

8

11