

## FEATURES & SPECIFICATIONS

**INTENDED USE** — Provides general illumination in commercial and residential applications. Ideal for use in closets, foyers, hallways, corridors, bedrooms, offices, utility work areas, stairways and more.

**CONSTRUCTION** — This contemporary shaped fixture features a matte white acrylic diffuser and white aluminum housing.

**OPTICS** — Produces the following lumens at 50,000 hours life:

- 2700K 612 lumens
- 3000K 642 lumens
- 4000K 660 lumens

**ELECTRICAL** — Fixture operates at 120 volts, 60 Hz. Standard input = 9.3 watts, 70 lumens per watt.

Works with most standard incandescent dimmers (see list of approved dimmers).

**INSTALLATION** — All mounting hardware included.

**LISTINGS** — CSA certified to US and Canadian standards and listed suitable for damp locations.

U.S. Patent No. D691,763

**WARRANTY** — 5-year limited warranty. Complete warranty terms located at [www.acuitybrands.com/CustomerResources/Terms\\_and\\_conditions.aspx](http://www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx)

Note: Specifications subject to change without notice.

|                |
|----------------|
| Catalog Number |
| Notes          |
| Type           |

Decorative Indoor

# Versi Lite™ 7" LED Flush



HIGH-PERFORMANCE LED



### Specifications

Height: 1-3/4 (4.4)

Width: 7-1/4 (18.4)

All dimensions are inches (centimeters) unless otherwise indicated.

### ORDERING INFORMATION

For shortest lead times, configure product using **standard options (shown in bold)**.

**Example:** FMML 7 840

| Series                     | Size                 | CRI              | Color temperature                       |
|----------------------------|----------------------|------------------|---|
| <b>FMML</b> LED Versi Lite | <b>7</b> 7" diameter | <b>8</b> >80 CRI | <b>40</b> 4000K<br>30 3000K<br>27 2700K |

LIGHTING FACTS

**LED lighting facts**  
A Program of the U.S. DOE

Light Output (Lumens) **612**  
Watts **10.35**  
Lumens per Watt (Efficacy) **59**

Color Accuracy  
Color Rendering Index (CRI) **85**

Light Color  
Correlated Color Temperature (CCT) **2700 (Warm White)**

2700K 3000K 4500K 6500K

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit [www.lightingfacts.com](http://www.lightingfacts.com) for the Label Reference Guide.

Registration Number: NJSM-9ECDFD (7/19/2013)  
Model Number: FMML 7 827  
Type: Surface-mounted fixture (other)

**LED lighting facts**  
A Program of the U.S. DOE

Light Output (Lumens) **642**  
Watts **10.2**  
Lumens per Watt (Efficacy) **63**

Color Accuracy  
Color Rendering Index (CRI) **85**

Light Color  
Correlated Color Temperature (CCT) **3000 (Bright White)**

2700K 3000K 4500K 6500K

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit [www.lightingfacts.com](http://www.lightingfacts.com) for the Label Reference Guide.

Registration Number: NJSM-B45YJQ (7/19/2013)  
Model Number: FMML 7 830  
Type: Surface-mounted fixture (other)

**LED lighting facts**  
A Program of the U.S. DOE

Light Output (Lumens) **659**  
Watts **9.4**  
Lumens per Watt (Efficacy) **70**

Color Accuracy  
Color Rendering Index (CRI) **85**

Light Color  
Correlated Color Temperature (CCT) **4000 (Bright White)**

2700K 3000K 4500K 6500K

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit [www.lightingfacts.com](http://www.lightingfacts.com) for the Label Reference Guide.

Registration Number: NJSM-QSEG7G (8/6/2013)  
Model Number: FMML 7 840 [UPGRADE 07/2013]  
Type: Luminaire - Other

**Suggested Dimmers**

The FMML is designed to operate with most standard Triac Based (Forward Phase-Control or Leading Edge) dimmers and is not compatible with 0-10v dimming systems. The following is a list of dimmers tested and does not imply any guarantee or warranty of compatibility with a particular application. Unlisted dimmers do not imply non-compatibility.

| Manufacturer | Part Number (s) | Manufacturer | Part Number (s) |
|--------------|-----------------|--------------|-----------------|
| Leviton      | 6633P           | Lutron       | DVELV 300P      |
| Leviton      | IPL06           | Lutron       | Skylark 300P    |
| Leviton      | 6674P           | Lutron       | NTELV 300       |
| Leviton      | IPE04           | Lutron       | NLV 600         |
| Leviton      | Trimatron 600W  | Synergy      | ISD 600 I 120   |

PHOTOMETRICS

FMML 7 test no. LTL22758, tested in accordance to IESNA LM-79.

