

**Available finishes**

Use **BOLD** color code in model number

Gloss finishes\*



**WH**  
White



**LA**  
Light Almond



**AL**  
Almond



**IV**  
Ivory



**GR**  
Gray



**BR**  
Brown



**BL**  
Black

Satin finishes\*



**SW**  
Snow



**LS**  
Limestone



**BI**  
Biscuit



**ES**  
Eggshell



**PD**  
Palladium



**TP**  
Taupe



**ST**  
Stone



**BG**  
Bluestone



**PL**  
Plum



**SG**  
Sea Glass



**TQ**  
Turquoise



**GS**  
Goldstone



**DS**  
Desert Stone



**GB**  
Greenbriar



**MS**  
Mocha Stone



**TC**  
Terracotta



**SI**  
Sienna



**HT**  
Hot



**MR**  
Merlot



**MN**  
Midnight



**SS**  
Stainless Steel

\*Coordinating wallplates only available separately. For wallplate information, see pg. 160.

Stainless Steel wallplate includes black plastic trim/adaptor, visible from side. Match with separate Black (BL) or Midnight (MN) controls.

## Dimmer model numbers

### Incandescent/halogen dimmers\*\*

#### Digital fade dimmers

Multi-location/single-pole 120V 600W	MA-600- <b>CC</b> <sup>3</sup>
Multi-location/single-pole 120V 600W	MSC-600M- <b>CC</b> <sup>4</sup>
Multi-location/single-pole 120V 1000W	MA-1000- <b>CC</b> <sup>3</sup>
Multi-location/single-pole 120V 1000W	MSC-1000M- <b>CC</b> <sup>4</sup>

#### eco-dim® digital fade dimmer\*\*

Multi-location/single-pole 120V 600W	MA-600G- <b>EE</b> <sup>2</sup>
---	---------------------------------

eco-dim model guarantees at least 15% energy savings and triples lamp life compared to a standard switch.

#### eco-minder™ digital fade dimmer\*\*

Multi-location/single-pole 120V 600W	MA-600I- <b>EE</b> <sup>2</sup>
---	---------------------------------

eco-minder green LED lights demonstrate 15% or more energy savings compared to a standard switch.

### Magnetic low-voltage dimmers\*\*

#### Digital fade dimmers

Multi-location/single-pole 120V 600VA (450W)	MALV-600- <b>CC</b> <sup>3</sup>
Multi-location/single-pole 120V 600VA (450W)	MSCLV-600M- <b>CC</b> <sup>4</sup>
Multi-location/single-pole 120V 1000VA (800W)	MALV-1000- <b>CC</b> <sup>3</sup>
Multi-location/single-pole 120V 1000VA (800W)	MSCLV-1000M- <b>CC</b> <sup>4</sup>

The stated VA (Volt-Ampere) rating includes the magnetic transformer heat losses and the lamp load. The stated W (Watt) rating is the maximum lamp wattage based on assumed 20% transformer loss.

### Electronic low-voltage dimmers\*

#### Digital fade dimmers

Multi-location/single-pole 120V 600W	MAELV-600- <b>CC</b> <sup>3</sup>
Multi-location/single-pole 120V 600W	MSCELV-600M- <b>CC</b> <sup>4</sup>

Only certain LED drivers are dimmable using an ELV dimmer, for more information visit [www.lutron.com/LED](http://www.lutron.com/LED).

**CC**<sup>3</sup>: Gloss color codes, see pg. 47  
**CC**<sup>4</sup>: Satin color codes, see pg. 47  
**EE**<sup>2</sup>: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA)  
 (Wallplates not included with above, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

\*Requires neutral wire connection.

\*\*Minimum load is 40W/VA.