### Compatible with RadioRA<sub>®</sub> 2 and HomeWorks<sub>®</sub> QS systems

The RF Dimming Module with 0–10 V=== control is a radio frequency (RF) control that operates 0–10 V=== controlled fluorescent ballasts or LED drivers based on input from RadioRA<sub>®</sub> 2 and HomeWorks<sub>®</sub> QS systems.

- 0-10 V---- control link automatically sources or sinks up to 60 mA to third-party fixtures.
- Switches line voltage up to 5 A.
- Configurable high- and low-end trim.
- Various operating voltages available refer to model number chart below for details on voltage requirements.
- Utilizes Lutron<sub>®</sub> Clear Connect<sub>®</sub> RF Technology refer to model number chart below for frequency band data and Lutron<sub>®</sub> system compatibility.
- RadioRA<sub>®</sub> 2 Inclusive or HomeWorks<sub>®</sub> QS software required for system functionality.
- Mounts to an electrical junction box through a 1/2 in (21 mm trade-size) knockout opening.
- Complies with requirements for use in a compartment handling environmental air (plenum) per NEC<sub>®</sub> 2011 300.22(C)(3) (LMJ- model only).

LMJ-5T-DV-B model shown


#### Models

Model Number	Region	Operating Voltage	Frequency Band	Compatible Systems
LMJ-5T-DV-B	U.S.A., Canada, Mexico	120/277 V~	431.0–437.0 MHz	RadioRA <sub>®</sub> 2,
LMK-5T-DV-B	Europe, U.A.E.	220-240 V~	868.125-869.850 MHz	HomeWorks <sub>®</sub> QS

**NOTE:** Contact Lutron for frequency band compatibility for your geographic region if it is not indicated above.


## Specification

Model Number	LMJ-5T-DV-B, LMK-5T-DV-B		
Power	120/277 V~ 50/60 Hz 5 A (LMJ- model) 220–240 V~ 50/60 Hz 5 A (LMK- model)		
Typical Power Consumption	< 1.0 W Typical power test conditions: all loads off		
Regulatory Approvals	UL <sub>®</sub> , UL 2043 Plenum Rated, FCC Approved. Complies with the limits for a Class B device, pursuant to Part 15 of the FCC rules: CSA, IC, NOM (LMJ- model) CE, TRA, CITC (LMK- model)		
Environment	Ambient operating temperature: 32 °F to 104 °F (0 °C to 40 °C) Ambient operating humidity: 0% to 90% humidity, non-condensing. Indoor use only.		
Communications	Operates using Clear Connect <sub>®</sub> RF Technology for reliable wireless communication; refer to model number chart on page 1 for frequency band details. RF range is 30 ft (9 m) from repeaters. Contact Lutron for applications using foil-backed or metallic ceiling tiles.		
Load	<ul> <li>0-10 V= Control Link Maximum Load: 60 mA, source or sink automatically configures. Control link compatible with ANSI E1.3 2001 (R2006), IEC 60929 Annex E.</li> <li>Switched Maximum load: 5 A lighting. No minimum load requirements. Load types include, but are not limited to: MLV, ELV, Incandescent, Magnetic fluorescent, Electronic fluorescent and LEDs.</li> </ul>		
Surge Protection	Tested to withstand surge voltages without damage or loss of operation, in accordance with IEEE C62.41-1991 Recommended Practice on Surge Voltages in Low-Voltage AC Power Circuits.		
Mounting	Mounts to an electrical junction box through a 1/2 in (21 mm) trade-size knockout opening.		
Warranty	www.lutron.com/TechnicalDocumentLibrary/Warranty.pdf www.lutron.com/TechnicalDocumentLibrary/Intl_Warranty.pdf		



#### Dimensions


Dimensions are shown as: in (mm)



Dimensions for all models. Model LMJ-5T-DV-B shown.


# RF Dimming Module with 0–10 V=== Control Wiring Schematics

#### LMJ- model:



#### **Communications**

#### Wired and RF Configuration (RadioRA<sub>®</sub> 2 and HomeWorks<sub>®</sub> QS)



\* In HomeWorks<sub>®</sub> QS systems, use Hybrid Repeaters for range extension. In RadioRA<sub>®</sub> 2, the repeater shown may be either a main repeater (1 required) or auxiliary repeater (up to 4 permitted).