

# DESIGNED FOR USE IN EXPLOSION-PROOF ATMOSPHERES

- Available in 12-24VDC and 120VAC
- Five lens colors
- 10,000 hour strobe tube
- Ceiling mount standard; other options available
- Marine Listed
- Type 4X, IP66 enclosure
- UL and cUL Listed

## Fireball® 2 Explosion-Proof Strobe Warning Light

Model FB2PSTX and FB2PSTX-I

Federal Signal's FB2PSTX explosion-proof strobe light is a compact unit that produces a "lightning bolt" flash of light. Measuring 13.69" (348mm) high and 7.44" (189mm) in diameter, the FB2PSTX is available in 12-24VDC, 24VDC and 120VAC. These strobe lights are well suited for a wide range of explosion-proof warning light applications.

All models are UL and cUL Listed for indoor/outdoor and marine use. This model is UL Listed for Class I, Division 1, Groups C and D; Class I, Division 2, Groups A, B, C and D; Class II, Division 1, Groups E, F and G; Class II, Division 2, Groups F and G; and Class III.

Model FB2PSTX has a self-contained power supply. The copper-free aluminum finned base dissipates heat and ensures long life. The outer dome is made of tempered glass. Polycarbonate inner lenses are available in Amber, Blue, Clear, Green and Red. A rugged ceiling mount fixture is standard; optional wall mounts and dome guards are also available.

The FB2PST-I features a voltage in-rush limiting PCB design that provides greater compatibility with factory automation control systems and less electrical interference with in-rush sensitive devices.

The Model FB2PSTX is suited for any application where a superior visual signal is needed and is especially effective for warning of industrial hazards, process control, status indication or in areas with high ambient noise levels.

|                          |                | Operating                      | Flash Rate/ | Cande             | ela              |
|--------------------------|----------------|--------------------------------|-------------|-------------------|------------------|
| Model                    | Voltage        | Current                        | Minute      | Peak <sup>1</sup> | ECP <sup>2</sup> |
| FB2PSTX-012-024 <u>*</u> | 12-24VDC       | 1.70-0.70 amps                 | 80          | 800,000           | 320              |
| FB2PSTX-I-024 <u>*</u>   | 24VDC          | 0.70 amps<br>(2.0 amp In-rush) | 80          | 800,000           | 320              |
| FB2PSTX-120 <u>*</u>     | 120VAC 50/60HZ | 0.25 amps                      | 80          | 800,000           | 320              |

<sup>\*</sup> Indicates color: (A) Amber, (B) Blue, (C) Clear, (G) Green or (R) Red

### **Hazardous Location Rating:**


| T-Code at Maximum Ambient Temperature, °C |          |          |  |  |
|---|----------|----------|--|--|
| Hazardous Location                        | 40°C     | 65°C     |  |  |
| Class I, Div 1 & 2, Groups C & D          | T6/85°   | T6/85°   |  |  |
| Class I, Div 2, Groups A & B              | T4A/120° | T3C/160° |  |  |
| Class II, Div 1 & 2, Groups E, F & G      | T4/135°  | T4/135°  |  |  |
| Class III                                 | T4/135°  | T4/135°  |  |  |


Peak candela is the maximum light intensity generated by a flashing light during its light pulse




<sup>&</sup>lt;sup>2</sup> ECP (Effective Candela) is the intensity that would appear to an observer if the light were burning steadily

#### **EXPLOSION-PROOF STROBE LIGHT (FB2PSTX/FB2PSTX-I)**







#### **SPECIFICATIONS**

| Lamp Life:             | 10,000 Hours   | 10,000 Hours  |
|------------------------|----------------|---------------|
| Light Source:          | Strobe tube    | Strobe tube   |
| Operating Temperature: | -13°F to 149°F | -25°C to 65°C |
| Net Weight:            | 9.6 lbs.       | 4.35 kg       |
| Shipping Weight:       | 13.1 lbs.      | 5.94 kg       |
| Height:                | 13.69"         | 348.0 mm      |
| Diameter:              | 7.44"          | 189.0 mm      |

#### REPLACEMENT PARTS

| <u>Description</u>    | <u>Part Number</u> |
|-----------------------|--------------------|
| Inner Lens, Amber     | K8550292A-02       |
| Inner Lens, Blue      | K8550292A-01       |
| Inner Lens, Clear     | K8550292A          |
| Inner Lens, Green     | K8550292A-04       |
| Inner Lens, Red       | K8550292A-03       |
| Outer Dome Assembly   | K8550272A-01       |
| PC Assembly, 12-24VDC | K2001202C          |
| PC Assembly, 120VAC   | K200D866G          |
| Strobe Tube           | K8107177A          |
|                       |                    |

#### **HOW TO ORDER**

- · Specify model, voltage and color
- Optional Accessories: Wall Mount (WMXC)
  Pendant Mount (PMXC)
  Dome Guard (DGFBX)
- Please refer to Model Number Index FB2PSTX beginning on page 373