


ORDERING INFORMATION

Order code: 62427
 Description: LED/DL6/13W/30K/RETRO/E26/D/STD
 UPC: 069549624276
 Case quantity: 8



PERFORMANCE DATA

Shape:	Downlight 6"
Wattage (W):	13
Lamp voltage (VAC):	120
Colour temperature (K)**:	3 000
Average life (L70 hours):	50 000
Initial lumens (lm)*:	756
Initial lumens per watt (lm/W):	53
CBCP:	-
CRI:	80
Beam angle:	-
Power factor:	-
Operating temperature range:	-20 °C/-4 °F to 50 °C/122 °F
Base:	E26

*Initial lumens range: +/- 5 %

**Typical colour temperature range: +/- 5 %



LED DOWNLIGHT RETROFIT ADAPTER BAND

62185 LED/ADAPTOR KIT/6IN FLEXLED DOWNLIGHT/4P

COMPATIBLE DIMMER LIST

LUTRON DIMMERS: TGCL-153PH, TG-600PNLH, S-600, LGCL-153PLH, GL-600H, DVCL-153PL, TT-300NLH, DV-603PG, DV-600PH, D-603PH, CN-600P, AY-600P, DVELV-300P, SELV-300P.

OTHER DIMMERS: Leviton IPI06, 6684, 6683, 6633-P, 6613-P.
 Kaoyi KHD-154U
 Legrand DRD4-W, D703-PTC, CDLV703-PW, CD703-PW.

CAUTIONS


- Turn power off before inspection, installation, or removal.
- Disconnect power at fuse or circuit breaker before installing or servicing.
- Risk of electric shock – do not use where directly exposed to water or weather.
- Suitable for use in wet locations – in covered ceilings.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60 Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers and recessed housings.
- Five year limited warranty.
- For housing compatibility list please see installation instructions or visit www.standardpro.com.
- For complete dimmer compatibility and warranty information visit www.standardpro.com.
- Operating temperature: -20°C/-4°F to 40°C/104°F.

NOTES: This device complies with Part 15 of the FCC rules and has been tested and found to comply with the limits for a Class B digital device. This product may cause interference with other devices. If interference occurs, change the location of the product. Any changes or modifications not expressly approved by the manufacturer could void the user's authority to operate the equipment. This RFLD device complies with Canadian ICES-003. LED lamps must be stored, operated under suitable environmental conditions and in accordance with, but not limited to, the latest National Electrical Code, cETLus, CSA and ANSI specifications.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

June 2, 2014

PHOTOMETRY



Lumens Per Zone

Zone	Lumens	% Total
0-10	26.3	3.1%
10-20	75.6	9.0%
20-30	115.3	13.8%
30-40	140.3	16.7%
40-50	147.3	17.6%
50-60	135.1	16.1%
60-70	105.1	12.5%
70-80	63.4	7.6%
80-90	25.3	3.0%

HOUSING COMPATIBILITY LIST

Manufacturer	Model #
Halo	H7ICAT, H7RICAT, H7ICT, H7RICT, H7ICATNB, H7ICTNB, H7T, H7RT, H7TNB, H7TCP, H7UICAT, H7UICAT, H27ICAT, H27RICAT, H27ICT, H27RICT, H27T, H27RT, H5ICAT, H5RICAT, H5T, H5RT, H25ICAT
All-pro	EI500AT, EI500RAT, ET500, ET500R, EI700AT, EI700RAT, EI700ATNB, EI700, EI700R, EI700NB, ET700, ET700R, EI700U, EI700UAT, EI2700AT, EI2700, EI2700R, ET2700, ET2700R
Capri	CR1, PR1, QL1, R9ASIC
Commercial electric	H2, H3, H4, H17, H18
Elco	EL71CA
Juno	ICC22/R/W/S, IC23/W, IC21/R, TC2/R, IC20, IC25/W/S, TC20
Lightolier	1104ICS/ICR/SIC/SICR, 1004ICS/ICR/SIC/SICR, 1104ICX
Lithonia	L7X, L7XP
Prescolite	IBXS
Progress	P87-AT, P86TG
Seagull	11018, 11028, 11118, 11128
Thomas	PS1, PS9RM