

Miniature - Miniatures



Fig.43




Fig.105



Fig.45

3

Line Ligne	Lamp Shape Forme lampe	Volts Tension	Amps (A) Watts Puiss. (W)	Lamp Base Culot Lampe	Internal Code Interne	Filament	Colour Couleur	Avg. Life (Hrs) Vie moy. (Hres)	Lumens	MSCP	L.C.L. Inches - (mm) H.C.L. Pouces - (mm)	M.O.L. Inches - (mm) L.H.T.M. Pouces - (mm)	Diam. inches (mm) Pouces (mm)	Fig. # N° Fig.
------------	------------------------	---------------	---------------------------	-----------------------	-----------------------	----------	----------------	---------------------------------	--------	------	---	---	-------------------------------	----------------

S-6 Bulb Lampe S-6

286	S-6	12	6W	E12	6S6-12VCY	C-2R	Yellow Jaune	1500	55		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
287	S-6	24	6W	E12	6S6-24VCAND	C-2V		1500	55		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
288	S-6	32	6W	E12	6S6-32VCAND	C-2V		1500	50		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
289	S-6	48	6W	E12	6S6-48VCAND	C-7		1500	45		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
290	S-6	50	3W	E12	3S6-50VCAND	C-7		1500	10		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
291	S-6	60	6W	E12	6S6-60VCAND	C-7		1500	45		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
292	S-6	75	3W	E12	3S6-75VCAND	C-7		1500	10		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
293	S-6	75	6W	E12	6S6-75VCAND	C-7A		1500	40		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
294	S-6	125	10W	E12	10S6-125VCAND	C-7A		1500	60		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
295	S-6	125	15W	E12	15S6-125VCAND	C-7A		1500	80		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
296	S-6	125	6W	E12	6S6-125VCAND	C-7A		3000	40		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
297	S-6	125	6W	E12	6S6-125VCAND/IF	C-7A	Frost Givrée	3000	35		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
298	S-6	125	6W	E12	6S6-125VCAND/WH	C-7A	White Blanc	3000	35		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
299	S-6	130	3W	E12	3S6-130VCAND	C-7A		3000	10		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
300	S-6	130	6W	E12	6S6-130VCAND	C-7A		3000	40		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
301	S-6	135	6W	E12	6S6-135VCAND	C-7A		3000	40		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
302	S-6	145	6W	E12	6S6-145VCAND	C-7A		3000	40		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
303	S-6	155	6W	E12	6S6-155VCAND	C-15		1500	40		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
304	S-6	160	6W	E12	6S6-160VCAND	C-7A		1500	35		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
305	S-6	230	10W	E12	10S6-230VCAND	CC-7A		1500	60		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
306	S-6	230	6W	E12	6S6-230VCAND	CC-7A		1500	35		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
307	S-6	280	6W	E12	6S6-280VCAND	CC-7A		1500	20		1 5/16 (33.3)	1 7/8 (48)	3/4 (19.81)	43
308	S-6	24	3W	E14	3S6-24V/E14		Clear Claire	1500				1 7/8 (48)		105
309	S-6	60	10W	E14	10S6/60V		Clear Claire	1500				1 7/8 (48)		105
310	S-6	60	8W	E14	8S6/60V		Clear Claire	1500				1 7/8 (48)		105
311	S-6	120	6W	E17	6S6-120VINT	C-7A		1500	40		1 15/32 (37)	1 13/16 (46)	3/4 (19.81)	45
312	S-6	125	10W	E17	10S6-125VINT	C-7A		1500	60		1 15/32 (37)	1 13/16 (46)	3/4 (19.81)	45