

Miniature - Miniatures



Fig.48



Fig.49

Line Ligne	Lamp Shape Forme lampe	Volts Tension	Amps (A) Watts Puiss. (W)	Lamp Base Culot Lampe	Internal Code Interne	Filament	Couleur Couleur	Avg. Life (Hrs) Vie moy. (Hres)	Lumens	MSCP	L.C.L. Inches - (mm) H.C.L. Pouces - (mm)	M.O.L. Inches - (mm) L.H.T.M. Pouces - (mm)	Diam. inches (mm) Pouces (mm)	Fig. # N° Fig.
---------------	---------------------------------	------------------	---------------------------------	--------------------------------	-----------------------------	----------	--------------------	--	--------	------	--	--	-------------------------------------	-------------------------

S-8 Bulb Lampe S-8

364	S-8	6.7	1.9A	BA15s	1619	C-6U		500	15		1 1/8 (28.6)	2 (51)	1 (25.4)	48
365	S-8	6.8	1.91A	BA15s	87	C-6		300	15		1 1/8 (28.6)	2 (51)	1 (25.4)	48
366	S-8	12	35W	BA15s	A3108	C-6		125	45		1 1/4 (31.8)	2 (51)	1 (25.4)	48
367	S-8	12.5	3A	BA15s	1295	C-2R		300	50		1 1/4 (31.8)	2 (51)	1 (25.4)	48
368	S-8	12.8	1.52	BA15s	1777	C-2R		400		26	1 1/8 (28.6)	2 (51)	1 (25.4)	48
369	S-8	12.8	0.71A	BA15s	91	C-2R		500	10		1 1/8 (28.6)	2 (51)	1 (25.4)	48
370	S-8	12.8	1.04A	BA15s	93	C-2R		700	15		1 1/8 (28.6)	2 (51)	1 (25.4)	48
371	S-8	12.8	1.19A	BA15s	1093	C-2R		1000	15		1 1/8 (28.6)	2 (51)	1 (25.4)	48
372	S-8	12.8	1.35A	BA15s	1161	CC-6		500	22		1 1/4 (31.8)	2 (51)	1 (25.4)	48
373	S-8	12.8	1.44A	BA15s	1141	C-6		500	21		1 1/4 (31.8)	2 (51)	1 (25.4)	48
374	S-8	12.8	1.6A	BA15s	1159	C-6		500	21		1 1/4 (31.8)	2 (51)	1 (25.4)	48
375	S-8	12.8	1.8A	BA15s	1073	C-6		200	32		1 1/4 (31.8)	2 (51)	1 (25.4)	48
376	S-8	12.8	2.1A	BA15s	1156	C-6		1200	32		1 1/4 (31.8)	2 (51)	1 (25.4)	48
377	S-8	12.8	2.25A	BA15s	199	C-6		1200	32		1 1/4 (31.8)	2 (51)	1 (25.4)	48
378	S-8	14	0.51A	BA15s	1095	C-6			4		1 1/4 (31.8)	2 (51)	1 (25.4)	48
379	S-8	28	0.51	BA15s	305	C-2V		300		15	1 1/8 (28.6)	2 (51)	1 (25.4)	48
380	S-8	28	0.51	BA15s	305-IF	C-2V	Frost Givrée	300		15	1 1/8 (28.6)	2 (51)	1 (25.4)	48
381	S-8	28	0.51	BA15s	705	CC-6		900		15	1 1/8 (28.6)	2 (51)	1 (25.4)	48
382	S-8	28	0.61	BA15s	1591-IF	C-2V	Inside Frost Intérieur Givrée	1000		15	1 1/8 (28.6)	2 (51)	1 (25.4)	48
383	S-8	28	0.61	BA15s	1691-IF	2C-2R	Inside Frost Intérieur Givrée	1000		15	1 1/8 (28.6)	2 (51)	1 (25.4)	49
384	S-8	28	0.61	BA15s	1691R	2C-2R	Red Rouge	1000		15	1 1/8 (28.6)	2 (51)	1 (25.4)	49
385	S-8	28	0.64	BA15s	2232	CC-8		2000		18	1 13/16 (30.2)	2 (51)	1 (25.4)	48
386	S-8	28	0.67	BA15s	307	C-2V		300		21	1 1/8 (28.6)	2 (51)	1 (25.4)	48
387	S-8	28	0.67	BA15s	307IF	C-2V	Frost Givrée	300		21	1 1/8 (28.6)	2 (51)	1 (25.4)	48
388	S-8	28	0.67	BA15s	307NR	C-2V	Natural Ruby Rubis naturel	300		21	1 1/8 (28.6)	2 (51)	1 (25.4)	48
389	S-8	28	0.77	BA15s	2233	CC-8		2000		21	1 13/16 (30.2)	2 (51)	1 (25.4)	48
390	S-8	28	0.8	BA15s	1665	C-2V		1000		21	1 1/8 (28.6)	2 (51)	1 (25.4)	48