

Decorator Devices Specification Grade Dead Front GFCI

20A, 125VAC

Features

- Rated as a 1½ HP motor control switch.
- Meets 2006 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to the load is disconnected.
- Prevents line-load reversal miswire: no power to the load or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red lamp).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Specifications

- Supply Voltage: 125VAC, 60 Hz.
- Supply Voltage Range: 102-132 VAC.
- Trip Threshold: 5± 1mA.
- Trip Time: 0.025 sec., nominal per UL Standard.
- 20 Amp feed-thru capacity.



2085-W



Catalog Number	Rating		Color	3rd Party Compliance	
	A.	VAC		UL943 C22.2 No. 144	UL508 C22.2 No. 14
Specification Grade Dead Front GFCI – 1½ HP Motor Control Rating					
2085-I	20	125	Ivory	•	•
2085-W	20	125	White	•	•
2085-BK	20	125	Black	•	•
2085-LA	20	125	Light Almond	•	•

Available Spring 2006.

For Configurable Solutions, see Page U-1.

Catalog Number	Description
Accessories – GFCIs	
1594-TPAI	7.0 cu. in. Extension Ring, Ivory
1594-TPAW	7.0 cu. in. Extension Ring, White
1594-TPA	7.0 cu. in. Extension Ring, Brown
1594-TPALA	7.0 cu. in. Extension Ring, Light Almond