

Straight Blade Receptacles Specification Grade Decorator Receptacles


15 & 20A, 125 & 250V

Pass & Seymour



Features

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 – #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.



26242I

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL UL498	FSUL WC596	cUL/CSA
Duplex Receptacles Back & Side Wire						
26652I	15 250	Ivory	6-15R	•	•	•
26652W	15 250	White	6-15R	•	•	•
26652	15 250	Brown	6-15R	•	•	•
26652GRY	15 250	Gray	6-15R	•	•	•
26652BK	15 250	Black	6-15R	•	•	•
26652RED	15 250	Red	6-15R	•	•	•
26852I	20 250	Ivory	6-20R	•	•	•
26852W	20 250	White	6-20R	•	•	•
26852	20 250	Brown	6-20R	•	•	•
26852GRY	20 250	Gray	6-20R	•	•	•
26852BK	20 250	Black	6-20R	•	•	•
26852RED	20 250	Red	6-20R	•	•	•
26852LA	20 250	Light Almond	6-20R	•	•	•
Duplex Receptacles Side Wire Only						
26242I	15 125	Ivory	5-15R	•	•	•
26242W	15 125	White	5-15R	•	•	•
26242	15 125	Brown	5-15R	•	•	•
26242GRY	15 125	Gray	5-15R	•	•	•
26242BK	15 125	Black	5-15R	•	•	•
26242RED	15 125	Red	5-15R	•	•	•
26342I	20 125	Ivory	5-20R	•	•	•
26342W	20 125	White	5-20R	•	•	•
26342	20 125	Brown	5-20R	•	•	•
26342GRY	20 125	Gray	5-20R	•	•	•
26342BK	20 125	Black	5-20R	•	•	•
26342RED	20 125	Red	5-20R	•	•	•

2 Pole, 3 Wire



NEMA
5-15R



NEMA
5-20R



NEMA
6-15R



NEMA
6-20R

For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.