


Pass & Seymour



Straight Blade Receptacles Hard Use Specification Grade Receptacles

15A, 125V, 125/250 & 250V; 20A, 125 & 125/250V




52621

Features	
<ul style="list-style-type: none"> Corrosion-resistant, plated and tabbed steel strap is locked in to face and back body to resist pulling away from face/body assembly. .032 inch thick, brass, triple-wipe power contacts for lasting retention. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Impact-resistant nylon face. 	<ul style="list-style-type: none"> 8 hole internal screw-pressure-plate back wire terminals accept #10 – 14 AWG solid or stranded copper or copper-clad conductors. Terminal compartments isolated from each other for positive conductor containment. Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				UL498	FSUL WC596	CS C22.2 No. 42
Duplex Receptacles Back & Side Wire						
52621	15 125	Ivory	5-15R	•	•	•
5262W	15 125	White	5-15R	•	•	•
5262	15 125	Brown	5-15R	•	•	•
5262GRY	15 125	Gray	5-15R	•	•	•
5262BK	15 125	Black	5-15R	•	•	•
NEW 5262RED	15 125	Red	5-15R	•	•	•
5262LA	15 125	Light Almond	5-15R	•	•	•
NEW 5262BL	15 125	Blue	5-15R	•	•	•
5362I	20 125	Ivory	5-20R	•	•	•
5362W	20 125	White	5-20R	•	•	•
5362	20 125	Brown	5-20R	•	•	•
5362GRY	20 125	Gray	5-20R	•	•	•
5362BK	20 125	Black	5-20R	•	•	•
NEW 5362RED	20 125	Red	5-20R	•	•	•
5362LA	20 125	Light Almond	5-20R	•	•	•
5362BL	20 125	Blue	5-20R	•	•	•
5652I	15 250	Ivory	6-15R	•	•	•
5652	15 250	Brown	6-15R	•	•	•
5652BK	15 250	Black	6-15R	•	•	•
5652LA	15 250	Light Almond	6-15R	•	•	•
Duplex Receptacles Side Wire						
5642I	15 250	Ivory	6-15R	•	•	•
5642	15 250	Brown	6-15R	•	•	•
NEW 5290I	15 125/250	Ivory	5/6-15R	•	•	•
5290	15 125/250	Brown	5/6-15R	•	•	•
5890I	20 125/250	Ivory	5/6-20R	•	•	•
5890W	20 125/250	White	5/6-20R	•	•	•
5890	20 125/250	Brown	5/6-20R	•	•	•

2 Pole, 3 Wire



For Configurable Solutions, see Page U-1.

All devices listed on this page conform to NEMA WD-1 and WD-6.