

Decorator Devices Specification Grade Hallway Lights 20A, 120/125VAC

Ordering Information




Catalog Number	Rating A. VAC	Light Output in FCD*	Color	NEMA Config. No.
Hallway Light & Single Receptacle				
PS8HWL-I	20 120/125	1.46	Ivory	5-20R
PS8HWL-W	20 120/125	1.46	White	5-20R
PS8HWL-LA	20 120/125	1.46	Light Almond	5-20R
Enhanced Full Hallway Light with Light Sensor				
TMHWL-ECC	— 120	4.25	Clear	—
Enhanced Full Hallway Light without Light Sensor				
TMHWL-ENSCC	— 120	4.25	Clear	—
Full Hallway Light for use with P&S Metal Louver Plates**				
TMHWL-LOUVCC	— 120	0.57	Clear	—



NEMA
5-20R

*FCD = Foot Candle Distance. 1 Lumen = 1 FCD.

**See Louver Plates information below.

Description	Catalog Number	Material
Louver Plates		
One Gang Horizontal 	SB760 SS760 SS760-I SS760-W SS760-LA	Brass 302 Stainless Steel 302 Stainless Steel Painted Ivory 302 Stainless Steel Painted White 302 Stainless Steel Painted Light Almond
One Gang Vertical 	SB771 SS771 SS771-I SS771-W SS771-LA SS771-X SS771-GRY	Brass 302 Stainless Steel 302 Stainless Steel Painted Ivory 302 Stainless Steel Painted White 302 Stainless Steel Painted Light Almond 302 Stainless Steel Painted Brown 302 Stainless Steel Painted Gray
Two Gang Vertical 	SS772	302 Stainless Steel

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Decorator Devices Specification Grade Hallway Lights 20A, 120/125VAC

Pass & Seymour



Technical Specifications

3rd Party Compliance	
PS8HWL:	cULus Listed, File Number E140596, Standard UL498.
TMHWL:	cULus Listed, Standard UL1598.


Performance	
Electrical	
Dielectric Voltage	Withstands 1500V minimum
Maximum Working Voltage	125V
Maximum Continuous Current	20A
Temperature Rise	Maximum 30°C after 50 cycles at 150% of rated current
Mechanical	
Terminal Accommodation	#14 AWG – #10 AWG
Product Identification	Amperage, Voltage, 3rd Party Compliance
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +50°C, minimum -40°C (without impact)

Materials			
Face	Polycarbonate	Terminal Screws	#8 Tri-Drive Brass
Back Body	Polycarbonate	Ground Screw	#8 Hex Tri-Drive Brass
Line Contacts	*.031 688 Brass	Mounting Screws	Tri-Drive Steel
Mounting Strap	.047 Steel	Lens	Polycarbonate
Ground Contacts	*.040 260 Brass	Illuminating Lamp	2 LED
Pressure Plate	.031 260 Brass		


*For Hallway Light and Single Receptacle P&S Cat.# PS8HWL only.

Warranty

1 Year



Dimensions for
Hallway Light and
Single Receptacle




Dimensions for
Full Hallway Light


PS8HWL, TMHWL

Specification grade devices offered in a sleek style for unique applications.

These versatile, innovative devices provide an easily integrated, high-value way to add safety wherever low-level lighting is needed. Choose our combination Hallway Light and Single Receptacle – or our Full Hallway Light. Both provide bright, extraordinary long-lasting illumination plus energy savings, thanks to 1/4 watt LED lighting.



Features & Benefits



Field Uses/Vertical Markets

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging
- Multiple Dwelling