

**P&S** **GFCI**  
**Receptacles**



MEETING THE 2006 UL® REQUIREMENTS  
WITH OUR TOUGHEST GFCI EVER.

**Pass & Seymour**

■ THE ONE THAT WORKS FOR YOU®



## P&S innovations — from the **first GFCI** receptacle to SafeLock™ Protection.

**The broadest  
range of  
ground-fault  
protection.**


In 1971, we introduced the first GFCI receptacle. Soon, our invention was preventing injuries and saving lives throughout North America.

That spirit of innovation and commitment to safety continues. In 2006, we introduced our most advanced GFCIs ever. They don't just meet the new 2006 UL® GFCI requirements — they exceed them to provide optimum safety and durability.

P&S GFCI receptacles provide more complete protection against electrical shock. In addition to disconnecting power to the receptacle if there's a ground fault, they also deny power if the receptacle is miswired or if it fails. Power to a GFCI receptacle without protection is an unsafe condition. And our GFCIs prevent it.

Today, you'll find P&S innovation and safety throughout a broad range of GFCI products — products that offer new versatility, save installation time and solve problems. And products that continue a proud safety tradition that we began over 30 years ago.

Choose P&S GFCI products for innovation — and for all your ground-fault protection needs.



**Where a safety revolution began:  
the first GFCI receptacle — created  
by P&S in 1971.**

Innovative features **add safety, speed installation** and **ensure durability.**



**Nickel post-plated mounting strap** for superior corrosion resistance.

**High-impact-resistant, thermoplastic construction** for superior strength and durability.

**Captive screws for easier installation** — won't get lost.



**1/4" thinner than competitors' GFCIs** to leave more room in the box.

2095-LA

**Ground terminal back-wire clamp** for fast installation.

**Trip indicator light** makes it easy to identify a tripped condition.

**Two back-wire holes per termination** add wiring flexibility, eliminate pigtailing and save box space.

**Side or internal screw-pressure-plate back-wire termination** speeds installation; takes #14-#10 AWG stranded or solid, copper or copper-clad conductors.

**Patented SafeLock™ Protection for more safety** — shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails.



**The most durable GFCI available** — exceeds UL943 voltage surge requirements; survives 100X the required UL 3kA/6kV voltage surge test cycles.



**All P&S GFCI Duplex Receptacles meet Fed Spec requirements** — FSUL Listed (Federal Specification WC596).

**Meets 2006 UL® requirements.**





1595-NTLLACC4

The first LED Nightlight/GFCI Combination — **perfect for bathrooms.**

- Sealed nightlight with Lexan® lens prevents tampering
- LED illumination with a 20-year life expectancy means no bulbs to change
- Photocell turns nightlight on in dark, off in daylight

Switch/GFCI Combination Devices — **ideal for remodeling.**

- User-preferred up-and-down switching
- Available in one- and two-switch models
- More function in a single-gang box or space
- 15A single-pole switches rated for 1/2 HP motor loads — perfect for bath and kitchen vent fans or garbage disposals



1595-SWTLACC4



1595-2SWTLACC4





1595-SLA

The Auto-Ground GFCI **speeds commercial-building installation.**

- Rugged, specification grade design fights callbacks and ensures durability
- Standard auto-ground clip ensures solid ground connection to metal box

Illuminated GFCI **makes spotting use of back-up power easy.**

- Light on when power is available
- LED turns off when unit has tripped or power has failed



2095-HGLAL

The first Tamper-Resistant GFCI **helps keep children safe.**

- Patented internal sliding shutters prevent children from sticking objects into the receptacle
- UL®-Listed shutter system



1595-TRLACC4

Portable GFCI **adds safety on the job.**

- Ideal for power tools, portable signs, pressure washers, grounds-keeping equipment and wet vacuums
- Rugged polycarbonate housing resists impacts
- Available in a wide variety of 15A and 20A models



1594-TC2M

**3rd Party Compliance**

Catalog Number	Rating A. VAC	Colors	Description	NEMA	3rd Party Compliance			
					UL943/C22.2 No. 144	UL498/C22.2 No. 42	FSUL/ WC596	UL20/C22.2 No. 111
<b>GFCI Receptacles</b>								
1595-*	15 125	Brown, I, LA, W, BK, GRY, RED	Spec Grade 15 Amp Duplex	5-15R	•	•	•	
2095-*	20 125	Brown, I, LA, W, BK, GRY, RED	Spec Grade 20 Amp Duplex	5-20R	•	•	•	
2085-*	20 125	I, LA, W, BK	Spec Grade 20 Amp Dead Front		•	(UL508/C22.2 No. 14)		
1595-HG*	15 125	Brown, I, LA, W, GRY, RED	Hospital Grade 15 Amp Duplex	5-15R	•	•	•	
2095-HG*	20 125	Brown, I, LA, W, GRY, RED	Hospital Grade 20 Amp Duplex	5-20R	•	•	•	
<b>Auto-Ground GFCI Receptacles</b>								
1595-S*	15 125	I, LA, W	Spec Grade 15 Amp Duplex	5-15R	•	•	•	
2095-S*	20 125	I, LA, W	Spec Grade 20 Amp Duplex	5-20R	•	•	•	
<b>Decorator Switch/GFCI Combination Receptacles</b>								
1595-SWT*CC4	15 120	I, LA, W, BK	Spec Grade 15 Amp Single-Pole Switch	5-15R	•	•		•
Switch: GFCI:	15 125							
1595-2SWT*CC4	15 120	I, LA, W, BK	Spec Grade 15 Amp Two Single-Pole Switches	5-15R	•	•		•
2 Switches: GFCI:	15 125							
<b>Decorator LED Nightlight/GFCI Combination Receptacles</b>								
1595-NTL*CC4	15 125	I, LA, W, BK	Spec Grade 15 Amp	5-15R	•	•	•	
2095-NTL*	20 125	I, LA, W, GRY, RED	Spec Grade 20 Amp	5-20R	•	•	•	
1595-HGNTL*	15 125	Brown, I, LA, W, GRY, RED	Hospital Grade 15 Amp	5-15R	•	•	•	
2095-HGNTL*	20 125	Brown, I, LA, W, GRY, RED	Hospital Grade 20 Amp	5-20R	•	•	•	
<b>Tamper-Resistant GFCI Receptacles</b>								
1595-TR*CC4	15 125	I, LA, W, BK	Spec Grade 15 Amp Duplex	5-15R	•	•	•	
1595-HGTR*	15 125	Brown, I, LA, W, GRY, RED	Hospital Grade 15 Amp Duplex	5-15R	•	•	•	
2095-TR*	20 125	Brown, I, LA, W, BK, GRY, RED	Spec Grade 20 Amp Duplex	5-20R	•	•	•	
2095-HGTR*	20 125	Brown, I, LA, W, GRY, RED	Hospital Grade 20 Amp Duplex	5-20R	•	•	•	
<b>Illuminated GFCI Receptacles</b> Light is on when power is available								
1595-*L	15 125	Brown, I, LA, W	Spec Grade 15 Amp Duplex	5-15R	•	•	•	
2095-*L	20 125	Brown, I, LA, W, GRY	Spec Grade 20 Amp Duplex	5-20R	•	•	•	
1595-HG*L	15 125	Brown, I, LA, W, GRY, RED	Hospital Grade 15 Amp Duplex	5-15R	•	•	•	
2095-HG*L	20 125	Brown, I, LA, W, GRY, RED	Hospital Grade 20 Amp Duplex	5-20R	•	•	•	



1595-W




1595-2SWTWCC4



1595-NTLWCC4



1595-TRWCC4



**\* Color Designation**

—	Brown	BK	Black
I	Ivory	GRY	Gray
LA	Light Almond	RED	Red
W	White		

For additional technical or application-specific information, call 800-223-4185 or visit our website at [www.passandseymour.com](http://www.passandseymour.com). We're eager to put our expertise to work for you.

**USA**  
P.O. Box 4822  
Syracuse, NY 13221-4822  
800-611-7277

**Canada**  
570 Applewood Crescent  
Vaughan, ON, L4K 4B4  
905-738-9195

**Distributed by:**

**Pass & Seymour**