



# Decorator Devices TradeMaster® & Specification Grade GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1594-I



2094-I

### Features

- Meets new 2003 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: If miswired, GFCI cannot be RESET.
- Trip Indicator Light (red lamp).
- Improved resistance to surge, corrosion and electrical power line noise.
- Side or internal screw-pressure-plate back wire with #14 – #10 AWG solid or stranded copper wire.
- Line and load terminations supplied backed out and ready-to-wire.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Two back wire holes per terminal.
- Ultrasonic welding of face to back body.
- Button colors match the device face.
- Ground screw with a wire guide channel.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching nylon wall plate.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A. VAC		Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>NEW TradeMaster/Spec Grade 15 Amp Duplex GFCI</b>							
1594-I	15	125	Ivory	5-15R	•	•	•
1594-W	15	125	White	5-15R	•	•	•
1594	15	125	Brown	5-15R	•	•	•
1594-GRY	15	125	Gray	5-15R	•	•	•
1594-BK	15	125	Black	5-15R	•	•	•
1594-LA	15	125	Light Almond	5-15R	•	•	•
<b>NEW TradeMaster/Spec Grade 15 Amp 20 Pack Duplex GFCI</b>							
1594-I20	15	125	Ivory	5-15R	•	•	•
1594-W20	15	125	White	5-15R	•	•	•
1594-GRY20	15	125	Gray	5-15R	•	•	•
1594-LA20	15	125	Light Almond	5-15R	•	•	•
<b>NEW Specification Grade 20 Amp Duplex GFCI</b>							
2094-I	20	125	Ivory	5-20R	•	•	•
2094-W	20	125	White	5-20R	•	•	•
2094	20	125	Brown	5-20R	•	•	•
2094-GRY	20	125	Gray	5-20R	•	•	•
2094-BK	20	125	Black	5-20R	•	•	•
2094-LA	20	125	Light Almond	5-20R	•	•	•
<b>NEW Specification Grade 20 Amp 20 Pack Duplex GFCI</b>							
2094-I20	20	125	Ivory	5-20R	•	•	•
2094-W20	20	125	White	5-20R	•	•	•




NEMA  
5-15R




NEMA  
5-20R

# Straight Blade Devices TradeMaster® & Specification Grade GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC



1594-I



2094-I

### Features

- Meets new 2003 UL requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: If miswired, GFCI cannot be RESET.
- Trip Indicator Light (red lamp).
- Improved resistance to surge, corrosion and electrical power line noise.
- Side or internal screw-pressure-plate back wire with #14 – #10 AWG solid or stranded copper wire.
- Line and load terminations supplied backed out and ready-to-wire.
- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Two back wire holes per terminal.
- Ultrasonic welding of face to back body.
- Button colors match the device face.
- Ground screw with a wire guide channel.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching nylon wall plate.

### Specifications

- Supply Voltage: 125VAC, 60 Hz
- Supply Voltage Range: 102-132 VAC
- Trip Threshold: 5± 1mA
- Trip Time: 0.025 sec., nominal per UL Standard
- 20 Amp feed-thru capacity

Catalog Number	Rating A.	VAC	Color	NEMA Config. No.	3rd Party Compliance		
					UL943 C22.2 No. 144	UL498 C22.2 No. 42	FSUL WC596
<b>TradeMaster/Spec Grade 15 Amp Duplex GFCI</b>							
1594-I	15	125	Ivory	5-15R	•	•	•
1594-W	15	125	White	5-15R	•	•	•
1594	15	125	Brown	5-15R	•	•	•
1594-GRY	15	125	Gray	5-15R	•	•	•
1594-BK	15	125	Black	5-15R	•	•	•
1594-LA	15	125	Light Almond	5-15R	•	•	•
<b>TradeMaster/Spec Grade 15 Amp 20 Pack Duplex GFCI</b>							
1594-I20	15	125	Ivory	5-15R	•	•	•
1594-W20	15	125	White	5-15R	•	•	•
1594-GRY20	15	125	Gray	5-15R	•	•	•
1594-LA20	15	125	Light Almond	5-15R	•	•	•
<b>Specification Grade 20 Amp Duplex GFCI</b>							
2094-I	20	125	Ivory	5-20R	•	•	
2094-W	20	125	White	5-20R	•	•	
2094	20	125	Brown	5-20R	•	•	
2094-GRY	20	125	Gray	5-20R	•	•	
2094-BK	20	125	Black	5-20R	•	•	
2094-LA	20	125	Light Almond	5-20R	•	•	
<b>Specification Grade 20 Amp 20 Pack Duplex GFCI</b>							
2094-I20	20	125	Ivory	5-20R	•	•	
2094-W20	20	125	White	5-20R	•	•	



NEMA 5-15R



NEMA 5-20R

# GFCIs with SafeLock™ Protection

## New GFCIs with SafeLock Protection

If critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.

Available in trilingual (English, French, and Spanish) individual packages.



**Trip indicator light** makes it easy to identify tripped condition.

**Side or internal screw-pressure-plate back wire termination** takes #14 - #10 AWG stranded or solid, copper or copper-clad conductors.

**Grooved channel to ground screw** allows for fast installation of ground wires.

**Extra-long strap for better sheet rock contact** eliminates "floaters" yet takes standard wall plate.


**High-impact-resistant, thermoplastic construction** for superior strength and durability.

**Two back wire holes per termination** add wiring flexibility, eliminate pigtailing, and save box space.

**Prevents line-load reversal miswire:** If miswired, GFCI can not be RESET.

**Line and load terminals backed out, ready-to-wire.**

**Improved resistance to surge, corrosion and electrical power line noise.**



### 1594-LA

#### 3RD PARTY COMPLIANCE

Catalog Number	Rating		Color	NEMA Config. No.	UL US		FSUL
	A.	VAC			UL943 C22.2 No. 144	UL498 C22.2 No. 42	
<b>TradeMaster™ /Spec Grade 15 Amp Duplex GFCI</b>							
1594-I	15	125	Ivory*	5-15R	•	•	•
1594-W	15	125	White*	5-15R	•	•	•
1594	15	125	Brown	5-15R	•	•	•
1594-GRY	15	125	Gray*	5-15R	•	•	•
1594-BK	15	125	Black	5-15R	•	•	•
1594-LA	15	125	Light Almond*	5-15R	•	•	•


<b>Specification Grade 20 Amp Duplex GFCI</b>							
Catalog Number	A.	VAC	Color	NEMA Config. No.	UL US	UL US	FSUL
2094-I	20	125	Ivory*	5-20R	•	•	•
2094-W	20	125	White*	5-20R	•	•	•
2094	20	125	Brown	5-20R	•	•	•
2094-GRY	20	125	Gray	5-20R	•	•	•
2094-BK	20	125	Black	5-20R	•	•	•
2094-LA	20	125	Light Almond	5-20R	•	•	•

<b>Hospital Grade 15 Amp Duplex GFCI</b>							
Catalog Number	A.	VAC	Color	NEMA Config. No.	UL US	UL US	FSUL
1594-HGI	15	125	Ivory	5-15R	•	•	•
1594-HGW	15	125	White	5-15R	•	•	•
1594-HG	15	125	Brown	5-15R	•	•	•
1594-HGGRY	15	125	Gray	5-15R	•	•	•
1594-HGRED	15	125	Red	5-15R	•	•	•
1594-HGLA	15	125	Light Almond	5-15R	•	•	•

<b>Hospital Grade 20 Amp Duplex GFCI</b>							
Catalog Number	A.	VAC	Color	NEMA Config. No.	UL US	UL US	FSUL
2094-HGI	20	125	Ivory	5-20R	•	•	•
2094-HGW	20	125	White	5-20R	•	•	•
2094-HG	20	125	Brown	5-20R	•	•	•
2094-HGGRY	20	125	Gray	5-20R	•	•	•
2094-HGRED	20	125	Red	5-20R	•	•	•
2094-HGLA	20	125	Light Almond	5-20R	•	•	•

#### 3RD PARTY COMPLIANCE

Catalog Number	Rating		Color	UL US	
	A.	VAC		UL943 C22.2 No. 144	UL508 C22.2 No. 14
<b>Specification Grade Dead Front GFCI - 1 1/2 HP Rating</b>					
2084-IN	20	125	Ivory	•	•
2084-WN	20	125	White	•	•
2084-BKN	20	125	Black	•	•
2084-LAN	20	125	Light Almond	•	•



\* Also available in 20 Packs. Add "20" to end of Catalog Number.

For additional technical or application-specific information - call 800-223-4185 or visit our Web site at [www.passandseymour.com](http://www.passandseymour.com). We're eager to put our expertise to work for you.

**Distributed by:**

**Pass & Seymour**  
**legrand®**  
 The one that works for you.®

[www.passandseymour.com](http://www.passandseymour.com)

BR1129 10/02

# Technical Specifications

## TradeMaster® & Specification Grade

### GFCI Receptacles with SafeLock™ Protection

2 Pole, 3 Wire Grounding 15 & 20A, 125VAC


Pass & Seymour  


**Typical Specifications**

Manufacturer's Identification: Pass & Seymour/Legrand 1594  
 Description: Straight Blade Duplex GFCI Receptacle  
 Type: 2 Pole, 3 Wire Grounding  
 Rating: 20A, 125VAC Feed Thru, 15A, 125VAC or 20A, 125VAC FACE  
 3rd Party Compliance: cULus Listed, File Number E42190; Standard UL498, Attachment Plugs and Receptacles UL943 GFCIs. Federal Specification WC596 (15A). Standard CSA-C22.2 No. 42, General-Use Receptacles, CSA-C22.2 No. 144 GFCIs. Conforms to NEMA WD-1, WD-6.



Catalog Number	Color	Rating	NEMA Configuration No.
<input type="checkbox"/> 1594-I	Ivory	15A 125VAC	5-15R
<input type="checkbox"/> 1594-W	White	15A 125VAC	5-15R
<input type="checkbox"/> 1594	Brown	15A 125VAC	5-15R
<input type="checkbox"/> 1594-GRY	Gray	15A 125VAC	5-15R
<input type="checkbox"/> 1594-RED	Red	15A 125VAC	5-15R
<input type="checkbox"/> 1594-LA	Light Almond	15A 125VAC	5-15R
<input type="checkbox"/> 1594-I20	Ivory	15A 125VAC	5-15R
<input type="checkbox"/> 1594-W20	White	15A 125VAC	5-15R
<input type="checkbox"/> 1594-LA20	Light Almond	15A 125VAC	5-15R
<input type="checkbox"/> 2094-I	Ivory	20A 125VAC	5-20R
<input type="checkbox"/> 2094-W	White	20A 125VAC	5-20R
<input type="checkbox"/> 2094	Brown	20A 125VAC	5-20R
<input type="checkbox"/> 2094-GRY	Gray	20A 125VAC	5-20R
<input type="checkbox"/> 2094-RED	Red	20A 125VAC	5-20R
<input type="checkbox"/> 2094-LA	Light Almond	20A 125VAC	5-20R
<input type="checkbox"/> 2094-I20	Ivory	20A 125VAC	5-20R
<input type="checkbox"/> 2094-LA20	Light Almond	20A 125VAC	5-20R



1594 Series



Performance			
<b>Electrical</b>			
Dielectric	Withstands 1500V minimum		
Trip Level	4 to 6 mA		
Trip Time	.025 Second Nominal		
Frequency	60 Hz		
Voltage	125VAC		
Voltage Range	102-132VAC		
Operating Temp.	-35°C to +66°C		
Maximum Humidity	95%		
<b>Mechanical</b>			
Terminal Identification	Terminals identified in accordance with UL498 (Hot, White, Green)		
Terminal Accommodation	#14 – #10 AWG solid or stranded copper conductor only		
Product Identification	Ratings are a permanent part of device		
<b>Environmental</b>			
Flammability	UL94 V2		
<b>Materials</b>			
Face	Nylon	Terminal Screws	Steel # 8 – 32
Body	Nylon	Hex Head Grounding Screw	Steel (Green)
Contacts	.03" Brass (.8)	Flat Hd. Mtg. Screws	Steel-Zinc-Plated
Mounting Straps	.05" Zinc-Plated Steel (1.3)	Test/Reset Buttons	Nylon

All devices listed on this page conform to NEMA WD-1.