Designer wallplate opening Skylark dimmers and fan controls



Shown actual size: Skylark dimmer and 1-gang Claro wallplate in White (WH).

Product family features

- Rocker switch returns light to your favorite light level
- Slide up to brighten, down to dim (adjust light to suit any activity)
- eco-dim
 model available
- 1000 W preset dimmers have voltage compensation which maintains stable light levels, despite line voltage variations
- 100% factory tested
- Coordinating Claro® and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates, see pg. 155

Control types

b Single-pole (one location)

 Image: Second state
 3-way or 4-way (two or more locations)

Direct load type compatibility

- Incandescent/halogen lighting
- Electronic low-voltage lighting
- ∠ Fluorescent lighting
- LED lighting
- Dimmable compact fluorescent
- 🔀 Ceiling fans
- ℅ Ceiling fan/lights

Load type requiring load interface

Neon/cold cathode lighting

Lighting load interfaces may be applicable for some additional load type, voltage and capacity combinations.

For additional information, see pg. 174.

Available finishes

Use **BOLD** color code in model number (Example: S-600P- \underline{GR}) Gloss finishes*

i.

T

 \Box

<u>AL</u> Almond







WH White

<u>GR</u> Gray

LA Light Almond





Brown

BL Black



<u>SS</u> Stainless Steel

*Coordinating wallplates only available separately. For wallplate information, see pg. 160. Stainless Steel wallplate includes black plastic trim/adapter, visible from side. Match with separate Black (BL) controls.

Dimmers

Slide-to-off dimmers



• Slide up to on/brighten; down to dim/off



- Dimmers with on/off switch and locator light
 - Rocker switch turns on/off
 - Slide up to brighten;
 down to dim
 - Includes amber locator light

Dimmers with on/off switch



- Rocker switch turns on/off
- Slide up to brighten; down to dim
- eco-dime model guarantees at least 15% energy savings compared to a standard switch

Fan and fan/light controls

Slide-to-off fan controls



- Slide up to on/increase speed;
 down to decrease/off
- 3-quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Quiet 3-speed designed to
 prevent motor hum

Dual devices

Dual slide-to-off dimmers (two loads)



fui lip

11

Tref

- Dimmers (left/right)
- Slide up to on/brighten; down to dim/off

Slide-to-off fan controls with on/off light switch

	1		
1	T	1	
		1	P.

Fan control (top)

- Slide up to on/increase fan speed; down to decrease fan speed/off
- 3-quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Quiet 3-speed designed to
 prevent motor hum

Switch (bottom)

Rocker switch turns light on/off

Dual slide-to-off fan control and dimmer

Fan control (left)


- Slide up to on/increase speed;
 down to decrease/off
- 3-quiet fan speeds for increased comfort
- Quiet 3-speed designed to
 prevent motor hum
- Fully variable available for use with multiple paddle or exhaust fans

Dimmer (right)


 Slide up to on/brighten; down to dim/off

Connections overview





Control types (for 2 or more locations) Dim from one location, switch from the others



For more information on ballasts, visit **www.lutron.com/ballasts**. For more information on LED drivers, visit **www.lutron.com/LED**.

*For illustration purposes only. Consult model number pages for specific voltage and capacity information.

Dimmer model numbers

Incandescent/halogen dimmers

Dimmers with on/off switch	
Single-pole	S-600P- <u>CC</u> ³
120V 600W	
Single-pole	S-10P- <u>CC</u> ³
120V 1000W	
3-way	S-603P- CC ³
120V 600W	
3-way	S-103P- <u>CC</u> 3
120V 1000W	

eco-dime dimmer with on/off switch

3-way/single-pole	S-603PG- <u>EE</u> 2
120V 600W	
and dim model quarantees at	loast 15% operav

eco-dim model guarantees at least 15% energy savings compared to a standard switch.

Dimmers with on/off switch and locator light

Single-pole	S-600PNL- <u>CC</u> 3
120V 600W	
Single-pole	S-10PNL- CC ³
120V 1000W	
3-way	S-603PNL- CC 3
120V 600W	
3-way	S-103PNL- CC 3
120V 1000W	

Slide-to-off dimmers

Single-pole	S-600- <u>CC</u> 3
120V 600W	
Single-pole	S-1000- <u>CC</u> ³
120V 1000W	

For dual slide-to-off dimmers (two loads), see page 111.

Dimmers with on/off switch	
Single-pole	SLV-600P- CC ³
120V 600VA (450W)	
3-way	SLV-603P- CC 3
120V 600VA (450W)	
The stated VA (Volt-Ampere) rati	ng includes
the magnetic transformer heat losses and the	
lamp load. The stated W (Watt) rating is the	
maximum lamp wattage based of	on assumed
20% transformer loss.	

Electronic low-voltage dimmers*

Dimmers with on/off switch

Single-pole	SELV-300P- <u>CC</u> 3
120V 300W	
3-way	SELV-303P- <u>CC</u> 3
120V 300W	
Certain LED drivers are dimmable using an	
ELV dimmer, for more information	n, visit

www.lutron.com/LED.

<u>CC</u>³: Gloss color codes, see pg. 105 <u>EE</u>²: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA)

(Wallplates not included, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

*Requires neutral wire connection.

Dimmer model numbers

2 3-wire fluorescent dimmers*

Dimmers with on/off	switch
Single-pole	SF-10P- CC ³
120V 8A	
Single-pole	SF-12P-277- CC 3
277V 6A	
3-way	SF-103P- <u>CC</u> 3
120V 8A	
3-way	SF-12P-277-3- CC 3
277V 6A	

For use with Hi-lume_®, Hi-lume_® Compact SE, Hi-lume_® 3D, Eco-10_®, EcoSystem_® ballasts.

No derating required if ganged.

Adjustable low-end trim.

Hi-lume® LED drivers:

3-wire fluorescent dimmers*

Dimmers with on/off switch	
Single-pole	SF-10P- <u>CC</u>³
120V 8A	
Single-pole S	SF-12P-277- CC ³
277V 6A	
3-way	SF-103P- <u>CC</u> 3
120V 8A	
3-way SF	-12P-277-3- <u>CC</u> ³
277V 6A	

For use with Hi-lume LED driver only.

For more information on Hi-lume LED drivers,

visit www.lutron.com/HilumeLED.

No derating required if ganged.

Adjustable low-end trim.

∠ Tu-Wire[®] fluorescent dimmers

Dimmers with on/off switch		
3-way/single-pole	SFTU-5A3P- CC 3	
120V 5A		
Also compatible with Advance I	Mark X	
ballasts, for further information, visit		
www.lutron.com/advance.		
For information on use with Uni	versal and	
OSRAM ballasts, contact Technical Support		
at 1.800.523.9466.		

Philips Energy Saver DIMMABLE CFL dimmer (screw base)

Dimmer with on/off switch

3-way/single-pole	SPDC-203P- CC 3
120V 200W	
UL listed for Philips screw k compact fluorescent (CFL)	
Use only with Philips models: EL/A R30 DIM, R40 DIM, PAR38 DIM.	
No derating required if gan	ged.

<u>CC</u>³: Gloss color codes, see pg. 105 (Wallplates not included, order separately, see pg. 160) For more information on ballasts, visit **www.lutron.com/ballasts**.

All models must be derated if ganged unless otherwise noted, see pg. 170.

*Requires neutral wire connection.

Fan control model numbers

Fan controls

Slide-to-off fan controls-quiet 3-speed		
Single-pole	SFSQ-F- <u>CC</u> 3	
120V 1.5A		
Single-pole	SFSQ-F-HO- <u>CC</u> 3	
120V 2.0A		
For use with only one ceiling paddle fan		

For use with only one ceiling paddle fan.

SFSQ-F-HO- for use with Hunter Original Series.

Slide-to-off fan control-fully variable

Single-pole	SFS-5E- <u>CC</u>³
120V 5A	

For use with multiple ceiling paddle fans or exhaust fans.

Fan/light controls

Fan control-quiet 3-speed and dimmer		
Single-pole fan control	S2-LFSQ- <u>CC</u> 3	
120V 1.5A (left)		
120V single-pole dimmer 300W (right)		
For use with only one ceiling paddle fan.		
Fan control-fully variable and dimmer		
Fan control-fully variable and di	mmer	
Fan control—fully variable and di Single-pole fan control	mmer S2-LF- <u>CC</u> ³	
Single-pole fan control	S2-LF- CC 3	

Fan control/light switch

Fan control-quiet 3-speed and switch

Single-pole fan control	SFSQ-LF- <u>CC</u> 3
120V 1.5A (top)	
120V single-pole switch 360W (bottom)	
(incandescent/halogen loads only)	

<u>CC</u>³: Gloss color codes, see pg. 105 (Wallplates not included, order separately, see pg. 160) All models must be derated if ganged unless otherwise noted, see pg. 170.

*Requires neutral wire connection.