369-143k 1 09.30.10

#### Maestro Wireless® Dimmers and Switches

The Maestro Wireless solution incorporates Maestro Wireless load controls, wireless sensors, and wireless remote controls, which provides a system that delivers energy savings, convenience, and ease of installation.


Maestro Wireless dimmers and switches use Lutron patented Clear Connect™ RF Technology, which enables wireless communication with Radio Powr Savr™ sensors and Pico® wireless controls for light control and general switched loads.


#### **Features**

- The Maestro Wireless solution provides dimming/ switching of multiple load types, occupancy/vacancy sensing, daylight harvesting, and high-end trim.
- Lutron patented *Clear Connect* RF Technology works through walls and floors.
- Incorporates advanced features such as fade on/ fade off, high-end trim, and rapid full on.
- Controls include Front Accessible Service Switch (FASS™) for safe lamp replacement.
- Two-wire dimmers and switches available for retrofit applications.
- Power failure memory: If power is interrupted, the control will return to its previously set level prior to interruption.

#### **Receiving Devices**


Maestro Wireless Controls





#### **Transmitting Devices**

Radio Powr Savr Sensors



#### Pico Wireless Controls



#### **\$LUTRON.** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

369-143k 2 09.30.10

#### Maestro Wireless® Dimmers

#### **Model Numbers**

#### **Dimmers**

Halogen/Incandescent/Magnetic Low-voltage

MRF2-600M-XX 600 W Incandescent

Dimmer 120 V∼

MRF2-6MLV-XX 600 W/600 VA Incandescent/

MLV Dimmer 120 V∼

MRF2-6ND-120-XX\* 600 W/600 VA

Spec Grade Neutral wire

Dimmer 120 V~

MRF2-10D-120-XX 1000 W/1000 VA

Spec Grade Dimmer 120 V∼

3-wire Fluorescent

MRF2-F6AN-DV-XX\* 6 A 3-wire Fluorescent

Spec Grade Neutral wire Dimmer 120–277 V∼

Electronic Low-Voltage Dimmer-

MRF2-6ELV-120-XX\* 600 W ELV Dimmer 120 V~



#### Companion Dimmer



#### **Companion Controls**

Claro® Gloss Finishes

MA-R-XX Companion Dimmer 120 V~
MA-R-277-XX Companion Dimmer 277 V~

Satin Colors® Satin Finishes

MSC-AD-XX Companion Dimmer 120 V∼ MSC-AD-277-XX Companion Dimmer 277 V∼

"XX" in the model number represents color/finish code.

#### **<b>\$LUTRON.** SPECIFICATION SUBMITTAL

Job Name: Model Numbers:

Job Number:

<sup>\*</sup> NEUTRAL WIRE REQUIRED.

369-143k 3 09.30.10

#### **Dimmer Load Type and Capacity**

#### **Neutral Required**

Control	Voltage	Load Type	Minimum Load	Maximum Load		
				Not Ganged	End of Gang	Middle of Gang
MRF2-6ND-120 <sup>1,2,4</sup> 120 V~	Incand.	25 W	600 W	500 W	400 W	
	120 V∼	MLV <sup>2</sup>	25 W/VA	450 W / 600 VA	400 W/ 500 VA	300 W / 400 VA
MRF2-6ELV <sup>2</sup>	120 V∼	ELV <sup>2</sup>	5 W	600 W	500 W	400 W
MRF2-F6AN-DV <sup>3,5</sup>	120–277 V∼	Lighting	1 ballast 0.05 A	6 A	5 A	3 A

#### No Neutral Required

Control Voltage	Load Minimum		Maximum Load			
		Type Load	Load	Not Ganged	End of Gang	Middle of Gang
MRF2-600M <sup>1,4</sup>	120 V∼	Incand.	50 W	600 W	500 W	400 W
MRF2-6MLV <sup>1,2,4</sup>	120 V~	MLV <sup>2</sup>	50 VA	450 W / 600 VA	400 W/ 500 VA	300 W/ 400 VA
		Incand.	50 W	1000 W	800 W	650 W
MRF2-10D-120 <sup>1,2,4</sup>	120 V∼	MLV <sup>2</sup>	50 W/VA	800 W / 1000 VA	600 W/ 800 VA	500 W / 650 VA

- Replace burned-out lamps as quickly as possible.
- · Use transformers that incorporate thermal protection or fused transformer primary windings to prevent transformer failure due to overcurrent.
- 3 Can control the following power boosters/load interfaces: Phase-adaptive Power Modules (PHPM-WBX-DV-WH), 3-wire Fluorescent Power Modules (PHPM-3F-DV-WH), Tu-Wire<sub>®</sub> Fluorescent Power Modules (PHPM-PA-DV-WH), and 0–10 V (GRX-TVI).
- 4 Can control the following power booster/load interface: Hi-Power 2•4•cm Boosters (HP-2, HP-4, HP-6) for control of most popular lighting sources including Lutrons 3-wire line voltage control fluorescent dimming ballasts (Hi-lumes, Hi-lume Compact SEm, Eco-10s, and EcoSystems).
- 5 Dimmer Load Type: -F6AN is designed for use with permanently installed 3-wire line voltage control fluorescent ballasts or LED drivers only (Hi-lume, Hi-lume Compact SE, Eco-10, and EcoSystem).

<b>ILLITRON</b>	SPECIFICATION	SHRMITTAL

Job Name:	Model Numbers:
Job Number:	

<sup>1</sup> Dimmer Load Type: -6ND, -6MLV and -10D are designed for use with permanently installed incandescent, magnetic low-voltage, or tungsten halogen only. -600M is designed for use with permanently installed incandescent or tungsten halogen only. -6ELV is designed for use with permanently installed electronic low-voltage only. Do not install dimmers to control receptacles or motor-operated appliances.

<sup>2</sup> Low-Voltage Applications: Use -6ND, -6MLV and -10D with magnetic (core and coil) low-voltage transformers only. Not for use with electronic (solid-state) low-voltage transformers. Use -6ELV with electronic (solid-state) low-voltage transformers only.
Operation of a low-voltage circuit with lamps inoperative or removed may result in transformer overheating and premature failure. Lutron strongly recommends the following transformers.

<sup>•</sup> Do not operate low-voltage circuits without operative lamps in place.

369-143k 4 09.30.10

#### Maestro Wireless Switches

#### **Model Numbers**

#### **Switches**

Lighting and motor loads

MRF2-6ANS-XX\* 6 A Lighting/3 A Fan (1/10 HP

motor), Electronic Switch

120 V~

MRF2-8ANS-120-XX\* 8 A Lighting, 5.8 A Fan (1/4 HI

motor), Spec Grade Electronic

Switch 120 V∼

MRF2-6ANS-277-XX\* 6 A Lighting, Spec Grade

Electronic Switch 277 V∼

MRF2-8S-DV-XX 8 A Lighting, 3 A Fan (1/10 HF

motor, 120 V∼ only), Spec Grade Electronic Switch 120–277 V∼, NO NEUTRAL

WIRE REQUIRED



#### Companion Switch



#### **Companion Controls**

Claro® Gloss Finishes

MA-AS-XX Companion Switch 120 V~ MA-AS-277-XX Companion Switch 277 V~

Satin Colors® Satin Finishes

MSC-AS-XX Companion Switch 120 V~ MSC-AS-277-XX Companion Switch 277 V~

#### **<b>\*\*LUTRON.** SPECIFICATION SUBMITTAL

Job Name: Model Numbers:

Job Number:

<sup>\*</sup> NEUTRAL WIRE REQUIRED.

<sup>&</sup>quot;XX" in the model number represents color/finish code.

Designer-style: Maestro®

#### Switch Load Type and Capacity

#### **Neutral Required**

Control	Voltage	Load Type	Minimum	Maximum Load		
		Load	Load	Not Ganged	End of Gang	Middle of Gang
MRF2-8ANS-120 <sup>1,3</sup> 120 V~	Lighting	25 W	8 A	6.5 A	5 A	
	120 V∼	Fan Motor	0.2 A	1/4 HP 5.8 A	1/4 HP 5.8 A	1/6 HP 4.4 A
	Lighting	25 W	6 A	5 A	3.5 A	
MRF2-6ANS <sup>1</sup>	120 V∼	Fan Motor	0.2 A	1/10 HP 3 A	1/10 HP 3 A	1/10 HP 3 A
MRF2-6ANS-277 <sup>2</sup>	277 V~	Lighting	25 W	6 A	5 A	3.5 A

#### No Neutral Required

Control	Voltage	Load Type Minimum	N	laximum Loa	ıd	
			Load	Not Ganged	End of Gang	Middle of Gang
	120–277 V∼	Incandescent/ Halogen	25 W	8 A	8 A/7 A <sup>4</sup>	7 A
MRF2-8S-DV <sup>2</sup>	120–277 V∼	Fluorescent/ LED/CFL	40 W (LUT-MLC) <sup>5</sup>	8 A	8 A/7 A <sup>4</sup>	7 A
	120 V~	Fan Motor	0.4 A	1/10 HP 3 A	1/10 HP 3 A	1/10 HP 3 A

<b>WILLITEON</b>	SPECIFICATION	SLIBMITTAL
	JEICHLICH HICH	TOTAL MALE

Job Name:	Model Numbers:
Job Number:	

<sup>1</sup> Switch Load Type: -8ANS-120 is designed for use with permanently installed lighting loads and with fan motor loads up to 1/4 HP (5.8 A).

-6ANS is designed for use with permanently installed lighting loads and with fan motor loads up to 1/10 HP (3 A).

<sup>-8</sup>S-DV is designed for use with permanently installed lighting loads and with fan motor loads up to 1/10 HP (3 Å, 120 V~ only).

 $<sup>{\</sup>bf 2} \ {\hbox{Switch Load Type: -6ANS-277 and -8S-DV are designed for use with permanently installed lighting loads.}$ 

<sup>3</sup> For loads larger than 8 A @ 120 V ∼, the -8ANS-120 switch can be used with the PHPM-SW-DV-WH power booster. For loads larger than the MRF2-6ANS-277 capacity of 6 A @ 277 V ∼, the -8ANS-120 can also be used with the PHPM-SW-DV-WH power booster to switch 277 V ∼ loads. Please note that in this application, the -8ANS-120 switch is providing an input at 120 V ∼ and the power booster is switching 277 V ∼.

<sup>4</sup> Maximum load for double gang application is 8 A. Triple gang application derates maximum load to 7 A.

<sup>5</sup> The LUT-MLC ensures proper function with certain fluorescent, CFL, and LED load types.

369-143k 6 09.30.10

#### **Specifications**

#### Regulatory Approvals

- UL Listed.
- CSA Certified.
- FCC Approved. Complies with the limits for a Class B digital device, pursuant to Part 15 of the FCC Rules.
- Industry Canada Certified.

#### Power

Operating voltage:

120 V∼ 50/60 Hz

277 V~ 50/60 Hz (-6ANS-277, -8S-DV, -F6AN-DV)

#### **Key Design Features**

#### **Dimmers**

- On a single-tap, lights fade UP or DOWN.
- On a double-tap, lights go to full ON.
- When ON, press and hold to engage 20-second fade to OFF.
- Light levels can be fine-tuned by pressing and holding the dimming rocker until the desired light level is reached.
- Two-wire dimmers available.

#### Switch

Job Name:

- On a single-tap, lights turn ON or OFF.
- Two-wire switches available.

#### All RF Local Controls

- Tested to withstand electrostatic discharge without damage or memory loss, in accordance with IEC 61000-4-2.
- Tested to withstand surge voltages without damage or loss of operation, in accordance with IEEE C62.41-1991 Recommended Practice on Surge Voltages in Low-Voltage AC Power Circuits.

- Controls always operate locally and do not require system control.
- Power failure memory: should power be interrupted, the control will return to its previously set level prior to the interruption when power is restored.
- Uses conventional 3-way and 4-way wiring.
- Multiple location control from Dimmer/Switch and up to 9 Companion Dimmer(s)/Switch(es).
- Use Lutron® Designer (Claro® and Satin Colors®)
  wallplates or designer-style wallplates from other
  manufacturers. Wallplates are sold separately.
- Lutron *Claro* and *Satin Colors* wallplates snap on with no visible means of attachment.
- Requires a 1-gang U.S. wallbox. 3½ in (89 mm) deep recommended, 2¼ in (57 mm) deep minimum.
- Green indicator lights.

## System Communications and Capacity

- Maestro Wireless controls communicate with the Pico™ wireless controls and Radio Power Savr™ sensors through radio frequency (RF).
- Maestro Wireless local controls must be located within 60 ft (18 m) line of sight or 30 ft (9 m) through walls, of Radio Power Savr sensors.
- Maestro Wireless local controls must be located within 100 ft (30 m) line of sight or 30 ft (9 m) through walls, of a Pico wireless control.
- Up to 10 Maestro Wireless controls can be configured to work together.

#### **Environment**

 Ambient operating temperature: 32 °F to 104 °F (0 °C to 40 °C), 0%-90% humidity, non-condensing. Indoor use only.


<b>WILLITEON</b>	SPECIFICATION	SLIBMITTAL
	JEICHLICH HICH	TOTAL MALE

Model Numbers:

Job Number:	
-------------	--

369-143k 7 09.30.10


#### Operation



#### **IMPORTANT NOTICE:**

**FASS** - Front Accessible Service Switch - to service load, remove power by pulling the *FASS* switch out completely on either the Dimmer/Switch or Companion Dimmer/Switch. After servicing load, push the *FASS* switch back in fully to restore power to the control.

#### Mounting



#### **\$LUTRON.** SPECIFICATION SUBMITTAL


Job Name:	Model Numbers:
Job Number:	


Side View

369-143k 8 09.30.10

#### **Dimensions**


## Front View





#### Ganging and Derating

When ganging with other controls in the same wallbox, derating is required. See Load Type and Capacity chart. Only -8ANS controls have fins that need to be removed for multigang installations. No other controls have fins, but they must still be derated in multigang installations.



#### **<b>\*\*LUTRON.** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

369-143k 9 09.30.10

#### Wiring Diagrams


#### **Single Location Installation**

-600M, -6MLV, -10D

# Blue - unused, tighten¹ Hot/Live 120 V~4 60 Hz or 277 V~4 60 Hz Neutral


#### Single Location Installation with Neutral

-6ND, -6ELV, -6ANS-120, -8ANS-120, -6ANS-277




#### Multi-Location Installation<sup>2</sup>

-600M, -6MLV, -10D with MA-R/MSC-AD



#### Multi-Location Installation with Neutral<sup>2,3</sup>

-6ND, -6ELV with MA-R/MSC-AD; -6ANS-120, -8ANS-120 with MA-AS/MSC-AS; -6ANS-277 with MA-AS-277/MSC-AS-277



<sup>&</sup>lt;sup>1</sup>When using controls in single location installations, tighten the blue terminal without any wires attached. **DO NOT** connect the blue terminal to any other wiring or to ground.

4 120 V∼: -6ND, -6ANS-120, -8ANS-120, -6ELV-120

277 V∼ : -6ANS-277, 8S-DV

#### **<b>ELUTRON** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

<sup>&</sup>lt;sup>2</sup>Up to 9 Maestro Companion Dimmers/Switches may be connected to the Maestro Wireless Dimmer/Switch. Total blue terminal wire length may be up to 250 ft (76 m).

<sup>&</sup>lt;sup>3</sup> Neutral wire Dimmers/Switches must be connected on the Load side of a multi-location installation.


 $<sup>^{5}</sup>$  Requires MA-AS/MSC-AS for 120 V  $\sim$  applications, and MA-AS-277/MSC-AS-277 for 277 V  $\sim$  applications.

369-143k 10 09.30.10

#### Wiring Diagrams

#### **Single Location Installation**


-8S-DV\*



\* A LUT-MLC ensures proper function when fluorescent, CFL, or LED loads are used. Install the LUT-MLC inside a load fixture or in a separate J-box of the circuit.

#### Multi-Location Installation<sup>2</sup>

-8S-DV4,\* with MA-AS/MA-AS-277 or MSC-AS/MSC-AS-277



<sup>&</sup>lt;sup>1</sup>When using controls in single location installations, tighten the blue terminal without any wires attached. **DO NOT** connect the blue terminal to any other wiring or to ground.

277 V∼: -6ANS-277, -8S-DV

#### **LUTRON.** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

<sup>&</sup>lt;sup>2</sup>Up to 9 Maestro Companion Dimmers/Switches may be connected to the Maestro Wireless Dimmer/Switch. Total blue terminal wire length may be up to 250 ft (76 m).

³ 120 V $\sim$  : -6ND, -6ANS-120, -8ANS-120, -6ELV-120


<sup>&</sup>lt;sup>4</sup> Requires MA-AS/MSC-AS for 120 V∼ applications, and MA-AS-277/MSC-AS-277 for 277 V∼ applications.

369-143k 11 09.30.10

#### Wiring Diagrams


#### Single Location Installation with Neutral

-F6AN-DV



#### Multi-Location Installation with Neutral<sup>2,3</sup>

-F6AN-DV with MA-R/MA-R-277 or MSC-AD/MSC-AD-2774



#### **LUTRON.** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

<sup>&</sup>lt;sup>1</sup> When using controls in single location installations, tighten the blue terminal. DO NOT connect the blue terminal to any other wiring or to ground.

<sup>&</sup>lt;sup>2</sup>Up to 9 Maestro Companion Dimmers may be connected to the Maestro Wireless Dimmer. Total blue terminal wire length may be up to 250 ft (76 m).

<sup>&</sup>lt;sup>3</sup> Neutral wire Dimmers must be connected on the Load side of a multi-location installation.


 $<sup>^4</sup>$  Requires MA-R/MSC-AD for 120 V $\sim$  applications, and MA-R-277/MSC-AD-277 for 277 $\sim$  V applications.

369-143k 12 09.30.10

#### Wiring Diagrams


## Single Location Installation with Power Booster Single Feed

-6ANS-120, -8ANS-120 with PHPM-SW-DV-WH




## Single Location Installation with Power Booster Dual Feed

-6ANS-120, -8ANS-120 with PHPM-SW-DV-WH




## Multi-Location Installation with Power Booster<sup>2,3</sup> Single Feed

-6ANS-120, -8ANS-120 with MA-AS/MSC-AS and PHPM-SW-DV-WH



## Multi-Location Installation with Power Booster<sup>2,3</sup> Dual Feed

-6ANS-120, -8ANS-120 with MA-AS/MSC-AS and PHPM-SW-DV-WH



<sup>&</sup>lt;sup>1</sup> When using controls in single location installations, tighten the blue terminal. **DO NOT** connect the blue terminal to any other wiring or to ground.

#### **LUTRON.** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

<sup>&</sup>lt;sup>2</sup>Up to 9 Maestro Companion Switches may be connected to the Maestro Wireless Switch. Total blue terminal wire length may be up to 250 ft (76 m).


<sup>&</sup>lt;sup>3</sup> Neutral wire Switches must be connected on the Load side of a multi-location installation.

369-143k 13 09.30.10

#### Wiring Diagrams


## Single Location Installation with Power Booster Single Feed

-F6AN-DV with PHPM-3F-DV-WH, PHPM-PA-DV-WH, or PHPM-WBX-DV-WH




## Single Location Installation with Power Booster Dual Feed

-F6AN-DV with PHPM-3F-DV-WH, PHPM-PA-DV-WH, or PHPM-WBX-DV-WH




#### Multi-Location Installation with Power Booster<sup>2,3</sup> Single Feed

-F6AN-DV with MA-R/MSC-AD and PHPM-3F-DV-WH, PHPM-PA-DV-WH, or PHPM-WBX-DV-WH



## Multi-Location Installation with Power Booster<sup>2,3</sup> Dual Feed

-F6AN-DV with MA-R/MSC-AD and PHPM-3F-DV-WH, PHPM-PA-DV-WH, or PHPM-WBX-DV-WH



<sup>&</sup>lt;sup>1</sup>When using controls in single location installations, tighten the blue terminal. DO NOT connect the blue terminal to any other wiring or to ground.

#### **ELUTRON.** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	

<sup>&</sup>lt;sup>2</sup>Up to 9 Maestro Companion Dimmers may be connected to the Maestro Wireless Dimmer. Total blue terminal wire length may be up to 250 ft (76 m).


<sup>&</sup>lt;sup>3</sup> Neutral wire Dimmers must be connected on the Load side of a multi-location installation.

<sup>&</sup>lt;sup>4</sup>When using a PHPM, tighten the brass (Sw Hot) terminal of the -F6AN-DV. DO NOT connect the brass terminal to any other wiring or to ground.

369-143k 14 09.30.10

#### Colors and Finishes

#### **Gloss Finishes**



#### **Satin Finishes**



HT







Plum PL

Turquoise TQ



Almond AL





Taupe TP



**Biscuit** 

BI

SI

MS



Gray





Midnight

EŠ

MN

BG





TC

GR



Palladium PD

GB



Greenbriar



Bluestone Mocha Stone





Due to printing limitations, colors and finishes shown cannot be guaranteed to perfectly match actual product colors.



Desert Stone DS



Stone

Limestone LS

#### Metal Finish (wallplate only)



Stainless Steel SS

When using Stainless Steel wallplates, it is recommended to order the controls in Black (BL) or Midnight (MN).

#### **LUTRON.** SPECIFICATION SUBMITTAL

Job Name:	Model Numbers:
Job Number:	