


Datasheet

Art.No. 57.910.6155.0

Fuse terminal WK 10/SIU6,3X32M.GLB/V0

Fuse terminal block with screw connection for mounting on TS 35 and TS 32, nominal cross section 10 mm<sup>2</sup>, width 10 mm, color gray



Art.No.	57.910.6155.0
EAN	4015573517424
Order unit	50 pieces

Approvals



Technical data

General

Nominal cross section	10 mm <sup>2</sup>
Colour	Grey
Number of levels	1
Width/grid dimension	12 mm
Insulating housing	PA666
Inflammability class of insulation material acc. with UL94	V0
Mounting method	DIN rail (top hat rail)/G-rail
Terminal blocks for electrical installations	No
Fuse insert	G-fuse 6.3x32 mm

Technical data

Rated current	10 A
Rated voltage	500 V
Rated impulse voltage	6 kV
Pollution degree	3
Closing plate required	Yes
Type of insulation material	Thermoplastic
Length	65 mm

Connection Data

Connection type 1	Screw connection
Connection type 2	Screw connection
Minimum cross section solid	1 mm <sup>2</sup>

Maximum cross section solid	10 mm <sup>2</sup>
Minimum cross section fine stranded	1 mm <sup>2</sup>
Maximum cross section fine stranded	10 mm <sup>2</sup>
Minimum cross section stranded	16 mm <sup>2</sup>
Maximum cross section stranded	16 mm <sup>2</sup>
Wire strip length	13 mm
Torque conductor mounting	2 Nm

**Technical Data UL/CSA**

Cross section UL	22-6 AWG
Voltage UL	600 V
Current factory wiring	15 A
Current field wiring	15 A
Cross section CSA	16-6 AWG
Voltage CSA	600 V
Current CSA	15 A

**Note**

Remark to rated voltage	Note fuse insert
Remark to rated current	Note fuse insert
Defect indicator	Glow lamp
Voltage type for defect indication	
Minimum operating voltage of defective display	380 V
Maximum operating voltage of defective display	500 V