

#### **Connections overview**

#### Load connections\*



# **Control types** (for 2 or more locations) Dim from one location, switch from the others



Dimmer

Source

For more information on ballasts, visit **www.lutron.com/ballasts**.

For more information on LED drivers, visit **www.lutron.com/LED**.

Switch

(1 or more)

Switch

\*For illustration purposes only. Consult model number pages for specific voltage and capacity information.

#### **Dimmer model numbers**

## Incandescent/halogen dimmers

### Dimmers with on/off switch

Single-pole	CT-600P- <u><b>CC</b></u> 3
120V 600W	
3-way	CT-603P- <u><b>CC</b></u> 3
120V 600W	
3-way/single-pole	CTCL-153P- <u><b>CC</b></u> <sup>3</sup>
120V 600W	

# eco-minder™ dimmers with on/off switch and locator light

and locator light	
Single-pole	MK-600PI- <u><b>EE</b></u> ²
120V 600W	
3-way	MK-603PI- <u><b>EE</b></u> ²
120V 600W	
eco-minder green LED der	nonstrates

15% or more energy savings compared to a standard switch.

### eco-dim<sub>®</sub> digital fade dimmer\*\*

Multi-location/single-pole	CT-603PG- <u><b>EE</b></u> 2
120V 600W	

eco-dim model guarantees at least 15% energy savings and triples lamp life compared to a standard switch.

# Dimmable CFL bulbs (screw-base)

# Dimmable LED bulbs (screw-base)

#### Dimmers with on/off switch

3-way/single-pole	CTCL-153P- <b>CC</b> 3
120V 150W	

Visit **www.lutron.com** for an approved list of dimmable CFL/LED bulbs, and "how to calculate wattage when mixing lamp types".

**CC**<sup>3</sup>: Gloss color codes, see pg. 101

EE<sup>2</sup>: Gloss White (WH), Light Almond (LA), Almond (AL) and Ivory (IV), see pg. 101 (Wallplates not included, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

\*\*Minimum load is 40 W/VA.