



TRAC 12

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Miniature Low Voltage Trac System

12V ELECTRONIC TRANSFORMERS

TL544N, TL546, TL547, TL548

PRODUCT SPECIFICATIONS


Catalog Number TL544N-WH, TL544N-BL

Description 12V-60VA Surface Mount Transformer • Low profile 12 volt electronic transformer • Rated for 10-60 watts for incandescent loads • 6' three-wire cord set and 4 1/2" leads with mating connector for TL43 monopoint • Rocker on/off switch

- Automatic resetting thermal, overload and short circuit protection.

Labels UL listed, CSA certified.

Surface Mount Transformer



Note: Remoting more than 5' is not recommended due to voltage drop.


Catalog Number TL546WH, TL546BL

Description 12V-150VA Canopy Mount Transformer • Canopy with 12 volt electronic transformer mounts over 120 volt outlet box to end-feed one Trac section or center feed two Trac sections • Rated for 50-150 watts for incandescent loads • Supplied with mounting plate • Automatic resetting thermal, overload and short circuit protection

- Not designed for use with Trac 12/25 trac.

Labels UL listed, CSA certified.

Canopy Transformer




Note: Remoting more than 5' is not recommended due to voltage drop.

Catalog Number TL547WH, TL547BL

Description 12V-150VA Surface Mount Transformer • 12 volt electronic transformer • Rated for 50-150 watts for incandescent loads • For in-line (Trac 12 trac only) or remote installation up to 5' away (Trac 12 or Trac 12/25) • End or top feed supply wiring using 1/2" electrical connectors • On/off switch • Automatic resetting thermal, overload and short circuit protection.

Labels UL listed, CSA certified.

Surface Transformer



Note: Remoting more than 5' is not recommended due to voltage drop.


Catalog Number TL548WH, TL548BL

Description 12V-60VA Portable Plug-In Electronic Transformer • Rated for 10-60 watts for incandescent loads • Includes: 10' two-wire cord and on-off line cord switch

- Automatic resetting thermal, overload and short circuit protection • May also be used with Trac12/25 trac.

Labels UL listed, CSA certified.

Portable Plug-In Transformer



PRODUCT CODES

Catalog Number	Finish	Description
TL544N-WH	White	60W Electronic Surface Mount 12V Transformer
TL544N-BL	Black	60W Electronic Surface Mount 12V Transformer
TL546WH	White	150W Electronic Canopy Mount 12V Transformer
TL546BL	Black	150W Electronic Canopy Mount 12V Transformer
TL547WH	White	150W Electronic Surface Mount 12V Transformer
TL547BL	Black	150W Electronic Surface Mount 12V Transformer
TL548WH	White	60W Electronic Portable Plug-in 12V Transformer
TL548BL	Black	60W Electronic Portable Plug-in 12V Transformer

Product specifications subject to change without notice.

APPLICATION

Consideration

• Trac run length

• Dimming

• Transformer Location

12V Electronic Transformer

• Use for short to medium run lengths and low to medium wattage systems

• Compatible with most standard incandescent dimmers. For optimal results use dimmer designed for low voltage electronics

• Install surface mount units in well-ventilated location where ambient temperature will not exceed 120°F (50°C)

12V Magnetic Transformer

• Use for medium to long and medium to higher wattage systems

• Use only dimmers specifically designed for use with magnetic transformers

• Install in well ventilated locations where ambient temperature will not exceed 140°F (60°C) Transformers must be accessible.

THIS SIDE INTENTIONALLY LEFT BLANK



1300 S. Wolf Road • Des Plaines, IL 60018 • Phone (847) 827-9880 • Fax (847) 827-2925
220 Chrysler Drive • Brampton, Ontario • Canada L6S 6B6 • Phone (905) 792-7335 • Fax (905) 792-0064
Visit us at www.junolightinggroup.com

Printed in U.S.A. ©2009 Juno Lighting, LLC.