

FEATURES & SPECIFICATIONS

INTENDED USE —Static T8 fixtures provide general illumination for recessed applications; idea for restricted plenum spaces.

ATTRIBUTES — Designed exclusively for use with T8 lamps, electronic ballasts and sockets.

CONSTRUCTION — Smooth hemmed sides and smooth, inward formed end flanges for safe handling. Lighter weight fixture allows for safe, easy installation.

Standard steel door frame has superior structural integrity with premium extruded appearance and precision flush mitered corners. Powder painted, steel latches provide easy, secure door closure.

Superior mechanical light seal requires no foam gasketing. Integral T-bar clips secure fixture to T-bar system. Housing formed from cold-rolled steel. Acrylic shielding material 100% UV stabilized. No asbestos is used in this product.

FINISH — Five-stage iron-phosphate pretreatment ensures superior paint adhesion and rust resistance. Painted parts finished with high-gloss, baked white enamel.

OPTICAL — Broad range of lens options available.

ELECTRICAL — Standard ballast is electronic, thermally protected, resetting, Class P, HPF, non-PCB, UL Listed, CSA certified ballast, universal voltage and sound rated A.

Luminaire is suitable for damp locations. AWM, TFN or THHN wire used throughout, rated for required temperatures.

LISTING — Standard: UL. Optional: Canada — CSA or cUL; Mexico — NOM.

WARRANTY — 1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

US patents: 6,210,025; 6,231,213; 2,288,471.


Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.

Catalog Number

Notes

Type



_____Specifications
Length: 48 (121.8)
Width: 12 (30.5)
Depth: 4-1/2 (11.4)
Weight: 17 lbs (7.7 kg)
All dimensions are inches (centimeters).



Example: GT8 2 32 A12 MVOLT GEB10IS

ORDERING INFORMATION For shortest lead times, configure products using **bolded options**.

GT8								
Series	Trim type	Number of lamps	Lamp type	Door frame	Diffuser type	Voltage	Options ¹	
GT8 1' wide	(blank) Grid F Overlapping flanged	1 2 3 Not included	32 32W T8 (48")	(blank) Flush steel, white FN Flush aluminum, natural FM Flush aluminum, matte black FW Flush aluminum, white RN Regressed aluminum, natural RW Regressed aluminum, white	A12 #12 pattern acrylic A12125 #12 pattern acrylic, .125" thick A19 #19 pattern acrylic, .156" thick A15 #15 pattern acrylic, .2" thick PC1S 1/2" x 1/2" x 1/2" x 1/2" plastic cube louver, silver PC2S 1-1/2" x 1-1/2" x 1" plastic cube louver, silver w/ flange PC3S 3/4" x 3/4" x 1/2" plastic cube louver, silver w/ finange	120 277 347 MVOLT Others available	GEB10IS GEB10RS EL EL14 GLR GMF LST PWS1836 LP_ PAF SSR CRE CRM JP CSA	One 3-lamp ballast Electronic ballast, <10% THD, instant start Electronic ballast, <10% THD, rapid start Emergency battery pack (nominal 300 lumens) Emergency battery pack (nominal 1400 lumens) Internal fast-blow fuse Internal slow-blow fuse Tandem-wired fixture pairs (shared ballasts) 6' prewire, 3/8" dia., 18-gauge, 1 circuit Lamped, specify lamp type and color Painted after fabrication (white enamel) Specular silver interior finish (95% reflective) Flanged trim for continuous row mounting (end) Flanged trim for continuous row mounting (middle) Palletized and stretch-wrapped without individual cartons; grid trim only CSA Certified NOM Certified


NOTES:


FLUORESCENT: GT8-1X4

MVOLT standard for 120-277V applications, 50-60 hz operation. Some options require voltage specified.

MOUNTING DATA

Continuous row mounting of flanged units requires CRE and CRM trim options (see Options).






NOTE:

1 Recommended rough-in dimensions for F-trim fixtures 12"x48" (Tolerance is +1/4"-0"). Swing-gate range 1-9/16" to 3-3/4". Swing-gate span 10-3/4" to 14-3/4".

DIMENSIONS

All dimensions are inches (centimeters) unless otherwise indicated.



PHOTOMETRICS

Calculated using the zonal cavity method in accordance with IESNA LM41 procedure. Floor reflectances are 20%. Lamp configurations shown are typical. Full photometric data on these and other configurations available upon request.

GT8 2 32 A12

Report: LTL12536 LUMENS PER LAMP:2850 Luminaire Efficiency:77.7%

Coefficients of Utilization

pf				2	20%					
рс		80%			50%			30%		
pw	70%	50%	30%	50%	30%	10%	50%	30%	10%	
0	92	92	92	86	86	86	83	83	83	
1	85	82	79	77	74	72	74	72	70	
2	78	72	67	68	64	61	66	63	60	
3	72	64	58	61	56	52	59	55	51	
د 4	66	58	51	55	50	45	53	48	45	
25 5	61	52	45	49	44	40	48	43	39	
^щ 6	57	47	40	45	39	35	44	39	35	
7	53	43	36	41	36	32	40	35	31	
8	49	39	33	38	32	28	37	32	28	
9	46	36	30	35	30	26	34	29	26	
10	43	33	28	32	27	24	32	27	23	

Zonal Lumen Summary

Zone	Lumens	% Lamp	% Fixture
0° - 30°	1471	25.8	33.2
0° - 40°	2347	41.2	53.0
0° - 60°	3777	66.3	85.3
0° - 90°	4426	77.7	100.0
90° - 180°	0	0.0	0.0
0° - 180°	4426	77.7	100.0

