



# AutoGuard® 2.4GHz Wireless Handheld LCD Receiver

GMSL



PROJECT
FIXTURE TYPE
MODEL
LAMP
CONTACT/TELEPHONE

## Specifications

### Description

GMSL is a 2.4GHz 2.5-in wireless handheld LCD receiver, to be used with AutoGuard® Motion Tracker with camera (i.e. GMSCR150 and GMSCR300). GMSL is able to monitor up to 4 motion tracker units, offering a wide range of monitoring and recording capabilities. GMSL is complete with a lithium battery, 1GB SD card, USB cable, installation CD and a power supply adapter.


### Features

- Receiving frequency range: ISM 2,400MHz ~ 2,468MHz
  - \* CH1 = 2,414MHz
  - \* CH2 = 2,432MHz
  - \* CH3 = 2,450MHz
  - \* CH4 = 2,468MHz
- Receiving sensitivity: ≤-85 dBm
- Consumption current (max.): 350mA
- Unobstructed effective range: 100m (330 ft.) approx.
- LCD screen type: 2.5" TFT-LCD
- Effective pixel resolution: 640x240
- Color configuration: R.G.B. delta
- Video system: NTSC, PAL
- Supported formats: MPEG4, MP3, WMA, WAV, JPG, TXT
- Video recording: 2 hours / 1GB
- Photo saving: 4,000 pictures / 1GB
- Operating temperature: -10°C ~ +50°C / +14°F ~ +122°F
- Power supply: 5VDC
- Li-battery charge time: 4 hours
- Li-battery operation time: 2 hours

### Listings



## Dimensions & Ordering Guide



## LITELINE CORPORATION

8 Abacus Road, Brampton, Ontario, Canada L6T 5B7  
 Tel: 416-996-1856 • Fax: 905-794-1990 / 1-888-738-9736  
 E-mail: sales@liteline.com • Website: www.liteline.com

Product specifications subject to change without notice.