




|               |       |      |
|---------------|-------|------|
| Project:      | Type: | QTY: |
| Product Code: |       |      |

Ø4"



### Product Code

**IP53** - **RFL4SD** - TRIM COLOR - INTENSITY - VOLTAGE  
 W\*=White      WW30\*=3000K      120=120V, AC  
 A =Aluminum      NW40 =4000K  
 CC =Custom Color

**Note: \* Components usually in-stock for quick assembly and shipping.**

### Features + Specifications

**Intended Use:**

- Building interior
- Building exterior (ceiling recessed only)
- Damp location listed
- IC rated, approved and tested for direct contact with insulation materials

**Construction:**

- Die-cast aluminum one piece trim frame with built-in heat sink
- Opal PMMA lens with light glide technology for even light distribution
- Full metal top plate protects LED PCB
- Heavy duty installation springs ensure tight fitting to ceiling

**Finish:**

- W = Powder coat painted
- A = Anodized aluminum
- CC = Powder coat painted




**Optical System:**

- High brightness 2835 SMDs with LM80 certificate **6W**
- \***WW30** = 3000K CCT, **600 lumens** minimum with 80+ CRI
- Optional CCT color NW40 also available (This CCT might require minimum quantities with longer lead time)
- L70 @ 50000hrs for ambient temperature <25°C, 35000hrs >25°C
- PCB made from laminated heavy gauge copper materials

**Electrical System:**

- Constant current driver technology
- 120V line voltage dimmable with most dimmers
- Overheat protected, RoHS compliant

**Installation hole  
cut out size: Ø4-1/8"**



Right reserved for material and spec modification without prior notice.

Datecode 20150120

Warranty - Up To 3 Years

Certified to CSA C22.2 No.250.0 Conformed to UL 1598  
Certification Marks (where applicable) will be found on our luminaires and its components



[www.iplighting.com](http://www.iplighting.com)

