

LED PARS



7-17
watts

25,000
hours

25X
longer
Life

500-
1300
lumens

features

- Cost-effective LED solution for replacing 40W-120W PAR halogen lamps
- Consumes 85% less energy while lasting 25x longer than the halogen PAR bulbs they replace
- Compatible with a wide variety of dimmers (10-100%)
- Instant-on with no warm-up time, unlike fluorescent replacement lamps
- Available in 25° narrow flood and 40° flood beam distributions
- Choice of warm white 2700K, soft white 3000K, and natural white 4000K color temperatures
- Emits virtually no harmful ultraviolet or infrared radiation



performance


- 7W/500 lumens LED replaces 40W PAR20 halogen
- 12W/850 lumens LED replaces 65W PAR30 halogen
- 14/950 lumens LED replaces 75W PAR38 halogen
- 17W/1300 lumens LED replaces 120W PAR38 halogen
- Long life L70: 25,000 hours
- Standard series 80+ CRI · 120V @ 60Hz
- Operating temperature range: -4°F (-20°C) to 104°F (40°C)
- UL listed for damp locations (17W PAR38 listed for wet locations)

applications


- Recessed/Track Lighting
- Property Management
- Accent/Display Lighting
- Retail/Residential
- Hospitality
- Houses of Worship
- Healthcare
- Task Lighting




dimensions




7W PAR20



12W PAR30



12W PAR30 Short Neck



14/17W PAR38

products

	ES	WET	LDL	Advantage Part #	UPC	Watts	Lumens	CCT	Beam Angle	CBCP	CRI	Rated Life (hrs)	Halogen Incandescent Replacement
PAR20	★			LED7WPAR20/FL/827K-DIM-G4A	90024	7W	500	2700K	40°	1074	80+	25,000	40W PAR20 Flood Warm White
	★			LED7WPAR20/FL/830K-DIM-G4A	90023	7W	500	3000K	40°	1127	80+	25,000	40W PAR20 Flood Soft White
			✓	LED7WPAR20/FL/840K-DIM-G4A	90022	7W	500	4000K	40°	1101	80+	25,000	40W PAR20 Flood Natural White
	★			LED7WPAR20/NFL/827K-DIM-G4A	90021	7W	500	2700K	25°	1526	80+	25,000	40W PAR20 Narrow Flood Warm White
	★			LED7WPAR20/NFL/830K-DIM-G4A	90020	7W	500	3000K	25°	1750	80+	25,000	40W PAR20 Narrow Flood Soft White
			✓	LED7WPAR20/NFL/840K-DIM-G4A	90019	7W	500	4000K	25°	1638	80+	25,000	40W PAR20 Narrow Flood Natural White
PAR30	★			LED12WPAR30/FL/827K-DIM-G4A	90072	12W	850	2700K	40°	1976	80+	25,000	65W PAR30 Flood Warm White
	★			LED12WPAR30/FL/830K-DIM-G4A	90071	12W	850	3000K	40°	2139	80+	25,000	65W PAR30 Flood Soft White
			✓	LED12WPAR30/FL/840K-DIM-G4A	90070	12W	850	4000K	40°	2058	80+	25,000	65W PAR30 Flood Natural White
	★			LED12WPAR30/NFL/827K-DIM-G4A	90069	12W	850	2700K	25°	4761	80+	25,000	65W PAR30 Narrow Flood Warm White
	★			LED12WPAR30/NFL/830K-DIM-G4A	90068	12W	850	3000K	25°	4661	80+	25,000	65W PAR30 Narrow Flood Soft White
			✓	LED12WPAR30/NFL/840K-DIM-G4A	90067	12W	850	4000K	25°	4712	80+	25,000	65W PAR30 Narrow Flood Natural White
PAR30 SHORT	★			LED12WPAR30S/FL/827-DIM-G4A	08553	12W	850	2700K	40°	1680	80+	25,000	65W PAR30 Short Flood Warm White
	★			LED12WPAR30S/FL/830-DIM-G4A	08554	12W	850	3000K	40°	2023	80+	25,000	65W PAR30 Short Flood Soft White
			✓	LED12WPAR30S/FL/840-DIM-G4A	08555	12W	850	4000K	40°	1852	80+	25,000	65W PAR30 Short Flood Natural White
	★			LED12WPAR30S/NFL/827-DIM-G4A	08556	12W	850	2700K	25°	5176	80+	25,000	65W PAR30 Short Narrow Flood Warm White
	★			LED12WPAR30S/NFL/830-DIM-G4A	08557	12W	850	3000K	25°	3826	80+	25,000	65W PAR30 Short Narrow Flood Soft White
			✓	LED12WPAR30S/NFL/840-DIM-G4A	08558	12W	850	4000K	25°	4501	80+	25,000	65W PAR30 Short Narrow Flood Natural White
PAR38	★			LED14WPAR38/FL/827K-DIM-G4A	90061	14W	950	2700K	40°	2092	80+	25,000	75W PAR38 Flood Warm White
	★			LED14WPAR38/FL/830K-DIM-G4A	90060	14W	950	3000K	40°	2422	80+	25,000	75W PAR38 Flood Soft White
			✓	LED14WPAR38/FL/840K-DIM-G4A	90059	14W	950	4000K	40°	2257	80+	25,000	75W PAR38 Flood Natural White
	★			LED14WPAR38/NFL/827K-DIM-G4A	90058	14W	950	2700K	25°	5148	80+	25,000	75W PAR38 Narrow Flood Warm White
	★			LED14WPAR38/NFL/830K-DIM-G4A	90057	14W	950	3000K	25°	4949	80+	25,000	75W PAR38 Narrow Flood Soft White
			✓	LED14WPAR38/NFL/840K-DIM-G4A	90056	14W	950	4000K	25°	5049	80+	25,000	75W PAR38 Narrow Flood Natural White
	★	●		LED17WPAR38/FL/827K-DIM-G4A	90044	17W	1300	2700K	40°	3156	80+	25,000	120W PAR38 Flood Warm White
	★	●		LED17WPAR38/FL/830K-DIM-G4A	90043	17W	1300	3000K	40°	3255	80+	25,000	120W PAR38 Flood Soft White
		●	✓	LED17WPAR38/FL/840K-DIM-G4A	90042	17W	1300	4000K	40°	3206	80+	25,000	120W PAR38 Flood Natural White
	★	●		LED17WPAR38/NFL/827K-DIM-G4A	90041	17W	1300	2700K	25°	7143	80+	25,000	120W PAR38 Narrow Flood Warm White
	★	●		LED17WPAR38/NFL/830K-DIM-G4A	90040	17W	1300	3000K	25°	7180	80+	25,000	120W PAR38 Narrow Flood Soft White
		●	✓	LED17WPAR38/NFL/840K-DIM-G4A	90039	17W	1300	4000K	25°	7162	80+	25,000	120W PAR38 Narrow Flood Natural White

★ ENERGY STAR[®] Certified ● Wet Location Rated ✓ Lighting Design Lab Qualified

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335