



Carriers

VersaMax provides several types of snap-together I/O carriers and interposing terminals to provide maximum wiring flexibility, as well as module hot insertion and removal. VersaMax carriers support IEC box-style, spring-style, and barrier-style terminals and are also available as snap-on auxiliary terminal strips and interposing terminals that can be mounted separately and connected to a connector-style carrier by an I/O cable.

	IC200CHS001	IC200CHS002	IC200CHS005
	VersaMax I/O Carrier, Local Barrier Style	VersaMax I/O Carrier, Local Box Style	VersaMax I/O Carrier, Local Spring Clamp Connection Style
Product Name			
Lifecycle Status	Active	Active	Active
Field Termination Type	Integrated	Integrated	Integrated
Wiring Termination Style	Barrier	Box	Spring
Orientation on Module on Base	Horizontal	Horizontal	Horizontal
Dimensions (W x H x D)	110.5 mm (4.35 in) x 139.7 mm (5.5 in) x 70 mm (2.75 in), not including the height of DIN Rail	110.5 mm (4.35 in) x 139.7 mm (5.5 in) x 70 mm (2.75 in), not including the height of DIN Rail	110.5 mm (4.35 in) x 139.7 mm (5.5 in) x 70 mm (2.75 in), not including the height of DIN Rail
Cables	N/A	N/A	N/A