

# Fluke SPECIALS

FLUKE®



**Visual IR  
Thermometer**  
**Fluke VT04**

**NEW**



**Two Pole  
Testers**  
**Fluke T100 series**



**Promotion**

**Multifunction  
Installation  
Testers**  
**Fluke 1650 series**



[www.fluke.ie/promotions](http://www.fluke.ie/promotions)

**Autumn/Winter 2013**

**Fluke.** *The Most Trusted Tools  
in the World.*

# Two Pole Testers from Fluke

Robust, easy, fast and safe.

## Robust

- Heavy duty molded design
- Thick cords with wear indicator
- Probe protector

## Easy


- Ergonomic design
- Large easy to use buttons even with gloves on
- Probe docking system with proper spacing for standard outlets

## Fast

- Built-in torch
- Combination of light, sound, vibration and digital display to make the test faster under any condition
- Display hold: no need to read measurement when probing

## Safe

- Compliant with the newest European standards EN 61243-3:2010



Fluke T150

Fluke T130

Fluke T110

Fluke T90



The new Fluke T100 series Fully compliant with

**IEC 61243-3:2010**

- Load connection through two separate push buttons
- Sound alarms louder than 58.5dB
- WearGuard™; two layers of insulation to indicate wear or tear

- Safety rating T90: CAT II 690/CAT III 600V
- Safety rating T110/130/150: CAT III 690V/CAT IV 600V

# Digital Multimeters Fluke 110 series

Compact design multimeters for ergonomic one-handed operation.



Fluke 113



Fluke 114



Fluke 115



Fluke 117

Features	Fluke 113	Fluke 114	Fluke 115	Fluke 117
True RMS readings	●	●	●	●
Display backlight	●	●	●	●
VoltAlert™, Non-contact voltage detection	-	-	-	●
LoZ (low input impedance)	-	●	-	●
Frequency, capacitance, Diode test	-/●/●	-	●	●
CAT III	600 V	600 V	600 V	600 V

# Take your readings where you want to be

Fluke tools from the CNX line can wirelessly connect to your computer, digital multimeter or thermal imager. With CNX, you can limit walking from one measurement to another and stay away from dangerous situations while taking readings.

Use wirelessly



Use as stand alone



Use as data logger



## 3 IN 1

### Multifunctional Tool that helps you to work faster and safer.



A touch of just one button is all it takes to transform your individual CNX tools into a wirelessly connected team for an instant overview of various readings.



**Fluke CNX i3000**  
iFlex™ AC Current Clamp



**Fluke CNX v3000**  
AC Voltage

**Fluke CNX pc3000**  
PC adapter



**Fluke CNX 3000**  
Wireless Multimeter



**Fluke CNX t3000**  
K-type Temperature



**Fluke CNX a3000**  
AC Current Clamp



**Fluke Ti100 series**  
Thermal Imager

[www.fluke.ie/wireless](http://www.fluke.ie/wireless)

# Fluke Thermal Imagers



**Fluke Ti100**



The perfect general use camera designed for professionals needing pick up-and-go simplicity

- Laser pointer
- Field replaceable, easy release battery
- True one-handed operation
- Rugged
- SmartView software
- IR-Fusion Picture-in-Picture (Ti105 only)



*IR-Fusion  
Picture-in-Picture*



**Fluke Ti105**

## Fluke T5-H5-1AC Kit



- Fluke T5-1000 Electrical Tester
- H5 Holster
- 1AC-II VoltAlert™

**Fluke T5-H5-1AC Kit**

## Fluke 117/323 Kit



- Fluke 117 Digital Multimeter
- Fluke 323 Clamp Meter

**Fluke 117/323 Kit**

# Fluke 1654B Multifunction Installation Tester – now with **FREE** software and earth spike kit!



The 1654B Installation Tester is the rugged reliable Multifunction Installation tester from Fluke designed to meet your needs for easy to use productive test tools. Some key capabilities of this tester are: Fast high current loop test, Test smooth DC sensitive RCDs (Type B), Loop & Line Resistance-mΩ resolution.

**Special Promotion**



**Fluke 1651B** - Basic Multifunction Installation Tester

**Fluke 1652C** - Multifunction Installation Tester

**Fluke 1653B** - Multifunction Installation Tester with download capability

**Fluke 1654B** - Multifunction Installation Tester with download capability

**Fluke 1654B/LIMITED EDITION KIT** - Multifunction Tester supplied with Software and Earth spikes

# Fluke 6000 Portable Appliance Testers



The Fluke 6500 portable appliance tester has redefined auto test capabilities to help you increase the number of portable appliance tests performed per day. They're designed to enable you to work faster without compromising safety - yours or your customer's. Some key capabilities are: designed for 'one-touch' operation & a fast throughput, pre-set pass/fail levels to save time, integral QWERTY keyboard for rapid data entry and additional Compact Flash memory card.

**Optional accessory:**  
DMS 0702/PAT  
Data Management  
Software for  
appliance testing



**Fluke 6500**

# Choose the best Fluke precision temperature meter for your job



Easy and all-round measurements.

**Fluke 62 MAX**  
**Fluke 62 MAX+**



All-round measurements including contact measurement.

**Fluke 561**



High precision measurements from longer distances, including contact measurements and datalogging.

**Fluke 566**  
**Fluke 568**  
**Fluke 572-2**



Visualise your measurements for faster recognition of the temp environment.

**Fluke VT02**  
**Fluke VT04**

## Fluke 572-2 Infrared Thermometer



**Fluke 572-2**



**The best choice when things are really hot.**

- Measure -30°C to 900°C
- 60:1 distance to spot ratio with dual laser sighting
- Multi-language interface
- Current Temperature plus MAX, MIN, DIF, AVG temperature displays
- Compatible with all standard mini-connector K-type thermocouples
- Data storage and review (99 data sets)

# Fluke VT04 Visual IR Thermometer

The NEW Fluke VT04 is the latest addition to the Visual IR Thermometer family. The VT04 produces a thermal heat map with enhanced blending to get the full picture allowing users to find problems quicker and easier.



**NEW**

**Fluke VT04  
Coming soon!**



## 5 reasons to choose a Visual IR Thermometer:

### Find Tough Problems

The VT04 temperature alarm feature and hot and cold markers pinpoint the problem area - **New in VT04.**

### Wider field of view

Improved scanning and the ability to get more context in tight spaces - **New in VT04.**

### Rechargeable battery

Convenient Li-ion rechargeable battery with 8-hour charge for long days in the field - **New in VT04.**

### Detect Issues Instantly

Problem areas are instantly visible in a thermal heat map image.

### Compact size

Perfect fit for your tool bag.



## BEST IN TEST FOR 65 YEARS.

**Come celebrate our 65th anniversary with us and get a FREE gift or extended warranty with purchase!**



Go to  
[www.fluke.ie/65](http://www.fluke.ie/65)  
and check out  
the special actions  
of this month.



## True-RMS AC/DC Clamp Meter with iFlex™



**Fluke 376**

## Laser Distance Meters

Fluke laser distance meters will become the next essential item on your toolbelt.



**Fluke 414D**  
**Fluke 419D**  
**Fluke 424D**

## Electrical Testers

The Fluke T5 testers let you check voltage, continuity and current with one compact tool.



**Fluke T5-600**  
**Fluke T5-1000**

## Clamp Meter with detachable jaw



**Fluke 365**

## True RMS Clamp Meters

Robust, easy, fast and safe, as expected from Fluke.



**Fluke 323**  
**Fluke 324**  
**Fluke 325**

## VoltAlert™

When the tip of the Fluke VoltAlert™ AC voltage detector glows red, you know there is voltage on the line.



**Fluke 2AC**

## Cable locator

The multipurpose solution to cable location.



**Fluke 2042**