



Carriers

VersaMax provides several types of snap-together I/O carriers and interposing terminals to provide maximum wiring flexibility, as well as module hot insertion and removal. VersaMax carriers support IEC box-style, spring-style, and barrier-style terminals and are also available as snap-on auxiliary terminal strips and interposing terminals that can be mounted separately and connected to a connector-style carrier by an I/O cable.

	IC200CHS003	IC200CHS011	IC200CHS012	IC200CHS014	IC200CHS015
Product Name	VersaMax I/O Carrier, VersaMax I/O Carrier, Connector Style. Interposing Barrier A connecting cable (Requires IC200CBL1xxx) and IC200CHS003 base interposing base (IC200CHS011, and connecting CHS012, CHS014, CHS015, cable IC200CBL1xxx) IC200CHS1xx or IC200CHS2xx) are required. This carrier can be used with all VersaMax I/O modules EXCEPT the following, due to their high isolation requirements: IC200MDL144 Input 240 VAC 4 Point Isolated Module; IC200MDL244 Input 240 VAC 8 Point Isolated Module; IC200MDD850 Mixed 240 VAC Isolated 4 Point / Output Relay 2.0A Isolated 8 Point Module	VersaMax I/O Carrier, Interposing Box Style (Requires IC200CHS003 base and connecting cable IC200CBL1xxx)	VersaMax I/O Carrier, Interposing Box Thermocouple Compensation (Requires IC200CHS003 base and connecting cable IC200CBL1xxx)	VersaMax I/O Carrier, Interposing Spring Clamp (Requires IC200CHS003 base and connecting cable IC200CBL1xxx)	VersaMax I/O Carrier, Interposing Spring Clamp (Requires IC200CHS003 base and connecting cable IC200CBL1xxx)
Lifecycle Status	Active	Active	Active	Active	Active
Field Termination Type	Integrated	Non-Integrated	Non-Integrated	Integrated	Non-Integrated
Wiring Termination Style	Connector	Barrier	Box	Box-Thermocouple Compensation	Spring
Orientation on Module on Base	Vertical	N/A	N/A	N/A	N/A
Dimensions (W x H x D)	66.8 mm (2.63 in) x 133.4 mm (5.25 in) x 70 mm (2.75 in), not including the height of DIN Rail	110.5 mm (4.35 in) x 105.4 mm (2.63 in) x 70 mm (2.75 in), not including the height of DIN Rail	110.5 mm (4.35 in) x 105.4 mm (2.63 in) x 70 mm (2.75 in), not including the height of DIN Rail	110.5 mm (4.35 in) x 105.4 mm (2.63 in) x 70 mm (2.75 in), not including the height of DIN Rail	110.5 mm (4.35 in) x 105.4 mm (2.63 in) x 70 mm (2.75 in), not including the height of DIN Rail
Cables	Requires a IC200CBL1xxx cable	Requires a IC200CBL1xxx cable	Requires a IC200CBL1xxx cable	Requires a IC200CBL1xxx cable	Requires a IC200CBL1xxx cable