

## Discrete Mixed I/O Modules



Discrete mixed modules provide maximum flexibility by combining inputs and outputs in a single, compact module. Discrete input modules receive signals from input devices such as sensors, push-buttons, and switches that can have two states: on or off, open or closed. Discrete output modules send control signals to devices such as contactors, indicator lamps, and interposing relays that can also have two states. Discrete mixed modules provide maximum flexibility by combining inputs and outputs in a single, compact module. Modules require a carrier base (IC200CHSxxx).

	IC200MDD840	IC200MDD842	IC200MDD843
Product Name	VersaMax Discrete Mixed Modules, 24 VDC Pos Logic Input 20 points/Output Relay 2.0 A, 12 points	VersaMax Discrete Mixed Modules 24 VDC Pos Logic Input 16/Output 24 VDC 0.5 A with ESCP	VersaMax Discrete Mixed Modules 24 VDC Positive Logic Input 10/Output Relay 6
Lifecycle Status	Active	Active	Active
Input Voltage	24 VDC	24 VDC	24 VDC
Output Voltage	0-125 VDC, 5/24/125 VDC nominal; 0-265 VAC (47-63 Hz), 120/240 VAC nominal	24 VDC	0-125 VDC, 5/24/125 VDC nominal; 0-265 VAC (47-63 Hz), 120/240 VAC nominal
Number of Points	20 in/12 out	16 in/16 out	10 in/6 out
Channel to Channel Isolation	No	No	No
Load Current per Point	2.0 A for 5-265 VAC, 2.0 A for 5-30 VDC	0.5 A for 30 VDC	2.0 A for 5-265 VAC, 2.0 A for 5-30 VDC, 0.2 A for 31-125 VDC
Input and Output Response Time- On/Off(ms)	0.5 and 10	0.5 and 0.5	0.5 and 10
Protection	No internal fuses or snubbers	Short circuit protection, overcurrent protection, free-wheeling diodes	No internal fuses or snubbers
On State Current	2.0-5.5 mA	2.0-5.5 mA	2.0-5.5 mA
Off State Current	0-0.5 mA	0-0.5 mA	0-0.5 mA
External Power Supply	0-125 VDC, 5/24/125 VDC nominal; 0-265 VAC (47-63 Hz), 120/240 VAC nominal	18-30 VDC, 24 VDC nominal	0-125 VDC, 5/24/125 VDC nominal, 0-265 VAC (47-63 Hz), 120/240 VAC nominal
Input Impedance	10 kOhms maximum	10 kOhms maximum	10 kOhms maximum
Load Current	2.0 A for 5-265 VAC or 5-30 VDC, 0.2 A for 31-125 VDC	0.5 Amp at 30 VDC maximum (resistive); 2.0 Amps maximum for 100ms inrush	10mA per point minimum, 8.0A maximum per module; 2.0 Amps for 5 to 265 VAC maximum (resistive); 2.0 Amps for 5 to 30 VDC maximum (resistive); 0.2 Amp for 31 to 125 VDC maximum (resistive)
5V Backplane Current Consumption (mA)	375 maximum	100 maximum	190 maximum
LED Indicators	One LED per point shows individual point on/off state (logic side); OK LED indicates backplane power is present	One LED per point shows individual point on/off state (logic side); OK LED indicates backplane power is present	One LED per point shows individual point on/off state (logic side); OK LED indicates backplane power is present
Dimensions (W x H x D)	110 mm (4.3 in) x 66.8 mm (2.63 in) x 50 mm (1.956 in), not including the height of the carrier or the mating connectors	110 mm (4.3 in) x 66.8 mm (2.63 in) x 50 mm (1.956 in), not including the height of the carrier or the mating connectors	110 mm (4.3 in) x 66.8 mm (2.63 in) x 50 mm (1.956 in), not including the height of the carrier or the mating connectors