

Heat Detectors

245A AND 246A



245A and 246A


FEATURES

- FIXED TEMPERATURE
- SELF RESTORING
- OPEN CIRCUIT TYPE
- EASY TO INSTALL
- PROTECTS 400 SQ. FT. (37 SQ. METERS)
- ULC LISTED

DESCRIPTION

The 245A and 246A heat detectors operate on a fixed temperature principle and will self-restore as the surrounding temperature returns to normal. The detector's contact rating is 1 amp at 24V/125VAC and 0.5 amp at 24Vdc. The finish is matte white.

INSTALLATION AND MOUNTING



ORDERING INFORMATION

Cat.No.	Description
245A	Operates at 135°F (57°C)
246A	Operates at 190°F (88°C)
CCS-1182	Wire guard

IMPORTANT NOTE: Independent studies indicate that heat detectors should only be used when property protection alone is involved. In cases where life safety is a factor, smoke detectors are recommended.

Heat Detectors

280-PL SERIES (FORMERLY 280C SERIES)



280-PL Series


FEATURES

- LOW PROFILE DESIGN
- POSITIVE OPERATING INDICATION
- EASY TO INSTALL
- AVAILABLE IN FIXED TEMPERATURE AND FIXED TEMPERATURE/RATE OF RISE
- OPEN CIRCUIT TYPE
- ULC LISTED

DESCRIPTION

The 280-PL Series detector operates on a fixed temperature or combination fixed temperature and rate-of-rise principle. When the fixed temperature element is activated, the center disc of the detector will fall free. The detector's contact rating is 3 amps at 125 VAC and 1 amp at 28VDC. The finish is matte white.

INSTALLATION AND MOUNTING



ORDERING INFORMATION

Cat.No.	Description
281B-PL	Rate-of-rise and fixed temperature, 135°F (57°C)
282B-PL	Rate-of-rise and fixed temperature, 194°F (90°C)
283B-PL	Fixed temperature, 135°F (57°C)
284B-PL	Fixed temperature, 194°F (90°C)
CCS1182	Wire guard
6253	Surface skirt

IMPORTANT NOTE: Independent studies indicate that heat detectors should only be used when property protection alone is involved. In cases where life safety is a factor, smoke detectors are recommended.